

Color :  White

UPC Code : 078477330340

Country Of Origin : Mexico

Available Colors :



Ivory

1241-W

15 Amp, 120/277 Volt, Toggle Pigtail Single-Pole AC Quiet Switch, Heavy Duty Spec Grade, Grounding, Wire lead 6-Inch Wired - WHITE

Leviton's Commercial Specification Grade switches are designed to offer outstanding reliability and top performance in commercial settings. Ideal applications include municipal facilities, government buildings, malls, department stores, hospital and health care facilities, office buildings, schools, colleges, universities, houses of worship and cultural institutions. Leviton offers a large selection of 15 and 20 Amp Commercial switches, available in a wide variety of colors, wiring options and other features.

Technical Information

AC Horsepower Ratings

HP Rating : 1/2HP-120V 2HP-240V-277V

Electrical Specifications

Amperage : 15 A

Current Interrupting : Certified for current interrupting at full rated current

Dielectric Voltage Withstand : 1500V minimum

Grounding : Self-Grounding

Max. Amperage : 12 Amp

Maximum Working Voltage : 120/277 VAC as rated

Temperature Rise : Maximum 30 degrees C rise

Voltage : 120/277 VAC

Environmental Specifications

Flammability : Rated V-2 per UL 94

Operating Temperature : -40°C to 65°C

Material Specifications

Actuator Material : Thermoplastic

Base Material : Urea

Body Material : Thermoplastic

Color : White

Contacts : Silver-Cadmium .031 Thick

Cover Material : Urea

Grounding Leads : 6", #12 AWG THHN

Mounting Screws : Triple Combination Head, Steel

Mounting Strap : Steel

Strap Material : .048" Thick Galvanized Steel

Terminal Leads : 6", #12 AWG THHN

Termination : Pre-Wired Leads

Mechanical Specifications

Lead Identification : Leads identified in accordance with UL 498 (black, white & green)

Product ID : Ratings are permanently marked on device

Terminal Accom. : 14-10 AWG

Terminal ID : Brass-Hot Black-Hot White-Neutral Green-Gnd

Termination : Pre-Wired Leads

Torque Range : 12-14 inch pounds

Product Features

Color : White

Device Type : Toggle Switch

Function : Single-Pole

Grade : Extra Heavy-Duty Industrial Specification Grade

Standards and Certifications

ANSI : C-73

CSA C22.2 No. 111 : File #152105


NEMA : WD-1 & WD-6

NOM : 057


UL Fed Spec WS896E : File #E7458

UL Standard : UL 20

Warranty : 2-Year Limited



SINGLE-POLE Wiring Diagram Single Pole



SPECIFICATION SUBMITTAL

JOB NAME: <input type="text"/>	CATALOG NUMBERS: <input type="text"/> <input type="text"/> <input type="text"/>		
JOB NUMBER: <input type="text"/>	<input type="text"/>		

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):

+1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2018 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/international/contacts/

