

DMM-B 13/32" x 1-3/8" and 1-1/2" 1000Vac/dc fast-acting fuses for multi-meters



Catalog symbol / color code:

- DMM-B
- Maroon (1000Vac/dc max voltage)

Description:

Fast-acting supplemental fuse for multi-meters only.

Intended to carry 100% of rated current indefinitely.

Not intended for branch circuit protection.

Specifications:

Ratings

Fuse amp range	Interrupting rating at rated voltage	Agency information	
	1000Vac/dc	UL®	CSA®
44/100 and 11	*	X	–

* DMM-B-44/100 – 10kA, 1000Vac, unity power factor and 10kA, 1000Vdc with time constant of 2.2ms. Minimum interrupt 400% of rated current at rated voltage.

DMM-B-11A – 20kA, 1000Vac, power factor ≤0.2; 20kA, 1000Vdc, time constant ≥10ms.

Agency information

- CE
- UL Recognized 1000Vdc, File E19180)
- RoHS compliant


Temperature specifications

- DMM-B-44/100 - Maximum temperature 28°C in 22°C ambient temperature when carrying 100% of rated current.
- DMM-B-11A - Maximum temperature 69°C in a 22°C ambient temperature when carrying 100% of rated current.

Catalog numbers (amps)

DMM-B-44/100 DMM-B-11A

Dimensions - in:



Carton quantity

Amps	Qty.
44/100 and 11	10


Features:

- Color coded for 1000Vac/dc maximum voltage rating
- Melamine tube construction
- Nickel-plated endcaps

Typical applications

- Multi-meters

Time-current characteristic curves – total clearing:



The only controlled copy of this data sheet is the electronic read-only version located on the Eaton network drive. All other copies of this document are by definition uncontrolled. This bulletin is intended to clearly present comprehensive product data and provide technical information that will help the end user with design applications. Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

Bussmann Division
114 Old State Road
Ellisville, MO 63021
United States
Eaton.com/bussmannseries

© 2015 Eaton
All Rights Reserved
Printed in USA
Publication No. 1047 - BU-SB14305
December 2015

Eaton and Bussmann are valuable trademarks of Eaton in the US and other countries. You are not permitted to use the Eaton trademarks without prior written consent of Eaton.

CSA is a registered trademark of the Canadian Standards Group.
UL is a registered trademark of the Underwriters Laboratories, Inc.

For Eaton's Bussmann series product information, call 1-855-287-7626 or visit: Eaton.com/bussmannseries

Follow us on social media to get the latest product and support information.

