






FCIconnect.com

Copyright FCI


PRODUCT NUMBER
SEE TABLE AND NOTES 1 & 2 ONSHEET 3





mat'l. code SEE NOTE 3				surface ISO 1302 ✓				tolerance ISO 406 ISO 1101				projection 				product family HPC															
ltr ecn no dr date				tolerances unless otherwise specified																title											
S I11-0094 SAL 2011-05-23				angles linear		.XX±.01/.3						4 ROW VERTICAL HEADER																			
T ELX-I-13738 MJA 2012-12-21						.XXX±.005/.13						W/PRESS-FIT PINS, 0 G.P.																			
U ELX-I-16877 MJA 2014-01-29				0°±2°		.XXX±.0020/.051						scale 1:1				dwg no sheet 1 of 14 size 50009 A3 type Product Customer Drawing															
- - - -				dr		D.HORCHLER		2005-06-29																							
N V05-0999 DAI 10/29/05				enr		D.HORCHLER		2005-06-29																							
P M06-0283 MHT 7/27/06				chr		M JACOB		2014-01-29																							
R M06-0447 AGS 11/07/06				appd		BIJU K PAUL		2014-01-29																							
sheet index		revision sheet		U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U									
				1	2	3	4	5	6	7	8	9	10	11	12	13	14														

PRODUCT NO.
SEE TABLE



SECTION U-U



SECTION X-X



RECOMMENDED PCB LAYOUT
(ALL HOLES LOCATED ON .100/2.54 GRID
UNLESS OTHERWISE SPECIFIED)

mat'l. code SEE NOTE 3				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HPC											
ltr	ecn no	dr	date	tolerances unless otherwise specified						title											
U				angles	linear	.XX±.01/.3		INCH/MM 	4 ROW VERTICAL HEADER												
						.XXX±.005/.13			W/PRESS—FIT PINS, 0 G.P.												
				0°±2°		.XXX±.0020/.051		scale 1:1													
				dr	D.HORCHLER	2005—06—21			dwg no						sheet 2 of 14				size		
				enr	D.HORCHLER	2005—06—21			50009										A3		
				chr	M JACOB	2014—01—29															
				appd	BIJU K PAUL	2014—01—29															
sheet index		revision sheet																			

NOTES:

①. PRODUCT NUMBERING CODE:
 50009 - X YYY Z LF
 LEAD FREE OPTION
 TAIL LENGTH, SEE TABLE
 NO. OF POSITIONS SEE NOTE 2
 PLATING IN CONTACT AREA SEE TABLE
 BASE NUMBER

PRODUCT NUMBERING CODE FOR
 SELECT LOAD PART NUMBERS:
 50009 - XXYYY LF
 LEAD FREE OPTION
 SEQUENCE NUMBER
 ALWAYS 'XX'
 BASE NUMBER

②. THIS PRODUCT IS CONFIGURED IN SIZES OF 6 thru 100 COLUMNS IN INCREMENTS OF ONE.
 i.e.: 6,7,8,9,.....99,100.

③. HOUSING MATERIAL: GLASS AND MINERAL FILLED HIGH TEMP. THERMOPLASTIC. FLAME RETARDANT PER UL94V-0. COLOR: BLACK.
 PIN MATERIAL: PHOS BRONZE

④. LENGTH CALCULATIONS:
 DIMENSION "A" = $.100/2.54 \times \text{NO. OF COLUMNS} + .75/19.1$
 DIMENSION "B" = $.100/2.54 \times \text{NO. OF COLUMNS} + .450/11.43$,
 DIMENSION "C" = $.100/2.54 \times \text{NO. OF COLUMNS} - .100/2.54$
 DIMENSION "D" = $.100/2.54 \times \text{NO. OF COLUMNS} + .050/1.27$

⑤. REFERENCE 50807 FOR F.M.L.B. AVAILABLE OPTIONS. SEE SHEETS 4-9. AND WORKSHEET.

⑥. $\phi .0453/1.151$ DRILLED HOLE PLATED WITH $.0003/.007$ MIN. SnPb OVER $.001/.03$ to $.003/.08$ Cu. PLATING TO ACHIEVE A $\phi .040 \pm .003/1.02 \pm .08$ HOLE.

⑦. TO ASSURE PROPER INSTALLATION: TOOLING, AS SPECIFIED IN INSTRUCTION MANUAL 155915-001 MUST BE USED. PIN MATING LENGTH WILL BE $\pm .002/.05$ AFTER INSTALLATION.

⑧. COMPANY NAME, PART NUMBER AND LOT CODE TO APPEAR ON THIS SURFACE PER BUS-12-108.


⑨. PRODUCT WITH "LF" SUFFIX MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

⑩. THIS PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING SOLDER PROCESS. HOWEVER, THE HOUSING MATERIAL WILL WITHSTAND HEAT UP TO THE 260°C .

- ②. THIS PRODUCT IS CONFIGURED IN SIZES OF 6 thru 100 COLUMNS IN INCREMENTS OF ONE.
i.e.: 6,7,8,9,.....99,100.
- ③. HOUSING MATERIAL: GLASS AND MINERAL FILLED
HIGH TEMP. THERMOPLASTIC. FLAME RETARDANT PER UL94V-0. COLOR: BLACK.
PIN MATERIAL: PHOS BRONZE
- ④. LENGTH CALCULATIONS:
DIMENSION "A" = $.100/2.54 \times \text{NO. OF COLUMNS} + .75/19.1$
DIMENSION "B" = $.100/2.54 \times \text{NO. OF COLUMNS} + .450/11.43$,
DIMENSION "C" = $.100/2.54 \times \text{NO. OF COLUMNS} - .100/2.54$
DIMENSION "D" = $.100/2.54 \times \text{NO. OF COLUMNS} + .050/1.27$
- ⑤. REFERENCE 50807 FOR F.M.L.B. AVAILABLE OPTIONS. SEE SHEETS 4-9. AND WORKSHEET.
- ⑥. $\phi .0453/1.151$ DRILLED HOLE PLATED WITH $.0003/.007$ MIN. SnPb OVER $.001/.03$ to $.003/.08$ Cu. PLATING TO ACHIEVE A $\phi .040 \pm .003/1.02 \pm .08$ HOLE.
- ⑦. TO ASSURE PROPER INSTALLATION: TOOLING, AS SPECIFIED IN INSTRUCTION MANUAL 155915-001 MUST BE USED. PIN MATING LENGTH WILL BE $\pm .002/.05$ AFTER INSTALLATION.
- ⑧. COMPANY NAME, PART NUMBER AND LOT CODE TO APPEAR ON THIS SURFACE PER BUS-12-108.
- ⑨. PRODUCT WITH "LF" SUFFIX MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- ⑩. THIS PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING SOLDER PROCESS. HOWEVER, THE HOUSING MATERIAL WILL WITHSTAND HEAT UP TO THE 260° C.
- ⑪. ADD LF SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- ⑫. TERMINAL PORTION OF THE CONNECTOR TO BE LUBED BEFORE PACKING.

form: A3 1 2 3 4 PDS: Rev. 11 STATUS: Released Printed: Jan 29, 2014 6


PRODUCT NO.	ITEM KEY	SIGNAL DATA			
		SIZE 4 x 25	TOTAL NO. OF POSITIONS –100	NO. OF POSITIONS LOADED – 100	
				PRESS FIT STYLE	
		PLATING	QTY.	MATING LENGTH	TAIL LENGTH
50009–XX005	A	SEE SHEET 3	98	.220 / 5.59	.177 / 4.50
	B	SEE SHEET 3	2	.260 / 6.60	.177 / 4.50
50009–XX005LF	A	SEE SHEET 3	98	.220 / 5.59	.177 / 4.50
	B	SEE SHEET 3	2	.260 / 6.60	.177 / 4.50



- ALL POSITIONS ARE LOADED WITH "A", EXCEPT AS SHOWN.
- COLUMN 1, ROW A IS DESIGNATED AS SIGNAL PIN 1, AS VIEWED FROM THE MATING FACE.

mat'l. code SEE NOTE 3				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HPC			
ltr	ecn no	dr	date	tolerances unless otherwise specified		scale 1:1	title 4 ROW VERTICAL HEADER W/PRESS–FIT PINS, 0 G.P.			
U				angles	linear					
				0°±2°						
				dr	D.HORCHLER	2005–06–29				
				enr	D.HORCHLER	2005–06–29	FCJ	dwg no		sheet 4 of 14
				chr	M JACOB	2014–01–29		50009		A3
				appd	BIJU K PAUL	2014–01–29		type		Product Customer Drawing
sheet index	revision sheet									

PRODUCT NO.	ITEM KEY	SIGNAL DATA		
		SIZE 4 x 25	TOTAL NO. OF POSITIONS -100	NO. OF POSITIONS LOADED - 100
		CONTACT PLATING	QTY.	MATING LENGTH
50009-XX067	A	SEE SHEET 3	98	.200 / 5.08
	B	SEE SHEET 3	2	.240 / 6.10
50009-XX067LF	A	SEE SHEET 3	98	.200 / 5.08
	B	SEE SHEET 3	2	.240 / 6.10



1. ALL POSITIONS ARE LOADED WITH "A", EXCEPT AS SHOWN.
2. COLUMN 1, ROW A IS DESIGNATED AS SIGNAL PIN 1, AS VIEWED FROM THE MATING FACE.

mat'l. code SEE NOTE 3				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HPC
ltr	ecn no	dr	date	tolerances unless otherwise specified		scale 1:1	title 4 ROW VERTICAL HEADER W/PRESS-FIT PINS, 0 G.P.
U				angles	linear		
				0°±2°			
				dr	D.HORCHLER	2005-06-29	dwg no 50009 type Product Customer Drawing
				enr	D.HORCHLER	2005-06-29	
				chr	M JACOB	2014-01-29	
				appd	BIJU K PAUL	2014-01-29	
sheet index	revision sheet						



PRODUCT NO.	ITEM KEY	SIGNAL DATA				
		SIZE 4 x 50	TOTAL NO. OF POSITIONS – 200		NO. OF POSITIONS LOADED – 200	
		PIN PLATING	QTY.	MATING LENGTH	TAIL LENGTH	TOTAL PIN LENGTH
50009–XX076	A	SEE SHEET 3	130	.230 / 5.84	.177 / 4.50	.595 / 15.11
	B	SEE SHEET 3	68	.270 / 6.86	.177 / 4.50	.634 / 16.10
	C	SEE SHEET 3	2	.190 / 4.83	.177 / 4.50	.555 / 14.10
50009–XX076LF	A	SEE SHEET 3	130	.230 / 5.84	.177 / 4.50	.595 / 15.11
	B	SEE SHEET 3	68	.270 / 6.86	.177 / 4.50	.634 / 16.10
	C	SEE SHEET 3	2	.190 / 4.83	.177 / 4.50	.555 / 14.10

	1		5		10		15		20		25		30		35		40		45		50	
<u>D</u>		B	C		B		B		B		B		B		B		B		B		B	C
<u>C</u>		B		B		B		B		B		B		B		B		B		B		B
<u>B</u>		B		B		B		B		B		B		B		B		B		B		B
<u>A</u>		B		B		B		B		B		B		B		B		B		B		B
PIN																						


PIN

1



1. ALL POSITIONS ARE LOADED WITH "A", EXCEPT AS SHOWN.
2. COLUMN 1, ROW A IS DESIGNATED AS SIGNAL PIN 1, AS VIEWED FROM THE MATING FACE.

mat'l. code SEE NOTE 3				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HPC														
ltr	ecn no	dr	date	tolerances unless otherwise specified						 INCH/MM		title 4 ROW VERTICAL HEADER W/PRESS-FIT PINS, 0 G.P.												
U				angles	linear	.XX±.01/.3																scale 1:1		
						.XXX±.005/.13																		
				0°±2°			.XXX±.0020/.051																	
				dr	D.HORCHLER	2005-06-29																		
				engr	D.HORCHLER	2005-06-29																		
				chr	M JACOB	2014-01-29																		
				appd	BIJU K PAUL	2014-01-29																		
sheet index		revision sheet										dwg no		sheet 7 of 14				size						
												50009						A3						
												type		Product		Customer		Drawing						

PRODUCT NO.	SIGNAL DATA				
	SIZE 4 x 35	TOTAL NO. OF POSITIONS -140	NO OF POSITIONS LOADED - 140		
	ITEM KEY	PINS: PLATING:	QUANTITY	MATING LENGTH	TAIL LENGTH
50009-XX124	A	SEE SHEET 3	140	.220 / 5.59	.603 / 15.32
50009-XX124LF	A	SEE SHEET 3	140	.220 / 5.59	.603 / 15.32



1. ALL POSITIONS ARE LOADED WITH "A".
2. COLUMN 1 ROW A IS DESIGNATED AS SIGNAL PIN 1, AS VIEWED FROM THE MATING FACE.

mat'l. code SEE NOTE 3				surface ISO 1302	tolerance ISO 406 ISO 1101	projection 	product family HPC			
ltr	ecn no	dr	date	tolerances unless otherwise specified		INCH/MM 	title 4 ROW VERTICAL HEADER W/PRESS-FIT PINS, 0 G.P.			
U				angles	linear					
				0°±2°						
				dr	D.HORCHLER	2005-06-29		dwg no		sheet 8 of 14
				enr	D.HORCHLER	2005-06-29		50009		A3
				chr	M JACOB	2014-01-29		type		
				appd	BIJU K PAUL	2014-01-29				
sheet index	revision sheet									



PRODUCT NUMBER	ITEM KEY	SIGNAL DATA			
		SIZE 4 x 50	TOTAL NO. OF POSITIONS –200	NO. OF POSITIONS LOADED – 200	
				PRESS FIT STYLE	
		PIN PLATING	QTY.	MATING LENGTH	TAIL LENGTH
50009–XX187	A	SEE SHEET 3	85	.220 / 5.59	.561 / 14.25
	B	SEE SHEET 3	1	.180 / 4.57	.521 / 13.23
	C	SEE SHEET 3	8	.260 / 6.60	.601 / 15.27
	D	SEE SHEET 3	106	.220 / 5.59	.177 / 4.50
50009–XX187LF	A	SEE SHEET 3	85	.220 / 5.59	.561 / 14.25
	B	SEE SHEET 3	1	.180 / 4.57	.521 / 13.23
	C	SEE SHEET 3	8	.260 / 6.60	.601 / 15.27
	D	SEE SHEET 3	106	.220 / 5.59	.177 / 4.50

	1	5	10	15	20	25
<u>D</u>	A	A	A	A	A	A
<u>C</u>	A	A	C	A	A	A
<u>B</u>	A	A	C	A	A	C
<u>A</u>	A	A	A	A	A	A

PIN
1

26	30	35	40	45	50
A	A	A	A	A	A
	A	A	A	A	C
A	A	A	A	A	C
A	A	A	A	A	


1. ALL POSITIONS ARE LOADED WITH "D" EXCEPT AS SHOWN.
2. COLUMN 1, ROW A IS DESIGNATED AS SIGNAL PIN 1, AS VIEWED FROM THE MATING FACE.

mat'l. code SEE NOTE 3				surface ISO 1302	tolerance ISO 406 ISO 1101	projection 	product family HPC			
ltr	ecn no	dr	date	tolerances unless otherwise specified		INCH/MM 	title 4 ROW VERTICAL HEADER W/PRESS–FIT PINS, 0 G.P.			
U				angles	linear					
				0°±2°						
				dr	D.HORCHLER	2005–06–29		dwg no		sheet 9 of 14
				engr	D.HORCHLER	2005–06–29		50009		A3
				chr	M JACOB	2014–01–29		type Product Customer Drawing		
				appd	BIJU K PAUL	2014–01–29				
sheet index	revision sheet									

PRODUCT NUMBER	ITEM KEY	SIGNAL DATA			
		SIZE 4 x 80	TOTAL NO. OF	POSITIONS -320	NO. OF POSITIONS LOADED - 320
		PRESS FIT STYLE			
		PIN PLATING	QTY.	MATING LENGTH	TAIL LENGTH
50009-XX188	A	SEE SHEET 3	304	.210 / 5.33	.533 / 13.54
	B	SEE SHEET 3	16	.244 / 6.20	.533 / 13.54
50009-XX188LF	A	SEE SHEET 3	304	.210 / 5.33	.533 / 13.54
	B	SEE SHEET 3	16	.244 / 6.20	.533 / 13.54

	1	5	10	15	20	25	30	35	40	
D	B	B								
C	B	B								
B	B	B								
A	B	B								
PIN 1										
	41	45	50	55	60	65	70	75	80	
									B	B
									B	B
									B	B
									B	B



1. ALL POSITIONS ARE LOADED WITH "A" EXCEPT AS SHOWN.
2. COLUMN 1, ROW A IS DESIGNATED AS SIGNAL PIN 1, AS VIEWED FROM THE MATING FACE.

mat'l. code SEE NOTE 3				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HPC											
ltr	ecn no	dr	date	tolerances unless otherwise specified						 INCH/MM scale 1:1		title 4 ROW VERTICAL HEADER W/PRESS-FIT PINS, 0 G.P.									
U				angles	linear	.XX±.01/.3															
						.XXX±.005/.13															
						.XXXX±.0020/.051															
				dr	D.HORCHLER	2005-06-29				dwg no				sheet10 of 14				size			
				enr	D.HORCHLER	2005-06-29				50009				A3							
				chr	M JACOB	2014-01-29															
				appd	BIJU K PAUL	2014-01-29															
sheet index		revision sheet																			

		1			2	3									4			5			6
PRODUCT NUMBER	ITEM KEY	SIGNAL DATA																			
		SIZE 4 x 80		TOTAL NO. OF POSITIONS –320				NO. OF POSITIONS LOADED – 320													
						PRESS FIT STYLE															
		PIN PLATING		QTY.		MATING LENGTH			TAIL LENGTH												
50009–XX189	A	SEE SHEET 3		304		.210 / 5.33			.660 / 16.76												
	B	SEE SHEET 3		16		.245 / 6.22			.660 / 16.76												
50009–XX189LF	A	SEE SHEET 3		304		.210 / 5.33			.660 / 16.76												
	B	SEE SHEET 3		16		.245 / 6.22			.660 / 16.76												

		1	5		10		15		20		25		30		35		40
<u>D</u>		B	B														
<u>C</u>		B	B														
<u>B</u>		B	B														
<u>A</u>		B	B														
PIN 1																	
		41	45		50		55		60		65		70		75		80
																	B B
																	B B
																	B B
																	B B

1. ALL POSITIONS ARE LOADED WITH "A" EXCEPT AS SHOWN.
2. COLUMN 1, ROW A IS DESIGNATED AS SIGNAL PIN 1, AS VIEWED FROM THE MATING FACE.



mat'l. code SEE NOTE 3				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HPC												
ltr	ecn no	dr	date	tolerances unless otherwise specified						 INCH/MM		title 4 ROW VERTICAL HEADER W/PRESS-FIT PINS, 0 G.P.										
U				angles	linear	.XX±.01/.3																scale 1:1
						.XXX±.005/.13																
				0°±2°		linear	.XXXX±.0020/.051					FCI 		dwg no				sheet11 of 14				size A3
					dr		D.HORCHLER		2005-06-29					50009								
				engr	D.HORCHLER		2005-06-29															
				chr	M JACOB		2014-01-29															
				appd	BIJU K PAUL		2014-01-29							type		Product		Customer		Drawing		
sheet index		revision sheet																				

PRODUCT NO.	ITEM KEY	SIGNAL DATA			
		SIZE 4 x 35	TOTAL NO. OF POSITIONS –140	NO. OF POSITIONS LOADED – 140	
		PLATING	QTY.	PRESS FIT STYLE	
				MATING LENGTH	TAIL LENGTH
50009–XX191	A	SEE SHEET 3	137	.220 / 5.59	.250 / 6.35
	B	SEE SHEET 3	3	.180 / 4.57	.250 / 6.35
50009–XX191LF	A	SEE SHEET 3	137	.220 / 5.59	.250 / 6.35
	B	SEE SHEET 3	3	.180 / 4.57	.250 / 6.35

	1	5	10	15	20	25	30	35	
D	B								B
C									
B									
A						B			

PIN
1

1. ALL POSITIONS ARE LOADED WITH "A", EXCEPT AS SHOWN.
2. COLUMN 1, ROW A IS DESIGNATED AS SIGNAL PIN 1, AS VIEWED FROM THE MATING FACE.

mat'l. code SEE NOTE 3				surface ISO 1302	tolerance ISO 406 ISO 1101	projection 	product family HPC			
ltr	ecn no	dr	date	tolerances unless otherwise specified		INCH/MM 	title 4 ROW VERTICAL HEADER W/PRESS–FIT PINS, 0 G.P.			
U				angles	linear					
				0°±2°						
				dr	D.HORCHLER	2005–06–29		dwg no		sheet13 of 14
				engr	D.HORCHLER	2005–06–29		50009		A3
				chr	M JACOB	2014–01–29		type Product Customer Drawing		
				appd	BIJU K PAUL	2014–01–29				
sheet index	revision sheet									

