

71922-YXXZLF

= STANDARD HOUSING COLOR GREY
(WITHOUT OPTIONAL LETTER)


S= SPECIFIC CUSTOMER PLATING OPTION
HOUSING COLOR GREY

- TOTAL NB OF POSITIONS, SEE SHEET 2

0= WITHOUT LATCH

1= STANDARD LATCH

2= LOW PROFILE LATCH



1 - HOUSING MAT'L : GLASS FILLED
THERMOPLASTIC. UL94V-0

2 - PIN MATERIAL : PHOSPHOR BRONZE

3 - PRODUCT PACKAGED IN TUBES

4 - 40N MIN LATCH RETENTION FORCE
AT FIRST EXTRACTION

5 - TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS $N \times 2.54 = 20.32\text{mm}$

6 - NO CENTRAL SLOT ON POSITIONS 6 & 8

7 - NO LEFT POLARIZATION ON POSITIONS 06, 08, 10, 14.

8 - NO GROOVE ON POSITIONS 06, 08, 10, 14, 30, 34

9 - 4.5mm SOLDER TAIL
ORDER 71922-4XX (WITH STANDARD LATCH ONLY)
ORDER 71922-5XX (WITH LOW PROFILE LATCH ONLY)

10 – RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - PLATING:

- "LF" MEANS THE PRODUCT IS LEAD-FREE, 2µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE.




b – MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C ±5°C SOLDER BATH TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm MIN THICK CIRCUIT BOARD.

c - LABELING:

— MEETS PACKAGING SPECS AS PER GS-14-920

d - LEGAL STATEMENT: SEE GS-47-0004.



mat'l. code SEE NOTES				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE			
ltr	ecn no	dr	date	tolerances unless otherwise specified						title			
V	F10-0054	LMU	10.05.19	angles		linear		mm		SHR.EL.HEADER			
W	B-16776	LMU	01.14.23							RA DR TMT			
X	B-18018	JCO	14.06.19					scale 2:1					
Y	B-18236	LMU	14.07.08	dr	D.LE	01.01.24				dwg no		sheet 1 of 2	size
AA	B-19092	LMU	14.10.16	engr	JM.C	01.01.24				71922		A3	
AB	B-20349	BVE	15.03.02	chr	JF.N	01.01.24				type		CUSTOMER Drawing	
				appd	JM.C	01.01.24							
sheet index	revision sheet	AB	T	1	2								





FCIconnect.com

Copyright FCI

PRODUCT NUMBER	SIZE	LATCHING AVAILABILITY	MISSING PIN POSITIONS
71922-X06(B)LF	2x3	0/1/2	
71922-X08(B)LF	2x4	0/1/2	
71922-X10(B)LF	2x5	0/1/2	
71922-X14(B)LF	2x7	0/1/2	
71922-X16(B)LF	2x8	0/1/2	
71922-X18(B)LF	2x9	0/1/2	
71922-X20(B)LF	2x10	0/1/2	
71922-X26(B)LF	2x13	0/1/2	
71922-X28(B)LF	2x13	0/1/2	PIN 5 TO 12
71922-X30(B)LF	2x15	0/1/2	
71922-X34(B)LF	2x17	0/1/2	
71922-X35(B)LF	2x17	0/1/2	PIN 2 & 3
71922-X39(B)LF	2x20	0/1/2	PIN 20
71922-X40(B)LF	2x20	0/1/2	
71922-X44(B)LF	2x22	0/1/2	
71922-X50(B)LF	2x25	0/1/2	
71922-X60(B)LF	2x30	0/1/2	
71922-X64(B)LF	2x32	0/1/2	

PLATING :

- 0.76µm GOLD/GXT
(PdNi WITH GOLD FLASH) ON CONTACT AREA
- 2µm MIN MATTE TIN ON TAIL
- UNDERPLATE : 1.27µm Ni MIN



mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE			
ltr ecn no dr date				tolerances unless otherwise specified				 mm scale 2:1		title SHR.EL.HEADER RA DR TMT			
M F06-0229		LMU	06.07.17	angles	linear					dwg no		sheet 2 of – size 71922 A3	
N F07-0195		LMU	07.05.25										
P F08-0146		YOV	08.04.11										
R B-16776		LMU	14.01.23	dr	D.LE		01.01.24			type CUSTOMER Drawing			
S B-19092		LMU	14.10.16	enrg	JM.C		01.01.24						
T B-20349		BVE	15.03.02	chr	JF.N		01.01.24						
				appd	JM.C		01.01.24						
sheet index		revision sheet											