

# C1608CH1H010C080AA

TDK Item Description : C1608CH1H010CT\*\*\*\*




## Application & Main Feature

Commercial Grade ( General (Up to 50V) )

## Series

C1608 [EIA CC0603]



## Dimensions

L 1.60mm +/-0.1mm  
W 0.80mm +/-0.1mm  
T 0.80mm +/-0.1mm  
B 0.20mm Min.  
G 0.30mm Min.

## Temperature Characteristic

CH (-25 to 85 degC 0+/-60ppm/degC)

## Rated Voltage

1H (50Vdc)

## Capacitance

1pF

## Capacitance Tolerance

C (+/-0.25pF)

## O Factor

420 Min.


## Insulation Resistance

10Gohm Min.


## AEC-Q200

Not Applicable


**|Z|, ESR vs. Freq. Characteristics**




**DC Bias Characteristic**



**Cap. vs. Freq. Characteristic**



**Temperature Characteristic**



All specifications are subject to change without notice.

February 3, 2014