


Features


- 130°C, 2,000 ~ 3,000 hours assured
- For automobile modules and other high temperature applications
- RoHS Compliance



SPECIFICATIONS

Items	Performance													
Operating Temperature Range	10 ~ 250V						350 ~ 450V							
	-40℃ ~ +130℃						-25℃ ~ +130℃							
Capacitance Tolerance	±20% (at 120Hz, 20℃)													
Leakage Current (at 20℃)	Rated voltage		≤ 100V				> 100V							
	Time		after 2 minutes				after 1 minutes							
	Leakage Current		I = 0.01CV or 3 (μA) whichever is greater				CV ≤ 1,000 I = 0.1CV+40(μA)		CV > 1,000 I = 0.04CV+100(μA)					
	Where, C = rated capacitance in μF V = rated DC working voltage in V													
Dissipation Factor (Tan δ at 120 Hz, 20℃)														
	Rated Voltage	10	16	25	35	50	63	160	200	250	350	400	450	
	Tan δ (max)	0.15	0.12	0.10	0.10	0.08	0.08	0.20	0.20	0.20	0.24	0.24	0.24	
Low Temperature Characteristics (at 120Hz)	Impedance ratio shall not exceed the values given in the table below.													
	Rated Voltage		10	16	25	35	50	63	160	200	250	350	400	450
	Impedance Ratio	Z(-25℃) / Z(+20℃)	3	2	2	2	2	2	3	3	3	6	6	6
		Z(-40℃) / Z(+20℃)	6	4	4	4	4	4	6	6	6	-	-	-
Load Life Test	Test Time		2,000 hrs for ϕ D ≤ 8 mm(125℃) 3,000 hrs for ϕ D ≥ 10 mm(130℃)											
	Capacitance Change		With in ±20% of initial value											
	Dissipation Factor		Less than 200% of specified value											
	Leakage Current		Within specified value											
* The above specifications shall be satisfied when the capacitors are restored to 20℃ after applied with ratedsubjected to DC voltage with the rated ripple current is applied for 2,000 / 3,000 hours at 125℃/130℃ .														
Shelf Life Test	Test Time		1,000 hrs											
	Capacitance Change		With in ±20% of initial value											
	Dissipation Factor		Less than 200% of specified value											
	Leakage Current		Less than 500% of specified value											
* The above specifications shall be satisfied when the capacitors are restored to 20℃ after exposing them for 1,000hrs at 130℃ without voltage applied.														
Ripple Current & Frequency Multipliers	W. V.(V)	Freq.(Hz)		120	1K	10K	100K up							
		Cap.(μF)												
	10 ~ 63	0.47 ~ 100	1.00	1.85	2.25	2.50								
		150 ~ 470	1.00	1.70	1.88	2.00								
		1000	1.00	1.45	1.58	1.65								
	160 ~ 450	Under 33	1.00	1.50	1.75	1.80								
47 up above		1.00	1.30	1.40	1.50									

DIAGRAM OF DIMENSIONS



LEAD SPACING AND DIAMETER Unit: mm

LEAD STRIPPING AND DIAMETER				Unit: mm
ϕD	8	10	12.5	16
P	3.5	5.0	5.0	7.5
ϕd	0.6			0.8
α	1.0	1.5		
β	0.5			

DIMENSION & PERMISSIBLE RIPPLE CURRENT

Dimension: $\phi D \times L(\text{mm})$

Ripple Current: mA/rms at 120 Hz, 130°C

μF	V. DC Contents	10V (1A)		16V (1C)		25V (1E)		35V (1V)		50V (1H)		63V (1J)	
		$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA
0.47	R47									8×11.5	18	8×11.5	18
1	010									8×11.5	26	8×11.5	26
2.2	2R2									8×11.5	39	8×11.5	39
3.3	3R3									8×11.5	48	8×11.5	48
4.7	4R7									8×11.5	57	8×11.5	57
10	100									8×11.5	84	8×11.5	84
22	220							8×11.5	113	10×12.5	149	10×12.5	149
33	330					8×11.5	138	10×12.5	162	10×16	200	10×16	200
47	470			8×11.5	150	10×12.5	194	10×16	213	10×16	239	10×20	260
100	101	10×12.5	231	10×16	285	10×16	312	10×20	338				
220	221	10×16	378	10×20	458	12.5×20	557	12.5×25	605	12.5×20	419	12.5×20	419
330	331	10×16	462	12.5×20	621	12.5×25	740	16×20	755				
470	471	10×20	599	12.5×25	806	16×20	902			16×20	689		
1,000	102	16×20	1073										

μF	V. DC Contents	160V (2C)		200V (2D)		250V (2E)		350V (2V)		400V (2G)		450V (2W)	
		$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA
4.7	4R7							10×20	53	10×20	53	10×25	58
10	100			10×20	78	10×20	78	10×25	85	10×25	86	12.5×20	86
22	220	10×20	115	10×25	126	12.5×20	128	12.5×25	139	12.5×25	142	16×25	154
33	330	10×25	154	12.5×20	157	12.5×25	171	16×25	189	16×25	189	16×31.5	203
47	470	12.5×20	187	12.5×25	204	16×25	225	16×31.5	243	16×31.5	243		
100	101	12.5×25	245	16×20	250	16×31.5	292						
220	221	16×25	329	16×25	329								
330	331	16×31.5	434										

Remark: The Case size 16×20 is used flat type rubber bung.