




1. STAMP AMP LOCATE APPROX AS SHOWN
2. WIRE INSUL DIA, 1.27-2.08 [.050-.082]
3. TONGUE MATL THK, 0.46±0.05 [.018±.002]

5000	ON TAPE, REEL	2-31518-1
1000	LOOSE PIECE	31518
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEM

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

FOR APPLICATION
TOOLING INFORMATION

FOR ORDER ENTRY

PRODUCT INFORMATION CENTER
1-800-522-6752

TOOLING ASSISTANCE CENTER
1-800-722-1111

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
-

VOLTAGE RATING:
-

CIRCULAR MIL AREA:
0.10mm²-0.41mm² [202-810]

STRANDED WIRE

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm [in]

MATERIAL
BODY, CU, SLV, CU PER
ASTM B152

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±-

2 PLC ±0.20 [.008]

3 PLC ±-

4 PLC ±-

ANGLES ±-

FINISH
TIN PLATE
PER MIL-T-10727

DWN
L OLMEDA
23JAN95

CHK
M ELLIS
23JAN95

APVD
S BORTNER
23JAN95

PRODUCT SPEC

APPLICATION SPEC

WEIGHT
-

CUSTOMER DRAWING

AMP Incorporated
Harrisburg, PA 17105-3608

NAME
TERMINAL, RING,
DIAMOND GRIP,
WIRE SIZE, 26-22 AWG

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-31518

SCALE
10:1

SHEET
1 OF 1

REV
E