


SMD Power Inductor


CDRH50D43R



Dimension - [mm]



Land pattern and Schematics - [mm]



Description

- Ferrite drum core construction.
- Magnetically shielded.
- L × W × H: 5.3 × 5.3 × 4.5mm Max.
- Product weight: 0.38g(Ref.)
- Moisture Sensitivity Level: 1
- RoHS compliance.

Environmental Data

- Operating temperature range: -40℃~+105℃ (including coil's self temperature rise)
- Storage temperature range: -40℃~+105℃
- Solder reflow temperature: 260 °C peak.

Packaging


- Carrier tape and reel packaging.
- 13.0" diameter reel
- 1500pcs per reel

Applications

- Ideally used in Slim-type TV , car navigation etc.

SMD Power Inductor

CDRH50D43R



Electrical Characteristics

Part No.	Stamp	Inductance (μH) [Within] ※1	D.C.R.(mΩ) [Within] (at 20℃)	Saturation current (A) ※2		Temperature rise current (A) ※3
				(at 20℃)	(at 105℃)	
CDRH50D43RNP-2R2NC	C	2.2±30%	22±25%	3.60	3.00	3.80
CDRH50D43RNP-3R3NC	D	3.3±30%	25±25%	2.90	2.50	3.50
CDRH50D43RNP-4R7MC	E	4.7±20%	30±25%	2.44	2.08	3.20
CDRH50D43RNP-6R8MC	F	6.8±20%	37±25%	2.12	1.70	2.80
CDRH50D43RNP-100MC	G	10±20%	47±25%	1.75	1.48	2.40
CDRH50D43RNP-150MC	H	15±20%	72±25%	1.44	1.28	1.90
CDRH50D43RNP-220MC	J	22±20%	112±20%	1.16	0.97	1.44
CDRH50D43RNP-330MC	K	33±20%	160±20%	0.96	0.80	1.25
CDRH50D43RNP-470MC	M	47±20%	270±20%	0.78	0.67	0.91
CDRH50D43RNP-680MC	N	68±20%	430±20%	0.65	0.53	0.72
CDRH50D43RNP-101MC	P	100±20%	545±20%	0.54	0.45	0.65
CDRH50D43RNP-151MC	Q	150±20%	775±20%	0.44	0.37	0.51
CDRH50D43RNP-221MC	R	220±20%	975±20%	0.36	0.30	0.49

※1. Measuring condition: at 100kHz.

※2. Saturation current: The value of D.C. current when the inductance decreases to 70% of it's nominal value.

※3. Temperature rise current: The value of D.C. current when the temperature rise is $\Delta t=40^{\circ}\text{C}$ ($T_a=20^{\circ}\text{C}$).













SMD Power Inductor

CDRH50D43R



Saturation Current & Temperature Rise Graph

— L (20°C) — L (105°C) — ΔT




SMD Power Inductor CDRH50D43R




Saturation Current & Temperature Rise Graph

— L (20°C) — L (105°C) — ΔT




Solder Reflow Condition

Heat Endurance



Temperature Chart



Please refer to the sales offices on our website - <http://www.sumida.com>

Hong Kong

Tel.+852-2880-6781
FAX.+852-2565-9600
sales@hk.sumida.com

Saitama(Japan)

Tel.+81-48-691-7300
FAX.+81-48-691-7340
sales@jp.sumida.com

Chicago

Tel.+1-847-545-6700
FAX. +1-847-545-6720
sales@us.sumida.com

Shanghai

Tel.+86-21-5836-3299
FAX.+86-21-5836-3266
shanghai.sales@cn.sumida.com

Seoul

Tel.+82-2-6237-0777
FAX.+82-2-6237-0778
sales@kr.sumida.com

Obernzell

Tel.+49-8591-937-0
FAX. +49-8591-937-103
contact@eu.sumida.com

Shenzhen

Tel.+86-755-8291-0228
FAX.+86-755-8291-0338
shenzhen.sales@cn.sumida.com

Singapore

Tel.+65-6296-3388
FAX.+65-6841-4426
sales@sg.sumida.com

Neumarkt

Tel.+49-9181-4509-110
FAX. +49-9181-4509-310
infocomp@eu.sumida.com

Taipei

Tel.+886-2-8751-2737
FAX.+886-2-8751-2738
sales@tw.sumida.com

San Jose

Tel.+1-408-321-9660
FAX.+1-408-321-9308
sales@us.sumida.com