

**Part Number: 91629-0410****0.50mm Pitch LaneLink™ I/O Jack Screw Receptacle, 4 Lane and 12 Lane, SAS, SATA, Fibre Channel, 8 Circuits**

Image not available

Status:	OBSOLETE
Replacement:	918030410 Foam Gasket, 918030411 Metal Gasket
Series:	91629
Category:	I/O Connectors

Series image - Reference only

Mates With Part(s):

916591020, 916591021, 916591022

Product Environmental Compliance**EU RoHS:** ELV and RoHS Compliant**China RoHS:****REACH SVHC:****Low-Halogen Status:** Not Reviewed**Part Detail****General**

Status	Obsolete
Category	I/O Connectors
Series	91629
Application	Wire-to-Board
Component Type	Receptacle
Product Name	InfiniBand*, LaneLink™
Type	N/A

Physical

Circuits (Loaded)	8
Circuits (maximum)	8
Circuits Detail	8 Differential Pair
Color - Resin	Black
Durability (mating cycles max)	250
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm, 2.40mm, 4.00mm
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	0.50mm
Plating min - Mating	0.102µm
Plating min - Termination	3.048µm
Polarized to Mating Part	Yes
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-20°C to +60°C
Termination Interface: Style	Surface Mount
Wire Size AWG	N/A

Electrical**(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	0.5A
Shielded	Yes
Voltage - Maximum	30V

Solder Process Data

Lead-free Process Capability	Reflow Capable (SMT only)
Process Temperature max. C	260

Material Info

UPC	756054557655
-----	--------------

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)