





REVISIONS				
SYM	ZONE	ECN, ERN NO.	DATE	APPRD.
A		PROPOSAL	SEP.22.08	A.G
B		UPDATED	MAR.11.09	A.G
C		ADD GENERAL TOLERANCES	JAN.06.11	A.G

MATERIAL NOTES:

PLASTIC HOUSING:
HIGH TEMPERATURE LCP
FLAMMABILITY RATING UL94V-0.

CONTACTS:

PHOSPHOR BRONZE

PLATING OPTION 2:

30μ" [0.76 μm] MIN. GOLD ON MATING AREA AND 2 μ" (0.05 μm) GOLD FLASH PLATING ON TERMINATION OVER 50μ" [1.27 μm] MIN. NICKEL UNDER LAYER.

PLATING OPTION 3:

30μ" [0.76 μm] MIN. GOLD ON MATING AREA AND 150-300 μ" (3.81-7.62 μm) MIN. LOW WHISKER MATTE TIN PLATING ON TERMINATION OVER 50μ" [1.27 μm] MIN. NICKEL UNDER LAYER.

PLATING OPTION 5:

15μ" [0.38 μm] MIN. GOLD ON MATING AREA AND 2 μ" (0.05 μm) GOLD FLASH PLATING ON TERMINATION OVER 50μ" [1.27 μm] MIN. NICKEL UNDER LAYER.

PLATING OPTION 6:

15μ" [0.38 μm] MIN. GOLD ON MATING AREA AND 150-300 μ" (3.81-7.62 μm) MIN. LOW WHISKER MATTE TIN PLATING ON TERMINATION OVER 50μ" [1.27 μm] MIN. NICKEL UNDER LAYER.



LUBRICANT OPTION: LUBRICANT CAN BE ADDED ON THE CONTACTS MATING AREA (SEE P/N FOR THE OPTION)

PACKAGING:


TAPE AND REEL.

TEMPERATURE RANGE:

-40°C TO +85°C



ABOVE STANDOFFS



AMPHENOL PART NUMBER CONFIGURATION

UX76 - A 20 - X 0 0 X T

SFP RECEPTACLE

UE76 = RoHS COMPLIANT

CONTACT PLATING

2 = PLATING OPTION 2 (SEE MATERIAL NOTES)
3 = PLATING OPTION 3 (SEE MATERIAL NOTES)
5 = PLATING OPTION 5 (SEE MATERIAL NOTES)
6 = PLATING OPTION 6 (SEE MATERIAL NOTES)

LUBRICANT OPTION

ON MATING AREA

0 = NO
1 = YES



THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

GENERAL TOLERANCES		
DECIMALS	INCH	MILLIMETERS
	X.XX±0.014	X.X± 0.35
	X.XXX±0.010	X.XX± 0.25
ANGLES	X°±1°	X.X°±0.5°



DRAWN	JaneZ	DATE	SEP.22.08
DESIGNED			
CHECKED	J.SI	DATE	SEP.22.08
I. E. APPRD.			
Q. A. APPRD.			
		DATE	SEP.22.08
ENG. REL. NO.			
REF.			
DIMENSIONS ARE IN	INCHES [mm]	CODE ID. NO	03554

Amphenol Canada Corp.


TITLE
SFP+ 20 POSITION HIGH SPEED CONNECTOR RECEPTACLE FIXED BOARD, RIGHT ANGLE SMT
OPTIONAL PLATING AND LUBRICANT ON MATING

DWG	DRAWING NO.	REV.
A	P-UX76-A20-X00XX	c
SCALE	4/1	WT. -----
SURF.	-----	SHEET 1 OF 3


REVISIONS				
SYM	ZONE	ECN, ERN NO.	DATE	APPRD.
A		PROPOSAL	SEP.22.08	A.G
B		UPDATED	MAR.11.09	A.G
C		ADD GENERAL TOLERANCES	JAN.06.11	A.G



SECTION E-E



DETAIL F



DRAWN	JaneZ	DATE	SEP.22.08
DESIGNED			
CHECKED	J.SI	DATE	SEP.22.08

Amphenol Canada Corp.


TITLE
SFP+ 20 POSITION HIGH SPEED CONNECTOR
RECEPTACLE FIXED BOARD, RIGHT ANGLE SMT
OPTIONAL PLATING AND LUBRICANT ON MATING

GENERAL TOLERANCES		DWG. APPRD.	A.G	SEP.22.08
INCH	MILLIMETERS	ENG. REL. NO.		
DECIMALS	X.XX±0.004 X.X±0.10	REF.	X	
	X.XXX±0.002 X.XX±0.05	DIMENSIONS ARE IN	INCHES [mm]	CODE ID. NO. 03554
ANGLES	X°±1° X.X°±0.5°			


DWG	A	DRAWING NO.	P-UX76-A20-X00XX	REV.	C
SCALE	2/1	WT.		SURF.	
				SHEET	2 OF 3

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

REVISIONS				
SYM	ZONE	ECN, ERN NO.	DATE	APPRD.
A		PROPOSAL	SEP.22.08	A.G
B		UPDATED	MAR.11.09	A.G
C		ADD GENERAL TOLERANCES	JAN.06.11	A.G



TOP VIEW OF BOARD



BOTTOM VIEW OF BOARD

RECOMMENDED LAYOUT DETAIL MATING TRANSCEIVER PCB

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

		DRAWN <i>JaneZ</i>		DATE <i>SEP.22.08</i>		Amphenol Canada Corp.			
		DESIGNED							
		CHECKED <i>J.SI</i>		<i>SEP.22.08</i>					
GENERAL TOLERANCES						TITLE SFP+ 20 POSITION HIGH SPEED CONNECTOR RECEPTACLE FIXED BOARD, RIGHT ANGLE SMT OPTIONAL PLATING AND LUBRICANT ON MATING			
	INCH	MILLIMETERS	DWG. APPRD.	<i>A.G</i>	<i>SEP.22.08</i>				
DECIMALS	<i>X.XX±0.004</i>	<i>X.X± 0.10</i>	ENG. REL. NO.						
	<i>X.XXX±0.002</i>	<i>X.XX± 0.05</i>	REF. <i>X</i>						
ANGLES	<i>X'±1°</i>	DIMENSIONS ARE IN			CODE ID. NO.	DWG <i>A</i>	DRAWING NO. <i>P-UX76-A20-X00XX</i>	REV. <i>C</i>	
	<i>X'±0.5°</i>	<i>INCHES [mm]</i>			<i>03554</i>				
						SCALE <i>4:1</i>	WT. _____	SURF. _____	SHEET <i>3</i> OF <i>3</i>