

# Dialight

## 585 Series

### Multi-Chip BASED LED T1 3/4 Midget Flange




#### FEATURES / BENEFITS

- ▲ Low current draw - uses up to 90% less energy than incandescent
- ▲ Long Life - up to 100K hours
- ▲ True non-polarized configurations available
- ▲ No heat generated
- ▲ Mounts directly into industry standard socket
- ▲ Available in 6, 14, and 28 VDC

Dialight's line of based LED lamps is designed to directly replace many popular subminiature and miniature incandescent lamps. The benefits of LED technology over incandescent are significant: They offer long life, are shock resistant, withstand vibration and provide energy conservation.

#### SPECIFICATIONS



CENTER  
CONTACT (+)  
ON POLARIZED  
VERSION

Measurements are typical  
Dimensions are inches [mm]

- ▲ Operating Voltages: 6, 14, and 28 VDC
- ▲ Polarized and non-polarized available
- ▲ Operating temperature: -20°C to +60°C
- ▲ Storage temperature: -30°C to +100°C
- ▲ Replaces incandescent lamp numbers: 327, 328, 330, 345, 349, 350, 376, 377, 380, 381, 382, 385, 387, and 7341.\*

\* See Dialight's Incandescent lamp/based LED cross reference for a complete listing

#### CONSIDERATIONS

- ▲ Since lens caps act as filters for the light emitted from the based LED, it is important to match the emitting color of the LED. If not matched properly, the overall light output may be substantially reduced. Dialight recommends using transparent lenses, which will optimize the light output.
- ▲ If you are unfamiliar with the polarity of the circuit, Dialight recommends using a non-polarized version.
- ▲ Although these lamps can be operated at a lower voltage, which will increase the life, the intensity will be reduced.
- ▲ Operation of the based LED at a higher voltage should not exceed 10% above the recommended voltage.
- ▲ Dialight does not recommend that based LED lamps be used in neon sockets.

Dialight reserves the right to make changes at any time  
in order to supply the best product possible.



#### Dialight Corporation

1501 Route 34 South • Farmingdale, NJ 07727 USA  
Tel: (1) 732-919-3119 • Fax: (1) 732-751-5778 • [www.dialight.com](http://www.dialight.com)

●●●●●●●●●●  
a Roxboro Group Company

MDEL585MF001\_B

## POLARIZED

| Part Number | Color  | Peak Wavelength (nm) | Voltage (VDC) | Current TYP.-(mA) | Intensity TYP.-(mcd) |
|-------------|--------|----------------------|---------------|-------------------|----------------------|
| 585-1211    | Red    | 660                  | 6             | 50                | 67                   |
| 585-1311    | Green  | 565                  | 6             | 46                | 77                   |
| 585-1411    | Yellow | 585                  | 6             | 44                | 22                   |
| 585-1213    | Red    | 660                  | 14            | 30                | 60                   |
| 585-1313    | Green  | 565                  | 14            | 28                | 70                   |
| 585-1413    | Yellow | 585                  | 14            | 30                | 23                   |
| 585-1215    | Red    | 660                  | 28            | 16                | 64                   |
| 585-1315    | Green  | 565                  | 28            | 15                | 75                   |
| 585-1415    | Yellow | 585                  | 28            | 15                | 23                   |

## NON-POLARIZED

| Part Number | Color  | Peak Wavelength (nm) | Voltage (VDC) | Current TYP.-(mA) | Intensity TYP.-(mcd) |
|-------------|--------|----------------------|---------------|-------------------|----------------------|
| 585-1221    | Red    | 660                  | 6             | 75                | 50                   |
| 585-1321    | Green  | 565                  | 6             | 67                | 56                   |
| 585-1421    | Yellow | 585                  | 6             | 73                | 18                   |
| 585-1223    | Red    | 660                  | 14            | 26                | 50                   |
| 585-1323    | Green  | 565                  | 14            | 23                | 56                   |
| 585-1423    | Yellow | 585                  | 14            | 24                | 18                   |
| 585-1225    | Red    | 660                  | 28            | 14                | 56                   |
| 585-1325    | Green  | 565                  | 28            | 13                | 65                   |
| 585-1425    | Yellow | 585                  | 28            | 13                | 20                   |

## Based LEDs SELECTION

With the technological advancements in Light Emitting Diodes (LEDs) brightness can now rival the incandescent lamp when used in similar packages. These advancements have created a new type of product called the based LED - an LED with the functionality of an incandescent bulb.

The following styles are currently available in red, green, yellow, blue and white:

- ▲ T1 3/4 Midget Flange      ▲ T1 3/4 Bi-Pin      ▲ T1 3/4 Wedge (T5)      ▲ T2 Telephone Slide
- ▲ T3 1/4 Miniature Bayonet (BA9s)      ▲ T3 1/4 Miniature Screw (E10)      ▲ T3 1/4 Wedge (T10)      ▲ 15mm SC Bayonet (BA15s)

Dialight's line of based LEDs continues to grow. Please visit our website for more information.  
[www.dialight.com](http://www.dialight.com)



**Dialight Corporation**  
1501 Route 34 South • Farmingdale, NJ 07727 USA  
Tel: (1) 732-919-3119 • Fax: (1) 732-751-5778 • [www.dialight.com](http://www.dialight.com)

●●●●●●●●●●  
a Roxboro Group Company

MDEL585MF001\_B