



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	RELEASED TO PRODUCTION	5/24/01	R.CARRICK
B	CORRECTED ORIENTATION OF CONNECTOR (ECN# 1346)	3/27/03.	T CLARK
C	ECN 3062: REVISED DIM. .910 WAS .930	10/30/07	D.FRISIELLO
D	ECN 3322: UPDATE DWG FORMAT	5/12/08	D.GRIFFIN




RECOMMENDED PANEL OPENING



IEEE-488
FEMALE CONNECTOR



IEEE-488 FEMALE CONNECTOR



NOTES:

HOUSING: ALUMINUM ALLOY DIE CAST, NICKEL PLATED
JACKSCREWS STEEL, BLACK ANODIZED
MOUNTING FLANGE STEEL NICKEL- PLATED
INSULATOR MATERIAL: PBT
CONTACT PLATING 15u INCH GOLD PLATE OVER NICKEL.

PACKAGING:

INDIVIDUALLY PACKAGE IN A POLYBAG

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\begin{aligned} & \geq 12 [305] = +1 [25] / -0 \\ & > 12 [305] \leq 60 [1524] = +2 [51] / -0 \\ & > 60 [1524] \leq 120 [3048] = +4 / -0 \\ & > 120 [3048] \leq 300 [7620] = +6 / -0 \\ & > 300 [7620] = +5\% / -0\% \end{aligned}$ ALL OTHER DIMENSIONAL TOLERANCES: $\begin{aligned} & .X = .3 \\ & .XX = .15 \end{aligned}$		APPROVALS DRAWN BY R.CARRICK 5/24/2001 CHECKED BY ENG 5/24/2001 APPROVED BY D. PARHAM 5/24/2001		DATE 5/24/2001 5/24/2001 5/24/2001		NORTH ANDOVER, MA 01845	
PROJECTION 		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY IEEE-488 GPIB			
		COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION REVERSING ADAPTOR GPIB BULKHEAD F/F			
				SIZE B	FSCM NO. 43321	DWG. NO. CIB24BFR	REV. D
		SCALE: 1:1		CAD FILE: CIB24BFR.SLDDRW		SHEET 1 OF 1	