





REV.	DATE	DESCRIPTION
A	11/21/03	UPDATE DRAWING FORMAT



RECOMMENDED CABLE
STRIPPING DIM'S



CRIMP NOTES:

1. CRIMPED FERRULE
HEX CRIMP SIZE .178"
2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .068"

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex									
8						DRAWN	G.R.S.						11/21/03				
7						CHECKED											
6						ISSUED			PART DESCRIPTION								
5									BNC CRIMP PLUG (FOR BELDEN 1865A, 8218, B1417B, B1164B, RG-B809)								
4	FERRULE	COPPER	NICKEL	1					PART NO.								
3	CONTACT PIN	BRASS	GOLD	1					112521								
2	INSULATOR	DELTRIN	NATURAL	1													
1	BODY	BRASS	NICKEL	1			SHEET	1 OF 1									
	DESCRIPTION	MATERIAL	FINISH	QTY		CAD FILE	C:/112/112521.DWG		DWG. NO.	112521.DWG		REV.	A	SIZE	A	SCALE	NA