






PART NUMBER

10106263-2006001LF




spec ref		*		dr		Peng-Bing Fu	2012/02/06	projection				MM		size		A3	scale		3:2			
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng		Peng-Bing Fu	2012/11/14					ecn no		ELX-DG-013143-1		rel level		Released				
ASME Y14.5				chr		Shao-Qi Kuang	2012/11/15															
				appr		Pei-Ming Zheng	2012/11/15															
								product family		PwrBlade+												
surface			linear		0.X		±0.5				title		IHP + 24S + IHP		dwg no		10106263-2006001		rev		B	
					0.XX		±0.25															
					0.XXX		±0.10															
ASME Y14.5		angular		0°		±2°		www.fci.com		cat. no.		Product - Customer Drw		sheet 1 of 3								



Copyright FCI.

PRODUCT NO.	ROW S	POWER		SIGNAL						POWER	
		E1	P1	1	2	3	4	5	6	P2	E2
10106263-2006001LF	D C B A		HE	SD	SD	SD	SD	SD	SD	HE	



CODE	DESCRIPTION
HA	METAL HOLD DOWN
HE	STD HIGH POWER CONTACT (3.05)
LB	LMFB SIGNAL CONTACT, ROW B (3.05)
SA	STD SIGNAL CONTACT, ROW A (3.05)
SB	STD SIGNAL CONTACT, ROW B (3.05)
SC	STD SIGNAL CONTACT, ROW C (3.05)
SD	STD SIGNAL CONTACT, ROW D (3.05)

dr	Peng-Bing Fu	2012/02/06	projection	MM	size	A3	scale	3:2	
eng	Peng-Bing Fu	2012/11/14			ecn no	ELX-DG-013143-1			
chr	Shao-Qi Kuang	2012/11/15			rel level			Released	
appr	Pei-Ming Zheng	2012/11/15	product family		PwrBlade+				
FCi			title		IHP + 24S + IHP		dwg no		rev
			RA PF HEADER		10106263-2006001				B
www.fci.com			cat. no.		Product - Customer Drw			sheet 2 of 3	

A

B

C

D

A

B

C

D

NOTES:

- 1) "FCI", PART NUMBER AND DATE CODE TO BE MARKED ON THIS SURFACE.
THE P/N CAN BE OMITTED IF THERE IS NOT ENOUGH SPACE ON THIS SURFACE.
- 2) MATERIALS:
-HOUSING - GLASS FILLED WITH HIGH TEMP THERMOPLASTIC, UL94V-0.
-SIGNAL CONTACT - COPPER ALLOY.
-POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY.
- 3) PLATING SPECIFICATION REFER TO FCI 10116351
- 4) DENOTES CONNECTOR KEEP OUT ZONE.
- 5) DATUM AND BASIC DIMENIONS WERE ESTABLISHED BY CUSTOMER.
- 6) ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.
- 7) 1.15 ± 0.025 MM DRILLED HOLE PLATED WITH 0.00762MM MIN Sn
OVER 0.0254-0.0762MM Cu PLATING TO ACHIEVE A 1.02 ± 0.07 MM HOLE.
- 8) PRODUCT SPECIFICATION REFER TO FCI GS-12-658.
APPLICATION SPECIFICATION REFER TO FCI GS-20-141.
PRODUCT PACKAGED IN TRAYS, REFER TO FCI GS-14-1502.
- B

9) A

B

 SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION



Copyright FCI.

dr	Peng-Bing Fu	2012/02/06	projection	MM	size	A3	scale	3:2			
eng	Peng-Bing Fu	2012/11/14			ecn no	ELX-DG-013143-1					
chr	Shao-Qi Kuang	2012/11/15			rel level	Released					
appr	Pei-Ming Zheng	2012/11/15	product family		PwrBlade+						
FCi www.fci.com			title		IHP + 24S + IHP RA PF HEADER		dwg no	10106263-2006001	rev	B	
cat. no.			Product - Customer Drw				sheet 3 of 3				