





LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AF	50		A3	REVISED PER ECR-07-018125	03AUG07	JR RL

SUGGESTED MATING TAB





- 1 - MATL: 1/2H BRASS OR NICKEL PL STEEL.
 - 2 - NO BURRS PERMISSIBLE AT HOLE.
 - 3 - MUST BE FLAT WITHIN 0.076 [.003] OVER THIS LENGTH.
 - 4 - TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMP. IS OVER 225°F.
 - 5 - HOLE MUST BE SYMMETRICAL ABOUT TAB Q WITHIN 0.076 [.003]
- * TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.



SCALE 10:1

- 1 CONTINUOUS STRIP ON REELS.
- 2 ACCEPTS #22-#18 AWG WIRE SIZES. WIRE CRIMP: .080 F TYPE
- 3 INSULATION RANGE IS 1.52-2.79 [.060-.110] DIA. INSULATION CRIMP: .130 F TYPE



SCALE 10:1

0.00381[.000150] MIN SILVER PLATE	1217378-3
0.002032[.000080] MIN TIN PLATE	1217378-2
-	1217378-1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 30MAR00		 Tyco Electronics Corporation Harrisburg, PA 17105-3608					
		CHK MS FEHER 30MAR00							
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE, POSITIVE LOCK, 6.35 [.250] SERIES —					
		APVD —							
		PRODUCT SPEC —							
		APPLICATION SPEC 114-2074							
		SIZE A2							
MATERIAL H06 BRASS		FINISH SEE TABLE		CAGE CODE 00779		DRAWING NO C-1217378		RESTRICTED TO —	
		WEIGHT —							
CUSTOMER DRAWING				SCALE 5:1		SHEET 1 OF 1		REV A3	