

FILE NO.	B - CD - 201 - 01
----------	-------------------


NOTES:

- ① MAT'L: COPPER (STOCK TKN. $\frac{.031}{.79}$)
PLATING: ELECTRO-TIN (.0003 MIN.)
② INSULATION: MOLDED PVC (BLUE)

STUD SIZES: (α , .005)

02 =	.094
04 =	.119
06 =	.146
08 =	.173
10 =	.198
14 =	.265
56 =	.328
38 =	.390

"UL" LISTING #E32244
"CSA" LISTING #18689



MWID = MAXIMUM WIRE
 INSULATION DIAMETER
 WIRE SIZE: 16-14 AWG
 1.0-2.5 MM²

ALL DIMENSIONS = $\frac{\text{INCHES}}{\text{MM}}$

PART NUMBER	"W" ±.010	"C" MIN.	"L" MAX.	AVAILABLE STUD SIZES		
B-218 -	$\frac{.534}{13.56}$	$\frac{.554}{14.07}$	$\frac{1.311}{33.30}$	10X, 14X, 56X, 38X		
B-223 -	$\frac{.250}{6.35}$	$\frac{.209}{5.31}$	$\frac{.835}{21.21}$	02X, 04X, 06X, 08X		
B-225 -	$\frac{.467}{11.86}$	$\frac{.388}{9.86}$	$\frac{1.112}{28.24}$	10X, 14X, 56X		
B-237 -	$\frac{.312}{7.92}$	$\frac{.285}{7.24}$	$\frac{.926}{23.52}$	04X, 06X, 08X, 10X		
B-239 -	$\frac{.342}{8.69}$	$\frac{.310}{7.87}$	$\frac{.971}{24.66}$	04X, 06X, 08X, 10X		
DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED		REFERENCE	SCALE: NTS	DATE	TITLE:	
FRAC.	DEC.	ANG.			RING TONGUE TERMINAL INSULKRIMP 200 SERIES	
±	±	±	CHKD. BY: GZ	10-25-84	DWG. NO. A CUSTOMER DWG.	
			APPRD. BY:		ETCmolex INCORPORATED	