

TC74LVX174F, TC74LVX174FN, TC74LVX174FT

HEX D-TYPE FLIP FLOP WITH CLEAR

The TC74LVX174 is a high speed CMOS HEX D-FLIP FLOP fabricated with silicon gate C²MOS technology.

Designed for use in 3.3 Volt systems, they achieve high speed operation while maintaining the CMOS low power dissipation. This device is suitable for low voltage and battery operated systems.

Information signals applied to D inputs are transferred to the Q output on the positivegoing edge of the clock pulse.

When the $\overline{\text{CLR}}$ input is held low, the Q output are in the low logic level independent of the other inputs.


An input protection circuit ensures that 0 to 7V can be applied to the input pins without regard to the supply voltage. This device can be used to interface 5V to 3V systems and two supply systems such as battery back up. This circuit prevents device destruction due to mismatched supply and input voltages.

FEATURES

- High speed : $f_{\text{MAX}} = 180\text{MHz}$ (Typ.) ($V_{\text{CC}} = 3\text{V}$)
- Low power dissipation : $I_{\text{CC}} = 4\mu\text{A}$ (Max.) ($T_a = 25^\circ\text{C}$)
- Input voltage level : $V_{\text{IL}} = 0.8\text{V}$ (Max.) ($V_{\text{CC}} = 3\text{V}$)
 $V_{\text{IH}} = 2.0\text{V}$ (min.) ($V_{\text{CC}} = 3\text{V}$)
- Power down protection is provided on all inputs.
- Balanced propagation delays : $t_{\text{pLH}} \approx t_{\text{pHL}}$
- Low noise : $V_{\text{OLP}} = 0.5\text{V}$ (Max.)
- Pin and function compatible with 74HC174


(Note) The JEDEC SOP (FN) is not available in Japan.

TC74LVX174F




SOP16-P-300-1.27

TC74LVX174FN



SOL16-P-150-1.27

TC74LVX174FT




TSSOP16-P-0044-0.65

Weight

SOP16-P-300-1.27	: 0.18g (Typ.)
SOL16-P-150-1.27	: 0.12g (Typ.)
TSSOP16-P-0044-0.65	: 0.06g (Typ.)

PIN ASSIGNMENT




TRUTH TABLE


INPUTS			OUTPUTS	FUNCTION
CLR	D	CK	Q	
L	X	X	L	CLEAR
H	L		L	—
H	H		H	—
H	X		Qn	NO CHANGE

X : Don't Care

IEC LOGIC SYMBOL



SYSTEM DIAGRAM



MAXIMUM RATINGS

PARAMETER	SYMBOL	RATING	UNIT
Supply Voltage Range	V_{CC}	$-0.5 \sim 7.0$	V
DC Input Voltage	V_{IN}	$-0.5 \sim 7.0$	V
DC Output Voltage	V_{OUT}	$-0.5 \sim V_{CC} + 0.5$	V
Input Diode Current	I_{IK}	-20	mA
Output Diode Current	I_{OK}	± 20	mA
DC Output Current	I_{OUT}	± 25	mA
DC V_{CC} /Ground Current	I_{CC}	± 50	mA
Power Dissipation	P_D	180	mW
Storage Temperature	T_{stg}	$-65 \sim 150$	°C

RECOMMENDED OPERATING CONDITIONS

PARAMETER	SYMBOL	RATING	UNIT
Supply Voltage	V_{CC}	2.0~3.6	V
Input Voltage	V_{IN}	0~5.5	V
Output Voltage	V_{OUT}	0~ V_{CC}	V
Operating Temperature	T_{opr}	$-40 \sim 85$	°C
Input Rise And Fall Time	dt/dv	0~100	ns/V

ELECTRICAL CHARACTERISTICS

DC characteristics

PARAMETER		SYM-BOL	TEST CONDITION		V_{CC} (V)	Ta = 25°C			Ta = -40~85°C		UNIT
						MIN.	TYP.	MAX.	MIN.	MAX.	
Input Voltage	"H" Level	V_{IH}			2.0	1.5	—	—	1.5	—	V
					3.0	2.0	—	—	2.0	—	
					3.6	2.4	—	—	2.4	—	
	"L" Level	V_{IL}			2.0	—	—	0.5	—	0.5	
					3.0	—	—	0.8	—	0.8	
					3.6	—	—	0.8	—	0.8	
Output Voltage	"H" Level	V_{OH}	$V_{IN} = V_{IH}$ or V_{IL}	$I_{OH} = -50 \mu A$	2.0	1.9	2.0	—	1.9	—	V
				$I_{OH} = -50 \mu A$	3.0	2.9	3.0	—	2.9	—	
				$I_{OH} = -4mA$	3.0	2.58	—	—	2.48	—	
	"L" Level	V_{OL}	$V_{IN} = V_{IH}$ or V_{IL}	$I_{OL} = 50 \mu A$	2.0	—	0.0	0.1	—	0.1	
				$I_{OL} = 50 \mu A$	3.0	—	0.0	0.1	—	0.1	
				$I_{OL} = 4mA$	3.0	—	—	0.36	—	0.44	
Input Leakage Current	I_{IN}		$V_{IN} = 5.5V$ or GND		3.6	—	—	± 0.1	—	± 1.0	μA
Quiescent Supply Current	I_{CC}		$V_{IN} = V_{CC}$ or GND		3.6	—	—	4.0	—	40.0	μA

TIMING REQUIREMENTS (Input $t_r = t_f = 3\text{ns}$)

PARAMETER	SYM-BOL	TEST CONDITION	Ta = 25°C		Ta = -40~85°C	UNIT
			V _{CC} (V)	LIMIT		
Minimum Pulse Width (CK)	t _W (L)		2.7	6.5	7.5	ns
	t _W (H)		3.3 ± 0.3	5.0	5.0	
Minimum Pulse Width (CLR)	t _W (L)		2.7	6.5	7.5	ns
			3.3 ± 0.3	5.0	5.0	
Minimum Set-up Time	t _s		2.7	7.5	8.5	ns
			3.3 ± 0.3	5.0	6.0	
Minimum Hold Time	t _h		2.7	0.0	0.0	ns
			3.3 ± 0.3	0.0	0.0	
Minimum Removal Time (CLR)	t _{rem}		2.7	4.5	4.5	ns
			3.3 ± 0.3	3.0	3.0	

AC characteristics (Input $t_r = t_f = 3\text{ns}$)

PARAMETER	SYM-BOL	TEST CONDITION	Ta = 25°C			Ta = -40~85°C		UNIT
			V _{CC} (V)	C _L (pF)	MIN.	TYP.	MAX.	
Propagation Delay Time (CK-Q)	t _{pLH} t _{pHL}		2.7	15	—	7.6	14.5	ns
				50	—	10.1	18.0	
			3.3 ± 0.3	15	—	5.9	9.3	
				50	—	8.4	12.8	
Propagation Delay Time (CLR-Q)	t _{pHL}		2.7	15	—	7.9	15.0	ns
				50	—	10.4	18.5	
			3.3 ± 0.3	15	—	6.2	9.7	
				50	—	8.7	13.2	
Maximum Clock Frequency	f _{MAX}		2.7	15	65	130	—	MHz
				50	45	60	—	
			3.3 ± 0.3	15	115	180	—	
				50	65	95	—	
Output To Output Skew	t _{osLH} t _{osHL}	(Note 1)	2.7	50	—	—	1.5	ns
			3.3 ± 0.3	50	—	—	1.5	
Input Capacitance	C _{IN}	(Note 2)			—	4	10	pF
Power Dissipation Capacitance	C _{pD}	(Note 3)			—	29	—	pF

(Note 1) Parameter guaranteed by design.

$$(t_{osLH} = |t_{pLHm} - t_{pLHn}|, t_{osHL} = |t_{pHLm} - t_{pHLn}|)$$

(Note 2) Parameter guaranteed by design.

(Note 3) C_{pD} is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption.

Average operating current can be obtained by the equation :

$$I_{CC}(\text{opr.}) = C_{pD} \cdot V_{CC} \cdot f_{IN} + I_{CC}/6 \text{ (per F/F)}$$


And the total C_{pD} when n pcs. of F/F operate can be gained by the following equation :

$$C_{pD}(\text{total}) = 19 + 10 \cdot n$$

Noise characteristics (Ta = 25°C, Input tr = tf = 3ns, CL = 50pF)


PARAMETER	SYMBOL	TEST CONDITION	VCC (V)	TYP.	LIMIT	UNIT
Quiet Output Maximum Dynamic VOL	VOLP		3.3	0.3	0.5	V
Quiet Output Minimum Dynamic VOL	VOLV		3.3	-0.3	-0.5	V
Minimum High Level Dynamic Input Voltage	VIHD		3.3	—	2.0	V
Maximum Low Level Dynamic Input Voltage	VILD		3.3	—	0.8	V

INPUT EQUIVALENT CIRCUIT



PACKAGE DIMENSIONS
SOP16-P-300-1.27

Unit : mm




Weight : 0.18g (Typ.)

PACKAGE DIMENSIONS
SOL16-P-150-1.27

Unit : mm




(Note) This package is not available in Japan.



Weight : 0.12g (Typ.)

PACKAGE DIMENSIONS
TSSOP16-P-0044-0.65

Unit : mm



Weight : 0.06g (Typ.)

RESTRICTIONS ON PRODUCT USE

000707EBA

- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property. In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc..
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- The products described in this document are subject to the foreign exchange and foreign trade laws.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA CORPORATION for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of TOSHIBA CORPORATION or others.
- The information contained herein is subject to change without notice.