





© COPYRIGHT

REVISIONS

P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
			W2	REVISED PER ECO-11-005140	31MAR11	HMR



- 1 POINT OF MEASUREMENT FOR PLATING THICKNESS.
2 CUSTOMERS APPLICATOR CUT-OFF DIMENSION.
3 .00030 GOLD OVER .00050 NICKEL.
4 .00015 GOLD OVER .00050 NICKEL.
5 .000100-.000200 BRIGHT TIN-LEAD OVER .00050 NICKEL.
6 .00050 GOLD OVER .00050 NICKEL.
7 .00010 GOLD OVER .00050 NICKEL.
8 OBSOLETE PART NO
9 SUPERSEDED BY 87022-9
10 SUPERSEDED BY 3-104246-4
11 SUPERSEDED BY 4-87022-1
12 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
13 OBSOLETE
14 SUPERSEDED

SUPERSEDE BY 104842-2

SEE 87078 FOR
ADDITIONAL PART NO'S.

.100	.793	.515	.278	3	9	9	.100	.863	.585		3	2	8	9
	.660	.165	.495	5	9	8	100	.663	.385	.278	3	2	8	8
	.835	.165	.670	5	9	8	.280	.815	.255	.560	4	2	8	7
.100	1.238	.960	.278	6	9	8	.100	.533	.255	.278	4	2	8	6
.100	.828	.550	.278	6	9	8	.100	.533	.255	.278	3	2	8	5
	.650	.255	.395	5	9	8	.100	.608	.330	.278	3	2	8	4
	.728	.450	.278	5	9	8	.335	.835	.165	.670	4	2	8	3
.100	.728	.450		4	9	8	.100	.562	.284	.278	6	2	8	2
	.863	.585		5	8	8		.928	.650		4	2	8	1
	.663	.385		5	8	8		.828	.550		4	2	8	0
.100	.863	.585		4	8	8		.628	.350		4	1		9
.100	.663	.385		4	8	8		.928	.650		3	1	8	8
	1.438	1.160		5	8	8		.828	.550		3	1		7
.100	1.438	1.160		4	8	8		.628	.350		3	1	8	6
	1.238	.960		5	8	8	.100	.443	.165	.278	7	1	9	5
.100	1.238	.960	.278	4	8	8		.437	.227	.210	5	7	8	4
.200	.580	.165	.395	3	8	8	.100	.562	.284	.278	3	7	8	3
.100	1.438	1.160	.278	3	8	8	.100	.443	.165		6	1		1
	1.238	.960		3	7	8		.443	.165		5	1		0
	.738	.450		3	7	8	.100	.443	.165		4			9
	.928	.650		6	7	8		.688	.410		6	8		8
	.628	.350	.278	6	7	8		.508	.230		6	8		7
	1.056	.738	.318	3	6	8	.100	1.016	.738		6	8		5
	.508	.230	.278	4	6	8					5	8		4
.100	.437	.227	.210	4	6		.100				4	8		3
	1.065	.165	.300	5	4	8	.100	1.016	.738		3			2
	.483	.165	.318	5	4	87022-3	.100	.443	.165	.278	3	87022-1		
ID	C	IB	IA	FINISH	PART NO.		ID	C	IB	IA	FINISH	PART NO.		

UNLESS OTHERWISE
SPECIFIED DIMENSIONS
ARE IN INCHES.TOLERANCES ON:
DECIMALS $\pm .005$
ANGLES $\pm$

MATERIAL

PHOS. BRONZE

FINISH

SEE TABLE

CONTRACT NO

DR

CHK

APPD

APPD

DSGN APPD

OTHER APPD

ETE TE Connectivity

NAME
POST, MOD II, .025 SQ,
UNINSULATEDSIZE
C
FSCM NO
00779
DRAWING NO
87022SCALE

SHEET 1 OF 1

CUSTOMER DRAWING