



Copyright FCI.













NOTES:

1. MATERIAL
HOUSING: LCP UL 94V-0
TERMINAL: NICKEL COPPER
2. PLATING
AS SHOWN IN TABLE.
3. SEE GS-12-547 FOR PRODUCT SPEC.
4. SEE GS-15-551 AND GS-14-816 FOR THE DETAILS OF PACKAGING.
PRODUCT WILL BE PACKED IN ACCORDANCE TO GLOBAL PROCEDURE GS-14-920.
5. PACKAGING OPTION 2: "NOT ALL SIZES AVAILABLE; CHECK WITH FACTORY".
6. THIS PRODUCT MEETS THE EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
7. THE HOUSING WITH WITHSTAND EXPOSURE UP TO 260° PEAK TEMPERATURE FOR 30 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR REFLOW OVEN.
8. PLATING OPTION "4" IS LEADFREE ALTERNATIVE FOR OPTION "0",
AND OPTION "6" IS LEADFREE ALTERNATIVE FOR OPTION "1".
9. A  SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.
10. THIS PARTNUMBER ONLY CATER FOR SPECIAL CUSTOMER REQUIREMENT OF COPLANARITY OF 0.1 FOR ALL POSITION.

REV F - 2006-04-17

10069524- AA B C D E F F

AA	POSITION
04	2X20
06	2X30
08	2X40
10	2X50
12	2X60
14	2X70
16	2X80
18	2X90
20	2X100

B	FOR PLUG, SEE DWG. NO. 10069525			
COMBINATION OF MATED HEIGHT	Plug 1	Plug 2	Plug 3	Plug 4
Recep 1				
Recep 2				
Recep 3				

E	PACKAGING
0	TUBE WITHOUT METAL CAP
2	T&R WITH METAL CAP
9	TUBE WITH METAL CAP

D	POLARIZATION PEG	HOLD DOWN
0	YES	NO
2	NO	NO

C	PLATING ON CONTACT AREA	FF
0	GOLD 0.2um MIN / TIN LEAD NICKEL UNDERPLATE OVERALL 1.27um MIN	NONE
1	GOLD FLASH (0.1um MIN) OVER PALLADIUM-NICKEL 0.76um MIN / TIN LEAD NICKEL UNDERPLATE OVERALL 1.27um MIN	NONE
4	GOLD 0.2um MIN / PURE TIN 2um MIN (LEAD FREE) NICKEL UNDERPLATE OVERALL 1.27um MIN	LF
5	GOLD 0.38um MIN / PURE TIN 2um MIN (LEAD FREE) NICKEL UNDERPLATE OVERALL 1.27um MIN	LF
6	GOLD FLASH (0.1um MIN) OVER PALLADIUM-NICKEL 0.76um MIN / PURE TIN 2um MIN (LEAD FREE) NICKEL UNDERPLATE OVERALL 1.27um MIN	LF
9	GOLD 0.2um MIN / GOLD 0.05um MIN (LEAD FREE) NICKEL UNDERPLATE OVERALL 1.27um MIN	LF




rev	ecn no	dr	date
A	S06-0286	MCH	2006-08-25
B	S06-0316	MCH	2006-09-25
C	S09-0326	MCH	2009-10-21
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		MM 			
			TOLERANCES UNLESS		OTHERWISE SPECIFIED							
Dr	M. Cheong	2006-08-25	ANGULAR	LINEAR	0.X	±0.20	size A3	Scale 17:1				
Eng	M. Cheong	2006-08-25			0.XX	±0.15						
Chr	M. Cheong	2009-10-21	0°	±2°	0.XXX	±0.10	ECN		ELX-N-20407			
Appr	Joey Ng	2009-10-21	Product family				BERGSTAK		Spec ref			
			title BERGSTAK 0.8MM RECEPTACLE ASSY				dwg no 10069524		Rev.			
									D			
			catalog no				-		CUSTOMER		sheet 1 of 6	



Copyright FCI.

PRODUCT NO.	NUMBER OF POSITIONS	DIMENSION		
		A	B	C
10069524-041***	2X20	15.2	21.8	20.2
10069524-061***	2X30	23.2	29.8	28.2
10069524-081***	2X40	31.2	37.8	36.2
10069524-101***	2X50	39.2	45.8	44.2
10069524-121***	2X60	47.2	53.8	52.2
10069524-141***	2X70	55.2	61.8	60.2
10069524-161***	2X80	63.2	69.8	68.2
10069524-181***	2X90	71.2	77.8	76.2
10069524-201***	2X100	79.2	85.8	84.2



RECEPTACLE 1



title BERGSTAK 0.8MM
RECEPTACLE ASSY
catalog no

dwg no

10069524

Rev.
D


CUSTOMER

sheet 2 of 6




Copyright FCI.


RECEPTACLE 1



RECOMMENDED PCB LAYOUT WITHOUT PEGS AND HOLDDOWN



RECOMMENDED PCB LAYOUT WITH PEGS
FOR NO. OF POSITION 2X20, 2X30, 2X40, 2X50, 2X60



RECOMMENDED PCB LAYOUT WITH PEGS
FOR NO. OF POSITION 2X70, 2X80, 2X90, 2X100



title BERGSTAK 0.8MM
RECEPTACLE ASSY
catalog no

dwg no 10069524




Rev. D

CUSTOMER sheet 3 of 6



Copyright FCI.

PRODUCT NO.	NUMBER OF POSITIONS	DIMENSION		
		A	B	C
10069524-042***	2X20	15.2	21.8	20.2
10069524-062***	2X30	23.2	29.8	28.2
10069524-082***	2X40	31.2	37.8	36.2
10069524-102***	2X50	39.2	45.8	44.2
10069524-122***	2X60	47.2	53.8	52.2
10069524-142***	2X70	55.2	61.8	60.2
10069524-162***	2X80	63.2	69.8	68.2
10069524-182***	2X90	71.2	77.8	76.2
10069524-202***	2X100	79.2	85.8	84.2







RECEPTACLE 2	
dwg no	10069524
Rev.	D
CUSTOMER	sheet 4 of 6

FCI	title	BERGSTAK 0.8MM	-	CUSTOMER	sheet 4 of 6
	catalog no	RECEPTACLE ASSY			



Copyright FCI.

PRODUCT NO.	NUMBER OF POSITIONS	DIMENSION		
		A	B	C
10069524-043***	2X20	15.2	21.8	20.2
10069524-063***	2X30	23.2	29.8	28.2
10069524-083***	2X40	31.2	37.8	36.2
10069524-103***	2X50	39.2	45.8	44.2
10069524-123***	2X60	47.2	53.8	52.2
10069524-143***	2X70	55.2	61.8	60.2
10069524-163***	2X80	63.2	69.8	68.2
10069524-183***	2X90	71.2	77.8	76.2
10069524-203***	2X100	79.2	85.8	84.2




RECEPTACLE 3

	title		BERGSTAK 0.8MM		dwg no	10069524		Rev.
			RECEPTACLE ASSY					D
	catalog no		-		CUSTOMER		sheet 5 of 6	




Copyright FCI.


RECEPTACLE 2 & 3



RECOMMENDED PCB LAYOUT WITHOUT PEGS AND HOLDDOWN



RECOMMENDED PCB LAYOUT WITH PEGS
FOR NO. OF POSITION 2X20, 2X30, 2X40, 2X50, 2X60



RECOMMENDED PCB LAYOUT WITH PEGS
FOR NO. OF POSITION 2X70, 2X80, 2X90, 2X100



title BERGSTAK 0.8MM
RECEPTACLE ASSY
catalog no

dwg no 10069524

Rev.
D

CUSTOMER sheet 6 of 6