


TCJ Series



Tantalum Solid Electrolytic Chip Capacitors with Conductive Polymer Electrode



- Conductive polymer electrode reduces ignition failure mode
- Lower ESR
- 3x reflow 260°C compatible
- CV range: 0.68-220µF / 2.5-50V
- 13 case sizes available




Elektro Award 2010



LEAD-FREE
LEAD-FREE COMPATIBLE
COMPONENT



RoHS
COMPLIANT



For part marking see page 131

CASE DIMENSIONS: millimeters (inches)

Code	EIA Code	EIA Metric	L±0.20 (0.008)	W+0.20 (0.008) -0.10 (0.004)	H+0.20 (0.008) -0.10 (0.004)	Wt±0.20 (0.008)	A+0.30 (0.012) -0.20 (0.008)	S Min.
A	1206	3216-18	3.20 (0.126)	1.60 (0.063)	1.60 (0.063)	1.20 (0.047)	0.80 (0.031)	1.10 (0.043)
B	1210	3528-21	3.50 (0.138)	2.80 (0.110)	1.90 (0.075)	2.20 (0.087)	0.80 (0.031)	1.40 (0.055)
C	2312	6032-28	6.00 (0.236)	3.20 (0.126)	2.60 (0.102)	2.20 (0.087)	1.30 (0.051)	2.90 (0.114)
D	2917	7343-31	7.30 (0.287)	4.30 (0.169)	2.90 (0.114)	2.40 (0.094)	1.30 (0.051)	4.40 (0.173)
G	1206	3216-15	3.20 (0.126)	1.60 (0.063)	1.50 (0.059) max	1.20 (0.047)	0.80 (0.031)	1.10 (0.043)
H	1210	3528-15	3.50 (0.138)	2.80 (0.110)	1.50 (0.059) max	2.20 (0.087)	0.80 (0.031)	1.40 (0.055)
K	1206	3216-10	3.20 (0.126)	1.60 (0.063)	1.00 (0.039) max	1.20 (0.047)	0.80 (0.031)	1.10 (0.043)
P	0805	2012-15	2.05 (0.081)	1.35 (0.050)	1.50 (0.059) max	1.0±0.1 (0.039±0.004)	0.50 (0.020)	0.85 (0.033)
R	0805	2012-12	2.05 (0.081)	1.30 (0.051)	1.20 (0.047) max	1.0±0.1 (0.039±0.004)	0.50 (0.020)	0.85 (0.033)
S	1206	3216-12	3.20 (0.126)	1.60 (0.063)	1.20 (0.047) max	1.20 (0.047)	0.80 (0.031)	1.10 (0.043)
T	1210	3528-12	3.50 (0.138)	2.80 (0.110)	1.20 (0.047) max	2.20 (0.087)	0.80 (0.031)	1.40 (0.055)
W	2312	6032-15	6.00 (0.236)	3.20 (0.126)	1.50 (0.059) max	2.20 (0.087)	1.30 (0.051)	2.90 (0.114)
Y	2917	7343-20	7.30 (0.287)	4.30 (0.169)	2.00 (0.079) max	2.40 (0.094)	1.30 (0.051)	4.40 (0.173)

Wt dimension applies to the termination width for A dimensional area only.

HOW TO ORDER

TCJ

Type

A

Case Size
See table above

226

Capacitance Code
pF code: 1st two digits represent significant figures, 3rd digit represents multiplier (number of zeros to follow)

M

Tolerance
M=±20%

004

Rated DC Voltage
002=2.5Vdc
004=4Vdc
006=6.3Vdc
010=10Vdc
016=16Vdc
020=20Vdc
025=25Vdc
035=35Vdc
050=50Vdc

R

Packaging
R = Lead Free 7" Reel
S = Lead Free 13" Reel

0300

ESR in mΩ

TECHNICAL SPECIFICATIONS

Technical Data:

All technical data relate to an ambient temperature of +25°C

Capacitance Range: 0.68 µF to 220 µF

Capacitance Tolerance: ±20%

Leakage Current DCL: 0.1CV

Rated Voltage (V _R)	≤ +85°C:	2.5	4	6.3	10	16	16	20	25	35	50
Category Voltage (V _C)	≤ +105°C:						12.8	16	20	28	40
Category Voltage (V _C)	≤ +125°C:	1.7	2.7	4	7	10					
Surge Voltage (V _S)	≤ +85°C:	3.3	5.2	8	13	20	20.8	26	33	46	65
Surge Voltage (V _S)	≤ +105°C:						16	20	25	35	50
Surge Voltage (V _S)	≤ +125°C:	2.2	3.4	5	8	13					

Temperature Range: -55°C to +125°C, -55°C to +105°C

Reliability: 1% per 1000 hours at 85°C, V_R with 0.1Ω/V series impedance, 60% confidence level



TCJ Series



Tantalum Solid Electrolytic Chip Capacitors with Conductive Polymer Electrode

CAPACITANCE AND RATED VOLTAGE, VR (VOLTAGE CODE) RANGE (LETTER DENOTES CASE SIZE)

125°C RATED PARTS

Capacitance		Rated Voltage DC (V _R) to 85°C				
μF	Code	2.5V (e)	4V (G)	6.3V (J)	10V (A)	16V (C)
1.0	105					
4.7	475				K(500), R(500)	
6.8	685					A(200)
10	106			A(300), R(500)	A(300)	A(200), B(200) T(150,200)
15	156		A(300)	A(300)	A(200)	B(150)
22	226		A(300)	A(300), K(400) S(400), T(150)	B(300), T(150)	B(150)
33	336		A(300)	A(200) B(70,200) T(150)	B(70,200) C(100) T(70,150)	
47	476		A(200), T(80)	A(200), B(70) K(400), P(500) T(80,120)	B(70), C(100)	
68	686	A(250)	A(250), B(70) T(80)	B(55,70) C(100), W(70)		
100	107	A(200), B(70)	A(200), B(70) G(300), T(150)	B(45,69,70)		
150	157	B(70)	B(70)	A(200), B(45,69,70) H(200), W(40,70) Y(25,40)*		
220	227		B(45,70)	B(70,200)		

105°C RATED PARTS

Capacitance		Rated Voltage DC (V _R) to 85°C				
μF	Code	16V (C)	20V (D)	25V (E)	35V (V)	50V (T)
0.68	684					B(300)
1.0	105			P(500)		B(300)
1.5	155					B(300), C(300)
2.2	225					C(300)
3.3	335					C(200)
4.7	475					C(200)
6.8	685					C(200), D(120)
10	106				B(200), C(200), Y(70)	D(120)
15	156			B(100)		
22	226		Y(70)	B(100), Y(70)		
33	336	Y(70)	Y(70)	Y(100)		
47	476	Y(70)	Y(70)			
68	686					

Available Ratings, (ESR ratings in mOhms in brackets)

Engineering samples - please contact manufacturer

*Codes under development – subject to change

Note: Voltage ratings are minimum values. AVX reserves the right to supply higher ratings in the same case size, to the same reliability standards.

TCJ Series



Tantalum Solid Electrolytic Chip Capacitors with Conductive Polymer Electrode

RATINGS & PART NUMBER REFERENCE

AVX Part No.	Case Size	Capacitance (µF)	Rated Voltage (V)	DCL (µA) Max.	DF % Max.	ESR Max. (mΩ) @100kHz	MSL	100kHz RMS Current (mA)			100kHz RMS Voltage (mV)			
								25°C	85°C	125°C	25°C	85°C	125°C	
2.5 Volt @ 85°C (1.7 Volt @ 125°C)														
TCJA686M002#0250	A	68	2.5	17.0	6	250	3	548	493	219	137	123	55	
TCJA107M002#0200	A	100	2.5	25.0	6	200	3	612	551	245	122	110	49	
TCJB107M002#0070	B	100	2.5	25.0	6	70	3	1102	992	441	77	69	31	
TCJB157M002#0070	B	150	2.5	37.5	6	70	3	1102	992	441	77	69	31	
4 Volt @ 85°C (2.7 Volt @ 125°C)														
TCJA156M004#0300	A	15	4	6.0	6	300	3	500	450	200	150	135	60	
TCJA226M004#0300	A	22	4	8.8	6	300	3	500	450	200	150	135	60	
TCJA336M004#0300	A	33	4	13.2	6	300	3	500	450	200	150	135	60	
TCJA476M004#0200	A	47	4	18.8	6	200	3	612	551	245	122	110	49	
TCJT476M004#0080	T	47	4	18.8	8	80	3	1000	900	400	80	72	32	
TCJA686M004#0250	A	68	4	27.2	6	250	3	548	493	219	137	123	55	
TCJB686M004#0070	B	68	4	27.2	6	70	3	1102	992	441	77	69	31	
TCJT686M004#0080	T	68	4	27.2	8	80	3	1000	900	400	80	72	32	
TCJA107M004#0200	A	100	4	40.0	6	200	3	612	551	245	122	110	49	
TCJB107M004#0070	B	100	4	40.0	8	70	3	1102	992	441	77	69	31	
TCJG107M004#0300	G	100	4	40.0	10	300	3	483	435	193	145	130	58	
TCJT107M004#0150	T	100	4	40.0	8	150	3	730	657	292	110	99	44	
TCJB157M004#0070	B	150	4	60.0	6	70	3	1102	992	441	77	69	31	
TCJB227M004#0045	B	220	4	88.0	10	45	3	1374	1237	550	62	56	25	
TCJB227M004#0070	B	220	4	88.0	10	70	3	1102	992	441	77	69	31	
6.3 Volt @ 85°C (4 Volt @ 125°C)														
TCJA106M006#0300	A	10	6.3	6.0	6	300	3	500	450	200	150	135	60	
TCJR106M006#0500	R	10	6.3	6.0	6	500	3	332	298	133	166	149	66	
TCJA156M006#0300	A	15	6.3	9.0	6	300	3	500	450	200	150	135	60	
TCJA226M006#0300	A	22	6.3	13.2	6	300	3	500	450	200	150	135	60	
TCJK226M006#0400	K	22	6.3	13.2	8	400	3	403	363	161	161	145	64	
TCJS226M006#0400	S	22	6.3	13.2	8	400	3	403	363	161	161	145	64	
TCJT226M006#0150	T	22	6.3	13.2	6	150	3	730	657	292	110	99	44	
TCJA336M006#0200	A	33	6.3	19.8	6	200	3	612	551	245	122	110	49	
TCJB336M006#0070	B	33	6.3	19.8	6	70	3	1102	992	441	77	69	31	
TCJB336M006#0200	B	33	6.3	19.8	6	200	3	652	587	261	130	117	52	
TCJT336M006#0150	T	33	6.3	19.8	8	150	3	730	657	292	110	99	44	
TCJA476M006#0200	A	47	6.3	28.2	6	200	3	612	551	245	122	110	49	
TCJB476M006#0070	B	47	6.3	28.2	6	70	3	1102	992	441	77	69	31	
TCLP476M006#0500	P	47	6.3	28.2	10	500	3	346	312	139	173	156	69	
TCJK476M006#0400	K	47	6.3	28.2	6	400	3	403	363	161	161	146	64	
TCJT476M006#0080	T	47	6.3	28.2	8	80	3	1000	900	400	80	72	32	
TCJT476M006#0120	T	47	6.3	28.2	8	120	3	816	735	327	98	88	39	
TCJB686M006#0055	B	68	6.3	40.8	8	55	3	1243	1119	497	68	62	27	
TCJB686M006#0070	B	68	6.3	40.8	8	70	3	1102	992	441	77	69	31	
TCJC686M006#0100	C	68	6.3	40.8	6	100	3	1049	944	420	105	94	42	
TCJW686M006#0070	W	68	6.3	40.8	8	70	3	1134	1021	454	79	71	32	
TCJB107M006#0045	B	100	6.3	60.0	10	45	3	1374	1237	550	62	56	25	
TCJB107M006#0069	B	100	6.3	60.0	10	69	3	1110	999	444	77	69	31	
TCJB107M006#0070	B	100	6.3	60.0	10	70	3	1102	992	441	77	69	31	
TCJA157M006#0200	A	150	6.3	90.0	10	200	3	612	551	245	122	110	49	
TCJB157M006#0045	B	150	6.3	90.0	10	45	3	1374	1237	550	62	56	25	
TCJB157M006#0069	B	150	6.3	90.0	10	69	3	1110	999	444	77	69	31	
TCJB157M006#0070	B	150	6.3	90.0	10	70	3	1102	992	441	77	69	31	
TCJH157M006#0200	H	150	6.3	90.0	6	200	3	632	569	253	126	114	51	
TCJW157M006#0040	W	150	6.3	90.0	6	40	3	1500	1350	600	60	54	24	
TCJW157M006#0070	W	150	6.3	90.0	6	70	3	1134	1021	454	79	71	32	
TCJB227M006#0070	B	220	6.3	132.0	10	70	3	1102	992	441	77	69	31	
TCJB227M006#0200	B	220	6.3	132.0	10	200	3	652	587	261	130	117	52	
10 Volt @ 85°C (7 Volt @ 125°C)														
TCJK475M010#0500	K	4.7	10	4.7	6	500	3	346	312	139	173	156	69	
TCJR475M010#0500	R	4.7	10	4.7	6	500	3	332	298	133	166	149	66	
TCJA106M010#0300	A	10	10	10.0	6	300	3	500	450	200	150	135	60	
TCJA156M010#0200	A	15	10	15.0	6	200	3	612	551	245	122	110	49	

Moisture Sensitivity Level (MSL) is defined according to J-STD-020.

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

ESR allowed to move up to 1.25 times catalog limit post mounting.

For typical weight and composition see page 124.

NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.



TCJ Series




Tantalum Solid Electrolytic Chip Capacitors with Conductive Polymer Electrode

RATINGS & PART NUMBER REFERENCE

AVX Part No.	Case Size	Capacitance (μF)	Rated Voltage (V)	DCL (μA) Max.	DF % Max.	ESR Max. (mΩ) @100kHz	MSL	100kHz RMS Current (mA)			100kHz RMS Voltage (mV)		
								25°C	85°C	125°C	25°C	85°C	125°C
TCJB226M010#0300	B	22	10	22.0	6	300	3	532	479	213	160	144	64
TCJT226M010#0150	T	22	10	22.0	6	150	3	730	657	292	110	99	44
TCJB336M010#0070	B	33	10	33.0	6	70	3	1102	992	441	77	69	31
TCJB336M010#0200	B	33	10	33.0	6	200	3	652	587	261	130	117	52
TCJC336M010#0100	C	33	10	33.0	6	100	3	1049	944	420	105	94	42
TCJT336M010#0070	T	33	10	33.0	6	70	3	1069	962	428	75	67	30
TCJT336M010#0150	T	33	10	33.0	6	150	3	730	657	292	110	99	44
TCJB476M010#0070	B	47	10	47.0	6	70	3	1102	992	441	77	69	31
TCJC476M010#0100	C	47	10	47.0	6	100	3	1049	944	420	105	94	42
16 Volt @ 85°C (10 Volt @ 125°C)													
TCJA685M016#0200	A	6.8	16	10.9	6	200	3	612	551	245	122	110	49
TCJA106M016#0200	A	10	16	16.0	6	200	3	612	551	245	122	110	49
TCJB106M016#0200	B	10	16	16.0	6	200	3	652	587	261	130	117	52
TCJT106M016#0150	T	10	16	16.0	6	150	3	730	657	292	110	99	44
TCJT106M016#0200	T	10	16	16.0	6	200	3	632	569	253	126	114	51
TCJB156M016#0150	B	15	16	24.0	6	150	3	753	677	301	113	102	45
TCJB226M016#0150	B	22	16	35.2	6	150	3	753	677	301	113	102	45

Voltage Derating vs Temperature Recommendation



AVX Part No.	Case Size	Capacitance (μF)	Rated Voltage (V)	DCL (μA) Max.	DF % Max.	ESR Max. (mΩ) @100kHz	MSL	100kHz RMS Current (mA)			100kHz RMS Voltage (mV)			
								25°C	85°C	105°C	25°C	85°C	105°C	
16 Volt @ 85°C (12.8 Volt @ 105°C)														
TCJY336M016#0070	Y	33	16	52.8	6	70	3	1336	1203	869	94	84	61	
TCJY476M016#0070	Y	47	16	75.2	6	70	3	1336	1203	869	94	84	61	
20 Volt @ 85°C (16 Volt @ 105°C)														
TCJY226M020#0070	Y	22	20	44.0	6	70	3	1336	1203	869	94	84	61	
TCJY336M020#0070	Y	33	20	66.0	6	70	3	1336	1203	869	94	84	61	
TCJY476M020#0070	Y	47	20	94.0	6	70	3	1336	1203	869	94	84	61	
25 Volt @ 85°C (20 Volt @ 105°C)														
TCJP105M025#0500	P	1.0	25	2.5	6	500	3	346	312	225	173	156	113	
TCJB156M025#0100	B	15	25	37.5	10	100	3	922	830	599	92	83	60	
TCJB226M025#0100	B	22	25	55.0	10	100	3	922	830	599	92	83	60	
TCJY226M025#0070	Y	22	25	55.0	10	70	3	1336	1203	869	94	84	61	
TCJY336M025#0100	Y	33	25	82.5	6	100	3	1118	1006	727	112	101	73	
35 Volt @ 85°C (28 Volt @ 105°C)														
TCJB106M035#0200	B	10	35	35.0	10	200	3	652	587	424	130	117	85	
TCJC106M035#0200	C	10	35	35.0	6	200	3	742	667	482	148	133	96	
TCJY106M035#0070	Y	10	35	35.0	6	70	3	1336	1203	869	94	84	61	
50 Volt @ 85°C (40 Volt @ 105°C)														
TCJB684M050#0300	B	0.68	50	3.4	6	300	3	532	479	346	160	144	104	
TCJB105M050#0300	B	1.0	50	5.0	6	300	3	532	479	346	160	144	104	
TCJB155M050#0300	B	1.5	50	7.5	6	300	3	532	479	346	160	144	104	
TCJC155M050#0300	C	1.5	50	7.5	6	300	3	606	545	394	182	163	118	
TCJC225M050#0300	C	2.2	50	11	6	300	3	606	545	394	182	163	118	
TCJC335M050#0200	C	3.3	50	16.5	8	200	3	742	667	482	148	133	96	
TCJC475M050#0200	C	4.7	50	23.5	8	200	3	742	667	482	148	133	96	
TCJC685M050#0200	C	6.8	50	34.0	8	200	3	742	667	482	148	133	96	
TCJD685M050#0120	D	6.8	50	34.0	10	120	3	1118	1006	727	134	121	87	
TCJD106M050#0120	D	10	50	50.0	10	120	3	1118	1006	727	134	121	87	

Moisture Sensitivity Level (MSL) is defined according to J-STD-020.

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

ESR allowed to move up to 1.25 times catalog limit post mounting.

For typical weight and composition see page 124.

NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.

Voltage vs Temperature Rating

