

PRODUCT NUMBER
10087122-7XXLF






PLATING
0.05µm Au FULL PLATED
OVER 1.27µm Ni MIN

INDICATES THE PRODUCT IS RoHS
COMPATIBLE, SEE NOTE 5

PIN STYLE	SIZE
06	2x3
08	2x4
10	2x5
14	2x7
16	2x8
18	2x9
20	2x10
26	2x13
30	2x15
34	2x17
40	2x20
44	2x22
50	2x25
60	2x30
64	2x32

NOTES:

- HOUSING MAT'L : GLASS FILLED THERMOPLASTIC. UL94V-0 COLOR: BLUE
- PIN MATERIAL : BRASS
- PRODUCT PACKAGED IN TUBES.
- TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS N x 2.54 = 20.32mm
- RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE, 2µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE.
 - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C ±5°C SOLDER BATH TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm MIN THICK CIRCUIT BOARD.
 - LABELLING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - LEGAL STATEMENT: SEE GS-47-0004



mat'l. code		surface	tolerance	projection	product family
ISO 1302		ISO 406	ISO 1101	mm	QUICKIE
ltr ecn no dr date		tolerances unless otherwise specified			title
A	F08-0149	LMU	08.03.27	.X ± 0.3	QKIE SSLIM HDR
B	B-19070	LMU	14.10.15	.XX ± 0.13	STR 0.05µm AU
C	B-19564	BVE	14.12.01	.XXX ± 0.05	
dr J.COMPAGNON		08.03.07		scale 2.5:1	dwg no
enrg L.MULIN		08.03.07			sheet 1 of 1
chr					size
appd L.MULIN		08.03.07			A3
sheet index		revision	sheet		type
					CUSTOMER Drawing