






Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



NOTES:

MATERIALS:

BUSHING - TIN PLATED STEEL
LEAD - SOLDER PLATED COPPER
NUT - TIN PLATED BRASS
L"WASHER - TIN PLATED PHOSPHOR BRONZE

MOUNTING TORQUE: 8 lb - ins. max

DCR - .01Ω max.

MAX. SOLDER TEMPERATURE 500°F

MIN. CAP (UF)	DWV (VDC)	I.R. MIN. @ 100 (VDC.)	WORKING VOLTAGE D.C.		CURRENT DC (AMPS.)	MIN. NO LOAD INSERTION LOSS (dB) @ 25°C PER MIL-STD-220						TEMP. CHARAC.
			85°C	125°C		30 KHz	100 KHz	300 KHz	1 MHz	10 MHz	1 GHz	
1.4	250	500 M	100	50	15	15	25	34	44	60	70	X7R

REVISION RECORD Original Release C.O. 930129-1 -066 ADDED 0-400 TO 125°C. E.C. 11-18-97 19971111-9-03 REVISED DWG. DRAWING MADE FOR EACH VAR. S.M. 06-13-02 2002 TABLE REVISED 50 WVDC @ 125° WAS 70 WVDC @ 125° L.E. 01-17-03 20030106-1-11 REVISED DWG. DRAWING MADE FOR EACH VAR. FROM FAMILY DWG. S.M. 02-06-03 20030204-2-13	0 4 5 6 7	--TOLERANCES-- Unless Otherwise Specified		Title COAXIAL BROADBAND - "L"	
		DECIMAL ±		Drawn E.C. 02-01-93 Scale 2 X	
		ANGLES ±		Approved B.Mc. 02-03-93	
		TUSONIX TUCSON, ARIZONA		A 4600-054	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix:](#)

[4600-054LF](#)