MAX4389/MAX4390/ MAX4392–MAX4396

Ultra-Small, Low-Cost, 85MHz Op Amps with Rail-to-Rail Outputs and Disable

General Description

The MAX4389/MAX4390/MAX4392–MAX4396 family of op amps are unity-gain stable devices that combine high-speed performance, rail-to-rail outputs, and disable mode. These devices are targeted for applications where an input or an output is exposed to the outside world, such as video and communications.

The MAX4389/MAX4390/MAX4392–MAX4396 operate from a single 4.5V to 11V supply or from dual ±2.25V to ±5.5V supplies. The common-mode input voltage range extends to the negative power-supply rail (ground in single-supply applications). The MAX4389/MAX4390/MAX4392–MAX4396 consume only 5.5mA of quiescent supply current per amplifier while achieving a 85MHz -3dB bandwidth, 27MHz 0.1dB gain flatness, and a 500V/µs slew rate. Disable mode sets the outputs to high impedance while consuming only 450µA of current.

The MAX4389 single, MAX4393 dual, MAX4394 triple, and MAX4396 quad include disable capabilities. The MAX4389 and MAX4390 are available in ultra-small, 6-pin SC70 packages.

Applications

- Set-Top Boxes
- Surveillance Video Systems
- Analog-to-Digital Converter Interface
- CCD Imaging Systems
- Digital Cameras
- Video-on-Demand
- Video Line Driver

µMAX is a registered trademark of Maxim Integrated Products, Inc.

Typical Operating Circuit



Features

- Low Cost
- High Speed
  - 85MHz -3dB Bandwidth
  - 27MHz 0.1dB Gain Flatness
  - 500V/µs Slew Rate
- Single 4.5V to 11V or Dual ±2.25V to ±5.5V Operation
- Rail-to-Rail Outputs
- Input Common-Mode Range Extends to V_{EE}
- Low Differential Gain/Phase: 0.015%/0.015°
- Low Distortion at 5MHz
  - -59dBc Spurious-Free Dynamic Range
- High Output Drive: ±50mA
- 450µA Disable Capability (MAX4389/MAX4393/MAX4394/MAX4396)
- Space-Saving SC70, SOT23, µMAX®, or TSSOP Packages

Ordering Information

PART	TEMP RANGE	PIN-PACKAGE	TOP MARK
MAX4389EXT+T	-40°C to +85°C	6 SC70	ABF
MAX4389EUT+T	-40°C to +85°C	6 SOT23	ABDC
MAX4390EXT+T	-40°C to +85°C	6 SC70	ABE
MAX4390EUK+T	-40°C to +85°C	5 SOT23	ADZM

+Denotes a lead(Pb)-free/RoHs-compliant package.
T = Tape and reel.

Ordering Information continued at end of data sheet.
Selector Guide appears at end of data sheet.

Pin Configurations



Pin Configurations continued at end of data sheet.

Absolute Maximum Ratings

Supply Voltage (V_{CC} to V_{EE}) ..... -0.3V to +12V
IN_+, IN_-, OUT_, $\overline{DISABLE}$ ..... (V_{EE} - 0.3V) to (V_{CC} + 0.3V)
Differential Input Voltage ..... ±2.5V
Current into Input Pins ..... ±20mA
Output Short-Circuit Duration to
V_{CC} or V_{EE} (Note 1) ..... Continuous
Continuous Power Dissipation (T_A = +70°C)
5-Pin SOT23 (derate 7.1mW/°C above +70°C) 571mW
6-Pin SOT23 (derate 8.7mW/°C above +70°C) 696mW
6-Pin SC70 (derate 3.1mW/°C above +70°C) 245mW
8-Pin SO (derate 5.88mW/°C above +70°C) 471mW
8-Pin µMAX (derate 4.5mW/°C above +70°C) 362mW
10-Pin µMAX (derate 5.6mW/°C above +70°C) 444mW
14-Pin SO (derate 8.33mW/°C above +70°C) 667mW
14-Pin TSSOP (derate 10mW/°C above +70°C) 727mW
20-Pin TSSOP (derate 10.9mW/°C above +70°C) 879mW
Operating Temperature Range ..... -40°C to +85°C
Junction Temperature ..... +150°C
Storage Temperature Range ..... -65°C to +150°C
Lead Temperature (soldering, 10s) ..... +300°C

Note 1: Continuous power dissipation must also be observed.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

DC Electrical Characteristics—Single Supply

(V_{CC} = 5V, V_{EE} = 0V, V_{CM} = V_{CC}/2, V_{OUT} = V_{CC}/2, R_L = ∞ to V_{CC}/2, $\overline{DISABLE_}$ = V_{CC} (MAX4389/MAX4393/MAX4394/MAX4396), T_A = T_{MIN} to T_{MAX}, unless otherwise noted. Typical values are at T_A = +25°C.) (Note 2)

PARAMETER	SYMBOL	CONDITIONS		MIN	TYP	MAX	UNITS
Input Common-Mode Voltage Range	V_{CM}	Guaranteed by CMRR test		V_{EE} - 0.2		V_{CC} - 2.25	V
Input Offset Voltage	V_{OS}	T_A = +25°C			5	18	mV
		T_A = -40°C to +85°C				26	
Input Offset Voltage Matching		MAX4392–MAX4396			1		mV
Input Offset Voltage Tempco	TC_{VOS}				15		µV/°C
Input Bias Current	I_B				2.5	15	µA
Input Offset Current	I_{OS}				0.2	5	µA
Input Resistance	R_{IN}	Differential mode (-1V ≤ V_{IN} ≤ +1V)			70		kΩ
		Common mode (-0.2V ≤ V_{CM} ≤ +2.75V)			3		MΩ
Common-Mode Rejection Ratio	CMRR	(V_{EE} - 0.2V) ≤ V_{CM} ≤ (V_{CC} - 2.25V)		70	95		dB
Open-Loop Gain	A_{VOL}	0.25V ≤ V_{OUT} ≤ 4.75V, R_L = 2kΩ		50	70		dB
		0.8V ≤ V_{OUT} ≤ 4.5V, R_L = 150Ω		50	60		
		1V ≤ V_{OUT} ≤ 4V, R_L = 50Ω			58		
Output Voltage Swing	V_{OUT}	R_L = 2kΩ	V_{CC} - V_{OH}		0.065	0.25	V
			V_{OL} - V_{EE}		0.05	0.15	
		R_L = 150Ω	V_{CC} - V_{OH}		0.3	0.5	
			V_{OL} - V_{EE}		0.25	0.5	
		R_L = 75Ω	V_{CC} - V_{OH}		0.5	0.8	
			V_{OL} - V_{EE}		0.45	0.8	
		R_L = 75Ω to ground	V_{CC} - V_{OH}		1	1.7	
			V_{OL} - V_{EE}		0.025	0.1	
Output Current	I_{OUT}	Sinking from R_L = 75Ω to V_{CC}		40	55		mA
		Sourcing into R_L = 75Ω to V_{EE}		40	50		
Output Short-Circuit Current	I_{SC}	Sinking or sourcing			±100		mA

DC Electrical Characteristics—Single Supply (continued)

(V_{CC} = 5V, V_{EE} = 0V, V_{CM} = V_{CC}/2, V_{OUT} = V_{CC}/2, R_L = ∞ to V_{CC}/2, $\overline{DISABLE_}$ = V_{CC} (MAX4389/MAX4393/MAX4394/MAX4396), T_A = T_{MIN} to T_{MAX}, unless otherwise noted. Typical values are at T_A = +25°C.) (Note 2)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
Open-Loop Output Resistance	R_{OUT}			8		Ω
Power-Supply Rejection Ratio	PSRR	V_{EE} = 0V, V_{CC} = 4.5V to 5.5V	48	65		dB
Operating Supply Voltage Range	V_S	Guaranteed by PSRR	4.5		11	V
Disabled Output Resistance	$R_{OUT(OFF)}$	$V_{\overline{DISABLE_}}$ = 0V, 0 ≤ V_{OUT} ≤ 5V	40	95		kΩ
$\overline{DISABLE_}$ Logic-Low Threshold	V_{IL}				V_{CC} - 3	V
$\overline{DISABLE_}$ Logic-High Threshold	V_{IH}		V_{CC} - 1.25			V
$\overline{DISABLE_}$ Logic-Input Low Current	I_{IL}	$V_{\overline{DISABLE_}}$ = 0V		20	60	µA
$\overline{DISABLE_}$ Logic-Input High Current	I_{IH}	$\overline{DISABLE_}$ = V_{CC}		5	40	µA
Quiescent Supply Current (Per Amplifier)	I_S	$\overline{DISABLE_}$ = V_{CC}		3.2	5	mA
		$V_{\overline{DISABLE_}}$ = 0V		0.3	0.4	

DC Electrical Characteristics—Dual Supply

(V_{CC} = 5V, V_{EE} = -5V, V_{CM} = 0V, V_{OUT} = 0V, R_L = ∞ to 0, $\overline{DISABLE_}$ = V_{CC} (MAX4389/MAX4393/MAX4394/MAX4396), T_A = T_{MIN} to T_{MAX}, unless otherwise noted. Typical values are at T_A = +25°C.) (Note 2)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
Input Common-Mode Voltage	V_{CM}	Guaranteed by CMRR test	V_{EE}		V_{CC} - 2.25	V
Input Offset Voltage	V_{OS}	T_A = +25°C		7	20	mV
		T_A = -40°C to +85°C			28	
Input Offset Voltage Matching		MAX4392–MAX4396		1		mV
Input Offset Voltage Tempco	TC_{VOS}			20		µV/°C
Input Bias Current	I_B			5	15	µA
Input Offset Current	I_{OS}			0.5	5	µA
Input Resistance	R_{IN}	Differential mode (-1V ≤ V_{IN} ≤ +1V)		70		kΩ
		Common mode (-0.2V ≤ V_{CM} ≤ +2.75V)		3		MΩ
Common-Mode Rejection Ratio	CMRR	V_{EE} ≤ V_{CM} ≤ (V_{CC} - 2.25V)	70	90		dB
Open-Loop Gain	A_{VOL}	-4.5V ≤ V_{OUT} ≤ 4.5V, R_L = 2kΩ	65	80		dB
		-4.25V ≤ V_{OUT} ≤ 4.25V, R_L = 150Ω	50	60		

DC Electrical Characteristics—Dual Supply (continued)

(V_{CC} = 5V, V_{EE} = -5V, V_{CM} = 0V, V_{OUT} = 0V, R_L = ∞ to 0, $\overline{DISABLE_}$ = V_{CC} (MAX4389/MAX4393/MAX4394/MAX4396), T_A = T_{MIN} to T_{MAX}, unless otherwise noted. Typical values are at T_A = +25°C.) (Note 2)

PARAMETER	SYMBOL	CONDITIONS		MIN	TYP	MAX	UNITS
Output Voltage Swing	V_{OUT}	R_L = 2kΩ	V_{CC} - V_{OH}		0.175	0.3	V
			V_{OL} - V_{EE}		0.075	0.2	
		R_L = 150Ω	V_{CC} - V_{OH}		0.575	0.85	
			V_{OL} - V_{EE}		0.4	1.5	
		R_L = 75Ω	V_{CC} - V_{OH}		1.5	2.35	
			V_{OL} - V_{EE}		0.75	1.6	
Output Current	I_{OUT}	Sinking from R_L = 75Ω to V_{CC}		50	95		mA
		Sourcing into R_L = 75Ω to V_{EE}		50	75		
Output Short-Circuit Current	I_{SC}	Sinking or sourcing			±100		mA
Open-Loop Output Resistance	R_{OUT}				8		Ω
Power-Supply Rejection Ratio	PSRR	V_{EE} = 0V, V_{CC} = 4.5V to 5.5V		48	60		dB
Operating Supply Voltage Range	V_S	Guaranteed by PSRR		4.5		11	V
Disabled Output Resistance	$R_{OUT(OFF)}$	$V_{\overline{DISABLE_}}$ = 0V, -5V ≤ V_{OUT} ≤ +5V		40	95		kΩ
$\overline{DISABLE_}$ Logic-Low Threshold	V_{IL}					V_{CC} - 3	V
$\overline{DISABLE_}$ Logic-High Threshold	V_{IH}			V_{CC} - 1.25			V
Quiescent Supply Current (Per Amplifier)	I_S	$\overline{DISABLE_}$ = V_{CC}			6	10	mA
		$V_{\overline{DISABLE_}}$ = 0V			0.45	0.8	

AC Electrical Characteristics—Single Supply

(V_{CC} = 5V, V_{EE} = 0V, V_{CM} = 1.5V, R_L = 100Ω to V_{CC}/2, $\overline{DISABLE_}$ = V_{CC} (MAX4389/MAX4393/MAX4394/MAX4396), V_{OUT} = V_{CC}/2, A_{VCL} = 1V/V, T_A = +25°C, unless otherwise noted.)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
Small-Signal -3dB Bandwidth	BW_{SS}	V_{OUT} = 100mV_{P-P}		72		MHz
Large-Signal -3dB Bandwidth	BW_{LS}	V_{OUT} = 2V_{P-P}		80		MHz
Small-Signal 0.1dB Gain Flatness	$BW_{0.1dBSS}$	V_{OUT} = 100mV_{P-P}		30		MHz
Large-Signal 0.1dB Gain Flatness	$BW_{0.1dBLS}$	V_{OUT} = 2V_{P-P}		30		MHz
Slew Rate	SR	V_{OUT} = 2V step		500		V/µs
Settling Time to 0.1%	t_S	V_{OUT} = 2V step		28		ns
Rise/Fall Time	t_R/t_F	V_{OUT} = 100mV_{P-P}		4		ns
Spurious-Free Dynamic Range	SFDR	f_C = 5MHz, V_{OUT} = 2V_{P-P}		-59		dBc

AC Electrical Characteristics—Single Supply (continued)

(V_{CC} = 5V, V_{EE} = 0V, V_{CM} = 1.5V, R_L = 100Ω to $V_{CC}/2$, $\overline{DISABLE_}$ = V_{CC} (MAX4389/MAX4393/MAX4394/MAX4396), V_{OUT} = $V_{CC}/2$, A_{VCL} = 1V/V, T_A = +25°C, unless otherwise noted.)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
Differential Phase Error	DP	NTSC, R_L = 150Ω		0.015		degrees
Differential Gain Error	DG	NTSC, R_L = 150Ω		0.015		%
Input Noise-Voltage Density	e_n	f = 10kHz		13		nV/√Hz
Input Noise-Current Density	i_n	f = 10kHz		2.1		pA/√Hz
Input Capacitance	C_{IN}			1		pF
Output Impedance	Z_{OUT}	f = 5MHz		0.6		Ω
Disable OFF Time		MAX4389/MAX4393/MAX4394/MAX4396		80		ns
Disable ON Time		MAX4389/MAX4393/MAX4394/MAX4396		40		ns
Channel-to-Channel Isolation	CH_{ISO}	MAX4392–MAX4396, specified at DC		-97		dB

AC Electrical Characteristics —Dual Supply

(V_{CC} = 5V, V_{EE} = -5V, R_L = ∞ to GND, GND = 0, V_{OUT} = 0V, Gain = 1V/V, $\overline{DISABLE}$ = V_{CC}, and T_A = T_{MIN} to T_{MAX}, unless otherwise noted. Typical values are at T_A = +25°C.)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
Small-Signal -3dB Bandwidth	BW_{SS}	V_{OUT} = 100mV_{P-P}		85		MHz
Large-Signal -3dB Bandwidth	BW_{LS}	V_{OUT} = 2V_{P-P}		90		MHz
Small-Signal Bandwidth for 0.1dB Gain Flatness	$BW_{0.1dBss}$	V_{OUT} = 100mV_{P-P}		27		MHz
Large-Signal Bandwidth for 0.1dB Gain Flatness	$BW_{0.1dBLS}$	V_{OUT} = 2V_{P-P}		24		MHz
Slew Rate	SR	V_{OUT} = 2V step		500		V/µs
Settling Time to 0.1%	t_S	V_{OUT} = 2V step		21		ns
Rise/Fall Time	t_R/t_F	V_{OUT} = 100mV_{P-P}		4		ns
Spurious-Free Dynamic Range	SFDR	f_C = 5MHz, V_{OUT} = 2V_{P-P}		-59		dBc
Differential Phase Error	DP	NTSC, R_L = 150Ω		0.015		degrees
Differential Gain Error	DG	NTSC, R_L = 150Ω		0.015		%
Input Noise-Voltage Density	e_n	f = 10kHz		13		nV/√Hz
Input Noise-Current Density	i_n	f = 10kHz		2.1		pA/√Hz
Input Capacitance	C_{IN}			1		pF
Output Impedance	Z_{OUT}	f = 5MHz		0.6		Ω
Disable OFF Time		MAX4389/MAX4393/MAX4394/MAX4396		80		ns
Disable ON Time		MAX4389/MAX4393/MAX4394/MAX4396		40		ns
Channel-to-Channel Isolation	CH_{ISO}	MAX4392/MAX4393/MAX4394/MAX4395/ MAX4396, specified at DC		-97		dB

Note 2: All devices are 100% production tested at T_A = +25°C. Specifications over temperature limits are guaranteed by design.

Typical Operating Characteristics

(V_{CC} = 5V, V_{EE} = -5V, V_{CM} = 0V, A_{VCL} = 1V/V, R_L = 100Ω to GND, GND = 0, T_A = +25°C, unless otherwise noted.)

GAIN AND PHASE vs. FREQUENCY



SMALL-SIGNAL GAIN vs. FREQUENCY



LARGE-SIGNAL GAIN vs. FREQUENCY



SMALL-SIGNAL GAIN FLATNESS vs. FREQUENCY



LARGE-SIGNAL GAIN FLATNESS vs. FREQUENCY



OUTPUT IMPEDANCE vs. FREQUENCY



DISTORTION vs. FREQUENCY



DISTORTION vs. FREQUENCY



DISTORTION vs. FREQUENCY



Typical Operating Characteristics (continued)

(V_{CC} = 5V, V_{EE} = -5V, V_{CM} = 0V, A_{VCL} = 1V/V, R_L = 100Ω to GND, GND = 0, T_A = +25°C, unless otherwise noted.)

DISTORTION vs. RESISTIVE LOAD



DISTORTION vs. VOLTAGE SWING



DIFFERENTIAL GAIN AND PHASE



COMMON-MODE REJECTION vs. FREQUENCY



POWER-SUPPLY REJECTION vs. FREQUENCY



OUTPUT VOLTAGE SWING vs. RESISTIVE LOAD



SMALL-SIGNAL PULSE RESPONSE



SMALL-SIGNAL PULSE RESPONSE



SMALL-SIGNAL PULSE RESPONSE



Typical Operating Characteristics (continued)

(V_{CC} = 5V, V_{EE} = -5V, V_{CM} = 0V, A_{VCL} = 1V/V, R_L = 100Ω to GND, GND = 0, T_A = +25°C, unless otherwise noted.)

LARGE-SIGNAL PULSE RESPONSE



LARGE-SIGNAL PULSE RESPONSE



LARGE-SIGNAL PULSE RESPONSE



VOLTAGE NOISE vs. FREQUENCY



CURRENT NOISE vs. FREQUENCY



ISOLATION RESISTANCE vs. CAPACITIVE LOAD



Typical Operating Characteristics (continued)

(V_{CC} = 5V, V_{EE} = -5V, V_{CM} = 0V, A_{VCL} = 1V/V, R_L = 100Ω to GND, GND = 0, T_A = +25°C, unless otherwise noted.)

SMALL-SIGNAL BANDWIDTH vs. LOAD RESISTANCE



OPEN-LOOP GAIN vs. RESISTIVE LOAD



CROSSTALK vs. FREQUENCY



DISABLE RESPONSE



INPUT OFFSET VOLTAGE vs. TEMPERATURE



INPUT BIAS CURRENT vs. TEMPERATURE



SUPPLY CURRENT vs. TEMPERATURE



Pin Description

PIN								NAME	FUNCTION
MAX4389	MAX4390		MAX4392	MAX4393	MAX4394	MAX4395	MAX4396		
SC70/SOT23	SC70	SOT23	µMAX/SO	µMAX	SO/TSSOP	SO/TSSOP	TSSOP		
1	1	1	—	—	—	—	—	OUT	Amplifier Output
2	2	2	4	4	11	11	16	V_{EE}	Negative Power Supply. Connect a 0.1µF capacitor to GND.
3	3	3	—	—	—	—	—	IN+	Noninverting Input
4	4	4	—	—	—	—	—	IN-	Inverting Input
5	—	—	—	—	—	—	—	$\overline{DISABLE}$	Disable. Connect to V_{CC} to enable.
6	6	5	8	10	4	4	5	V_{CC}	Positive Power Supply. Connect a 0.1µF capacitor to GND.
—	5	—	—	—	—	—	10, 11	N.C.	No Connection. Not internally connected.
—	—	—	3	3	5	3	4	INA+	Amplifier A Noninverting Input
—	—	—	2	2	6	2	3	INA-	Amplifier A Inverting Input
—	—	—	1	1	7	1	2	OUTA	Amplifier A Output
—	—	—	—	5	1	—	1	$\overline{DISABLEA}$	Shutdown Amplifier A. Connect to V_{CC} to enable.
—	—	—	5	7	10	5	6	INB+	Amplifier B Noninverting Input
—	—	—	6	8	9	6	7	INB-	Amplifier B Inverting Input
—	—	—	7	9	8	7	8	OUTB	Amplifier B Output

Pin Description (continued)

PIN								NAME	FUNCTION
MAX4389	MAX4390		MAX4392	MAX4393	MAX4394	MAX4395	MAX4396		
SC70/SOT23	SC70	SOT23	µMAX/SO	µMAX	SO/TSSOP	SO/TSSOP	TSSOP		
—	—	—	—	6	3	—	9	$\overline{\text{DISABLEB}}$	Shutdown Amplifier B. Connect to V_{CC} to enable.
—	—	—	—	—	12	10	15	INC+	Amplifier C Noninverting Input
—	—	—	—	—	13	9	14	INC-	Amplifier C Inverting Input
—	—	—	—	—	14	8	13	OUTC	Amplifier C Output
—	—	—	—	—	2	—	12	$\overline{\text{DISABLEC}}$	Shutdown Amplifier C. Connect to V_{CC} to enable.
—	—	—	—	—	—	12	17	IND+	Amplifier D Noninverting Input
—	—	—	—	—	—	13	18	IND-	Amplifier D Inverting Input
—	—	—	—	—	—	14	19	OUTD	Amplifier D Output
—	—	—	—	—	—	—	20	$\overline{\text{DISABLED}}$	Shutdown Amplifier D. Connect to V_{CC} to enable.

Detailed Description

The MAX4389/MAX4390/MAX4392–MAX4396 are dual-supply, rail-to-rail, voltage-feedback amplifiers that employ current-feedback techniques to achieve 500V/µs slew rates and 85MHz bandwidths. Excellent harmonic distortion and differential gain/phase performance make these amplifiers an ideal choice for a wide variety of video and RF signal-processing applications.

Applications Information

The output voltage swings to within 200mV of each supply rail. Local feedback around the output stage ensures low open-loop output impedance to reduce gain sensitivity to load variations. The input stage permits common-mode voltages to the negative supply and to within 2.25V of the positive supply rail.

Choosing Resistor Values

Unity-Gain Configuration

The MAX4389/MAX4390/MAX4392–MAX4396 are internally compensated for unity gain. When configured for unity gain, a 24Ω resistor (R_F) in series with the feedback path optimizes AC performance. This resistor improves AC response by reducing the Q of the parallel LC circuit formed by the parasitic feedback capacitance and inductance.

Video Line Driver

The MAX4389/MAX4390/MAX4392–MAX4396 are low-power, voltage-feedback amplifiers featuring large-signal ($2V_{P-P}$) bandwidths of 90MHz and 0.1dB large-signal gain flatness of 24MHz. They are designed to minimize differential-gain error and differential-phase error to 0.015% and 0.015°, respectively. They have a 21ns settling time to 0.1%, 500V/µs slew rates, and output-current-drive capability of up to 50mA making them ideal for driving video loads.

Inverting and Noninverting Configurations

Select the gain-setting feedback (R_F) and input (R_G) resistor values to fit your application. Large resistor values increase voltage noise and interact with the amplifier's input and PCB capacitance. This can generate undesirable poles and zeros and decrease bandwidth or cause oscillations. For example, a noninverting gain-of-two configuration ($R_F = R_G$) using 2kΩ resistors, combined with 1pF of amplifier input capacitance and 1pF of PCB capacitance, causes a pole at 79.6MHz. Since this pole is within the amplifier bandwidth, it jeopardizes stability. Reducing the 2kΩ resistors to 100Ω extends the pole frequency to 1.59GHz, but could limit output swing by adding 200Ω in parallel with the amplifier's load resistor (Figures 1a and 1b).



Figure 1a. Noninverting Gain Configuration



Figure 1b. Inverting Gain Configuration

Layout and Power-Supply Bypassing

The MAX4389/MAX4390/MAX4392–MAX4396 operate from single 4.5V to 11V or from dual ±2.25V to ±5.5V supplies. Bypass each supply with a 0.1µF capacitor as close to the pin as possible.

Maxim recommends using microstrip and stripline techniques to obtain full bandwidth. To ensure that the PCB does not degrade the amplifier's performance, design it for a frequency greater than 1GHz. Pay careful attention to inputs and outputs to avoid large parasitic capacitance. Whether or not you use a constant-impedance board, observe the following design guidelines:

- Do not use wire-wrap boards; they are too inductive.
- Do not use IC sockets; they increase parasitic capacitance and inductance.
- Use surface-mount instead of through-hole components for better, high-frequency performance.
- Use a PCB with at least two layers; it should be as free from voids as possible.
- Keep signal lines as short and as straight as possible. Do not make 90° turns; round all corners.

Low-Power Disable Mode

The MAX4389/MAX4393/MAX4394/MAX4396 feature a disable function that allows the amplifiers to be placed in a low-power, high-output impedance state. When the disable pin ($\overline{DISABLE}$) is active, the amplifier's output impedance is 95kΩ. This high resistance and the low 2pF output capacitance make the MAX4389/MAX4390/MAX4392–MAX4396 in RF/video multiplexer or switch applications. For larger arrays, pay careful attention to capacitive loading (see the *Output Capacitive Loading and Stability* section).

Output Capacitive Loading and Stability

The MAX4389/MAX4390/MAX4392–MAX4396 are optimized for AC performance. They are not designed to drive highly reactive loads, which decrease phase margin and may produce excessive ringing and oscillation. Figure 2 shows a circuit that eliminates this problem. Figure 3 is a graph of the Optimal Isolation Resistor (R_S) vs. Capacitive Load. Figure 4 shows how a capacitive load causes excessive peaking of the amplifier's frequency response if the capacitor is not isolated from the amplifier by a resistor. A small isolation resistor (usually 10Ω to 15Ω) placed before the reactive load prevents ringing and oscillation. At higher capacitive loads, AC performance is controlled by the interaction of the load capacitance and the isolation resistor. Figure 5 shows the effect of a 15Ω isolation resistor on closed-loop response.



Figure 2. Driving a Capacitive Load Through an Isolation Resistor



Figure 3. Isolation Resistance vs. Capacitive Load



Figure 4. Small-Signal Gain vs. Frequency with Load Capacitance and No Isolation Resistor



Figure 5. Small-Signal Gain vs. Frequency with Load Capacitance and 27Ω Isolation Resistor

Chip Information

PROCESS: BiCMOS

Pin Configurations (continued)













Pin Configurations (continued)



Ordering Information (continued)

PART	TEMP RANGE	PIN-PACKAGE	TOP MARK
MAX4392ESA+T	-40°C to +85°C	8 SO	—
MAX4392EUA+T	-40°C to +85°C	8 µMAX	—
MAX4393EUB+T	-40°C to +85°C	10 µMAX	—
MAX4394ESD+T	-40°C to +85°C	14 SO	—
MAX4394EUD+T	-40°C to +85°C	14 TSSOP	—
MAX4395ESD+T	-40°C to +85°C	14 SO	—
MAX4395EUD+T	-40°C to +85°C	14 TSSOP	—
MAX4396EUP+T	-40°C to +85°C	20 TSSOP	—

+Denotes a lead(Pb)-free/RoHs-compliant package.
/V denotes an automotive qualified part.
T = Tape and reel.

Selector Guide

PART	NO. OF AMPS	DISABLE
MAX4389	1	Yes
MAX4390	1	No
MAX4392	2	No
MAX4393	2	Yes
MAX4394	3	Yes
MAX4395	4	No
MAX4396	4	Yes

Package Information

For the latest package outline information and land patterns (footprints), go to www.maximintegrated.com/packages. Note that a "+", "#", or "-" in the package code indicates RoHS status only. Package drawings may show a different suffix character, but the drawing pertains to the package regardless of RoHS status.

PACKAGE TYPE	PACKAGE CODE	OUTLINE NO.	LAND PATTERN NO.
6 SC70	X6SN+1	21-0077	90-0189
6 SOT23	U6SN+1	21-0058	90-0175
5 SOT23	U5+1	21-0057	90-0174
8 µMAX	U8+1	21-0036	90-0092
10 µMAX	U10+2	21-0061	90-0330
8 S0	S8+2	21-0041	90-0096
14 SO	S14+1	21-0041	90-0112
14 TSSOP	U14+1	21-0066	90-0113
20 TSSOP	U20+3	21-0066	90-0116

Revision History

REVISION NUMBER	REVISION DATE	DESCRIPTION	PAGES CHANGED
4	11/09	Added automotive qualified parts	2, 15
5	5/14	Revised package codes	16
6	4/15	Removed automotive packages from data sheet	1, 15

For pricing, delivery, and ordering information, please contact Maxim Direct at 1-888-629-4642, or visit Maxim Integrated's website at www.maximintegrated.com.

Maxim Integrated cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim Integrated product. No circuit patent licenses are implied. Maxim Integrated reserves the right to change the circuitry and specifications without notice at any time. The parametric values (min and max limits) shown in the Electrical Characteristics table are guaranteed. Other parametric values quoted in this data sheet are provided for guidance.