


15

16





3

1


4

[illegible]

TERMINATED VIEW
W/COVER ASSEMBLED



1. CONNECTORS COMPLIANT WITH AMP SPEC. 108-40,012 AND MATF WITH ANY SAME NUMBER POSITION RECEPTACLE CONNECTOR IN AMPLIMITE SERIES.
2. CONNECTOR DESIGNED FOR 28 AND 26 AWG STRANDED AND SOLID CONDUCTOR RIBBON CABLE ON .0504.
- ▲ FASTENERS WILL WITHSTAND 6 IN. LBS. TORQUE AND 50 LBS PULL CUT FORCE FROM MATING FACE SIDE.
- ▲ MOLDED PARTS: UL RATED 94 V-0 THERMOPLASTIC, CO-OR-B-A-CK.
- ▲ SHELL: STEEL PER QQ-5-658.
- ▲ CONTACTS: PHOSPHOR BRONZE PER QQ-3-750.
- ▲ FASTENERS: BRASS PER QQ-8-626.
- ▲ GOLD PLATING PER MIL-G-45204, BRIGHT TIN PLATING PER MIL-T-10727, NICKEL PLATING PER QQ-N-290.
- ▲ SHELL: BRIGHT TIN PLATED.
- ▲ CONTACTS: .000030 GOLD C ON MATING END, .000100-.000200 BRIGHT TIN LEAD ON TERMINATION END, ALL OVER .000050 NICKEL ON ENTIRE CONTACT.
- ▲ LOCKING FASTENER IS COLOR CODED RED TO IDENTIFY SELF-LOCKING FEATURE.
- ▲ LOCKING FEATURE PROVIDES A RESISTIVE TORQUE OF 10 TO 18 IN-OZ, USING A 4-40 GAUGE SCREW.



	1.216	.934	.759	.666	.400	8	9	746862-4
OB50LE1E	1.541	.312	1.087	.994	.700	14	15	746862-3
OB50LETE	2.090	.852	1.623	1.534	1.200	24	25	746862-2
OB50LETE	2.732	2.500	2.275	2.183	1.800	36	37	746862-1

[illegible]