




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00						
			D1	REVISED PER ECO-11-004835	11MAR11	RK	HMR

- 1 0.38µm [.000015] MIN GOLD ON MATING AREA,
1.27µm [.000050] MIN BRIGHT TIN-LEAD ON CRIMP AREA, BOTH OVER
1.27µm [.000050] MIN NICKEL.
- 2 2.54µm [.000100] MIN BRIGHT TIN-LEAD, OVER
1.27µm [.000050] MIN NICKEL.
- 3 GOLD FLASH ON CRIMP AREA,
2.54µm [.000100] MIN TIN ON MATING AREA, BOTH OVER
1.27µm [.000050] MIN NICKEL.
- 4 0.38µm [.000015] MIN GOLD ON MATING AREA,
GOLD FLASH ON CRIMP AREA, BOTH OVER
1.27µm [.000050] MIN NICKEL.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 6 GOLD PLATING MAY OR MAY NOT BE PRESENT ON THE BOTTOM OF THE CRIMP BARREL

5 OBSOLETE	4	487923-5
3	6	487923-4
5 OBSOLETE	1	487923-3
	2	487923-1
FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.OBERMAN 3-7-90	TE TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK R.STONE 3-8-90				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
	0 PLC ± -		CONTACT, SOLDER TAB,			
	1 PLC ± -		.050 C/L			
	2 PLC ± 0.13 [.005]		-			
	3 PLC ± -		SIZE			
	4 PLC ± -		CAGE CODE			
	ANGLES ± -		DRAWING NO			
	FINISH		RESTRICTED TO			
MATERIAL PHOSPHOR BRONZE		SEE TABLE	WEIGHT			
			A2 00779 C=487923			
			CUSTOMER DRAWING			
			SCALE 10:1 SHEET 1 OF 1 REV D1			