

LOC	DIST	REVISIONS			DATE	OWN	APVD
		P	LTR	DESCRIPTION			
			M	REV PER ECO 13-016525	12-9-13	CT	JW

METRIC


DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	 E13288 Listed
2/0 AWG SOLID OR STRANDED	2/0 AWG STRANDED
 LR7189 Certified	MILITARY P/N AND CLASS
2/0 AWG SOLID OR STRANDED	NOT APPLICABLE


- 1

STAMP AMP 2/0W* APPROX AS SHOWN
- 2

STAMP 125 APPROX AS SHOWN



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 150° C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 60.6-76.3mm² [119,500-150,500] CIR MILS SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

<u>BODY:</u> COPPER ASTM B-152 TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727	13.08 ±0.13 [.515 ±.005]	1/2	51989-3
	9.91 ±0.13 [.390 ±.005]	3/8	51989-2
	8.33 ±0.13 [.328 ±.005]	5/16	51989-1
	6.73 ±0.13 [.265 ±.005]	1/4	51989
<u>INSERT:</u> BRASS PER MIL-C-50 TIN PLATE 0.00762[.000300] MIN EXT THK PER MIL-T-10727	'A'	'B'	PART NO
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 1/20/94 CHK 1/21/94 APVD -	 TE Connectivity
DIMENSIONS: MM [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC APPLICATION SPEC	
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± ± - FINISH	WEIGHT -	TERMINAL, RING TONGUE, COPALUM TM
MATERIAL SEE TABLE	SEE TABLE	CUSTOMER DRAWING	
SIZE		CAGE CODE	DRAWING NO
A2		00779	G-51989
RESTRICTED TO		SCALE	SHEET
-		2:1	1 of 1
REV		M	