SERIES 4212R 4212

RoHS Compliant

Traditional First Quality

Wound Beads



DASH NUMBER*	FIGURE	TURNS	MINIMUM IMPEDANCE 10 MHz	50 MHz	100 MHz	150 MHz	200 MHz	220 MHz
SERIES 4212R / 4212								
-1	1–3	2 1/2	—	—	750	700	—	400
-2	1–3	2 1/2	325	—	575	525	—	—
-3	1–1	1 1/2	—	325	425	—	400	—
-4	1–1	1 1/2	170	320	375	—	—	—
-5	1–2	2	—	525	600	—	600	—
-6	1–2	2	240	520	480	—	—	—
-7	1–4	3	—	950	900	—	600	—
-8	1–4	3	400	800	550	—	—	—

*Complete part # must include series # PLUS the dash #

For surface finish information, refer to www.delevanfinishes.com

Physical Parameters

	Inches	Millimeters
Length	0.374 to 0.414	9.50 to 10.51
Diameter	0.216 to 0.256	5.48 to 6.35
Lead Size		
AWG #24 TCW	0.0185 to 0.0215	0.47 to 0.55
A	0.12 Max.	3.05 Max.
B	1.10 Min.	28.0 Min.

Impedances measured on HP 4191A Impedance Analyzer.

High resistivity ferrite material eliminates the need to insulate windings.

Lead Wire Plated copper

Packaging Bulk only

For more detailed graphs, contact factory



270 Quaker Rd., East Aurora NY 14052 • Phone 716-652-3600 • Fax 716-652-4814 • E-mail: apisales@delevan.com • www.delevan.com

API Delevan®