


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.



REVISIONS			DOC. NO. SPC-F005 * Effective: 12/21/98 * DCP No: 680					
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
	B	REVISED & REDRAWN						
95	C	REDRAWN	HYO	1/31/00	JC	3/3/00	JC	3/3/00

SPC TYPE NO.	VOLTS	AMPS	WATTS	MSCP	LIFE HOURS
17	28	0.065	1.82	0.65	5000
37	14	0.09	1.26	0.5	1500
56	5	0.115	0.58	0.15	20000
73	14	0.08	1.12	0.3	15000
74	14	0.1	1.4	0.7	500
79	6	0.2	1.2	0.6	1000
85	28	0.04	1.12	0.3	7000
86	6.3	0.2	1.26	0.4	20000

NOTE:
Filament for all SPC type NOs.: C-2F

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
J.C.	1/6/93
CHECKED BY:	DATE:
J.P.	2/2/93
APPROVED BY:	DATE:
J.L.	2/8/93



SPC TECHNOLOGY

DRAWING TITLE:
T 1-3/4 SUB MINIATURE WEDGE LAMP

SIZE A	DWG. NO. TA-194	ELECTRONIC FILE TA-194.DWG	REV C
SCALE: NTS	U.O.M.: INCHES	SHEET: 1	OF 1