




Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire.
Propriété de ©BERG ELECTRONICS. Droits de reproduction BERG ELECTRONICS INC.

BERG
ELECTRONICS

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of ©BERG ELECTRONICS Copyright BERG ELECTRONICS INC.

PRODUCT NUMBER
SEE TABLE



mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		BERG ELECTRONICS	
ltr	ecr no	dr	date		.XX $\pm .01 / X \pm .3$		projection		title	
U	REDRAWN	MSC	4/4/88	linear	.XXX $\pm .005 / XX \pm .13$				BERGSTIK® I HEADER	
V	V50357	WDF	6/13/95		.XXXX $\pm .0020 / XXX \pm .051$				.125/3.18cc SR STRAIGHT	
W	S60163	SLOW	15JUL96	angles	0° $\pm 2°$				product family	BERGSTIK
X	S60211	A H	10/15/96	dr	BK CHUA	15JUL96	INCH/MM		size	dwg no
Y	T00045	JSR	2/25/2K	engr	JOYCE PEH	15JUL96	scale		A	65540
				chr	JOYCE PEH	15JUL96	4:1			
				appd	MK KAN	15JUL96				
sheet index	revision sheet	Y	W	W						
		1	2	3						

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire.
Propriété de ©BERG ELECTRONICS. Droits de reproduction BERG ELECTRONICS INC.

BERG
ELECTRONICS

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of ©BERG ELECTRONICS Copyright BERG ELECTRONICS INC.

PRODUCT NUMBER
SEE TABLE

	OVERPLATING	UNDERPLATING	PLASTIC COLOR
-1YY	30u"/0.76u GOLD	50u"/1.27u NICKEL	BLACK
-2YY	15u"/0.38u GOLD	50u"/1.27u NICKEL	CREAM
-3YY	50u"/1.27u GOLD	50u"/1.27u NICKEL	BROWN
-4YY	150u"/3.81u 93/7 TIN LEAD	-----	BLACK
-5YY	15u"/.38u GXT	50u"/1.27u NICKEL	DK BLUE
-6YY	30u"/.76u GXT	50u"/1.27u NICKEL	LT BLUE


OBSOLETE

OBSOLETE

PART NUMBER INFORMATION

PRODUCT BASE NO. XXXXX-YYY
 NUMBER OF POSITIONS NOTE 5
 TERMINAL PLATING

EXAMPLE: 65547-408 DENOTES AN 8 POSITION PART WITH 150u"/3.81u TIN PLATED TERMINALS. THE OVERALL PLASTIC LENGTH MAY BE 1.050/26.67 MAX. (NOTE 6). THE PLASTIC COLOR IS BLACK.



RECOMMENDED HOLE PATTERN

NOTES:

- MOLDING MATERIAL: 20% MIN GLASS FILLED NYLON, RATED PER UL-94V-0.
PIN MATERIAL: 3/4 HARD PHOS BRONZE.
- MEASURED AT DATUM -D- WITH PART IN RESTRAINED CONDITION.
- 5 LBS/ 2.3 KGS MINIMUM TERMINAL PUSH-OUT FORCE IN EITHER DIRECTION.
- BERG LOGO MAY APPEAR ON THIS SURFACE.
- MIN NO. OF POSITIONS = 1.
MAX NO. OF POSITIONS = 36.
- .060/1.52 MAX AS MOLDED (MOLDED AS 36 POS. ONLY).
.085/2.16 MAX WHEN BROKEN TO SPECIFIED LENGTHS.
- .020/0.51 MAX FLASH AROUND PIN IN THIS AREA.
- TWO SIDES OF LEAD-IN ON PINS NOT PLATED.
TYPICAL BOTH SIDES.

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		BERG ELECTRONICS	
ltr	ecn no	dr	date	linear	.XX ± .01 / X ± .3	projection	title		
v					.XXX ± .005 / XX ± .13		BERGSTIK® 1 HEADER		
w				angles	.XXX ± .0020 / XXX ± .051		.125/3.18cc SR STRAIGHT		
				dr	BK CHUA 15JUL.96	INCH/MM	product family		code
				enrg	JOYCE PEH 15JUL.96	scale	size		sheet
				chr	JOYCE PEH 15JUL.96		dwg no		2 of
				appd	MK KAN 15JUL.96		A 65540		
sheet index	revision	sheet	1					cage code	4
								22526	

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite
 sous quelque forme que ce soit sans autorisation écrite du propriétaire.
 Propriété de ©BERG ELECTRONICS. Droits de reproduction BERG ELECTRONICS INC.

BERG
ELECTRONICS

All rights strictly reserved. Reproduction or issue to third parties in any form
 whatever is not permitted without written authority from the proprietor.
 Property of ©BERG ELECTRONICS Copyright BERG ELECTRONICS INC.

PRODUCT		TOTAL PIN LENGTH		TAIL LENGTH		MATING LENGTH		AVAILABLE PLATING					
NUMBER	DIM A	DIM A	DIM B	DIM B	DIM C	DIM C		-1YY	-2YY	-3YY	-4YY	-5YY	-6YY
65540-XY	0.525	13.34	0.195	4.95	0.230	5.84		YES	YES	YES	YES	NO	NO
65541-XY	0.825	20.96	0.495	12.57	0.230	5.84		YES	YES	YES	YES	NO	NO
65542-XY	0.425	10.80	0.095	2.41	0.230	5.84		YES	YES	YES	YES	NO	NO
65543-XY	0.615	15.62	0.285	7.24	0.230	5.84		YES	YES	YES	YES	NO	NO
65544-XY	0.730	18.54	0.400	10.16	0.230	5.84		YES	YES	YES	YES	NO	NO
65545-XY	0.965	24.51	0.635	16.13	0.230	5.84		YES	YES	YES	YES	NO	NO
65546-XY	1.025	26.04	0.695	17.65	0.230	5.84		YES	YES	YES	YES	NO	NO
65547-XY	0.450	11.43	0.120	3.05	0.230	5.84		YES	YES	YES	YES	NO	NO
65548-XY	0.480	12.19	0.150	3.81	0.230	5.84		YES	YES	YES	YES	NO	NO
65549-XY	0.580	14.73	0.250	6.35	0.230	5.84		YES	YES	YES	YES	NO	NO
65550-XY	0.655	16.64	0.325	8.26	0.230	5.84		YES	YES	YES	YES	NO	NO
65551-XY							- N O T	A V A I L A B L E					
65552-XY							- N O T	A V A I L A B L E					
65553-XY	1.155	29.34	0.825	20.96	0.230	5.84		YES	YES	YES	YES	NO	NO
65623-XY	0.855	21.72	0.455	11.56	0.300	7.62		YES	YES	YES	YES	NO	NO
65634-XY	0.615	15.62	0.215	5.46	0.300	7.62		YES	YES	YES	YES	NO	NO
65635-XY	0.525	13.34	0.107	2.72	0.318	8.08		YES	YES	YES	YES	NO	NO
65636-XY	0.673	17.09	0.120	3.05	0.453	11.51		YES	YES	YES	YES	NO	NO
65957-XY	0.650	16.51	0.232	5.89	0.318	8.08		YES	YES	YES	YES	NO	NO
65963-XY	0.945	24.00	0.615	15.62	0.230	5.84		YES	YES	YES	YES	NO	NO
66487-XY							- N O T	A V A I L A B L E					
67899-XY							- N O T	A V A I L A B L E					
68698-XY							- N O T	A V A I L A B L E					
68699-XY	0.861	21.87	0.461	11.71	0.300	7.62		YES	YES	YES	YES	NO	NO
68700-XY							- N O T	A V A I L A B L E					
68701-XY							- N O T	A V A I L A B L E					

OBSOLETE OBSOLETE

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		BERG ELECTRONICS	
lir	ecn no	dr	date	linear	.XX ±.01/.X ±.3			projection INCH/MM	title BERGSTIK® I HEADER .125/3.18cc SR STRAIGHT		
V					.XXX ±.005/.XX ±.13						
W					.XXXX ±.0020/.XXX ±.051						
					° ±2'						
				angles					product family BERGSTIK size dwg no A 65540 sheet 3 of		
				dr	BK CHUA	15JUL96					
				enrg	JOYCE PEH	15JUL96					
				chr	JOYCE PEH	15JUL96					
				appd	MK KAN	15JUL96		scale 1:1	cage code 22526		
sheet index	revision sheet										