

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19 .

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

AF

50

P

LTR

DESCRIPTION

DATE

DWN

APVD

A



REL PER 0G1A-0348-98

10/2/98



JR

SH


- 1 CONTINUOUS STRIP ON REELS.
- 2 WIRE SIZE [#20-#16] AWG.
- 3 INSULATION RANGE 1.52-2.54
[.060-.100] DIA.
- 4 MATING TAB THK 0.51 ± 0.025
[.020±.001].



VIEW A-A
SCALE 10:1



SECTION B-B
SCALE 10:1



SECTION C-C
SCALE 10:1

1217102-1

PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN JR RUTH 7/27/98

CHK MS FEHER 7/27/98

APVD G YETTER 7/27/98

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

AMPAMP Incorporated
Harrisburg, PA 17105-3608NAME
RECEPTACLE, FASTON,
2.79 [.110] SERIES

SIZE

CAGE CODE

DRAWING NO


RESTRICTED TO

A300779 C- 1217102

SCALE 5:1

SHEET 1 OF 1

REV A

DIMENSIONS:
MM [INCHES]TOLERANCES UNLESS
SPECIFIED OTHERWISE

0 PLC	±-
1 PLC	±-
2 PLC	±0.25 [.010]
3 PLC	±-
4 PLC	±-
ANGLES	±-

MATERIAL

082 C.R.STEEL

FINISH

0.00381 [.000150]

MIN NICKEL