




B	CHARACTERISTICS		ELECTRICAL DATA		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE: ☒ US (inch) CUSTOMARY ☐ SI (mm) METRIC NO PLACE X ±.040 ±1 ONE PLACE .X ±.030 ±0,4 TWO PLACE .XX ±.015 ±0,15 THREE PLACE .XXX ±.005 ± ANGLES ± 3° ± RAW MATERIAL-COMMERCIAL STANDARD			DRAWN	TRF	23JAN02	Honeywell Sensing and Control				B	
	OPERATING FORCE----- 46 GRAMS MAX		CONTACT ARRANGEMENT S P D T					CHECK	SAV	23JAN02						
A	RELEASE FORCE----- 6 GRAMS MIN		L156 11A 1/3HP 125, 250 OR 277 VAC 1/2A 125 VDC, 1/4A 250 VDC 4A 125 VAC "L" 		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL SENSING AND CONTROL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE							A	
	DIFFERENTIAL TRAVEL----- .123 MAX							SWITCH, BASIC								
	OVERTRAVEL----- .163 MIN							SIZE	DWG TYPE	DRAWING NAME				REV		
	RELEASE TRAVEL----- .044 MIN							B	I	V7-7B17D8-140				1		
				THIRD ANGLE PROJECTION			DIMENSIONS ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED									
							PTC 2D		ASME Y14.5M-1994		SCALE 2 : 1		WEIGHT		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V7-7B17D8-140](#)