




10 9 8 7 6 5 4 3 2 1

F


E

D

C

B


A




8 CKT.




12 CKT.



9 CKT.




13 CKT.



10 CKT.



14 CKT.





11 CKT.




15 CKT.

極数の種類

KIND OF CKT. NO. (FRONT VIEW)




SECTION Y-Y



基板パターンレイアウト (参考)

RECOMMENDED P.C.B. PATTERN LAYOUT (REF.)



REVISED EC NO.: J2013-0870 DRWN: KAWASHIO CHKD: KASAKAWA APPR: Y01 ITO	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION						
		10 UNDER	± 0.2	T. MIYAZAKI	2006/08/28	TITLE 1.25 W/B CONN. SINGLE S/T REC. ASS'Y 8-15CKT.								
		10 OVER 30 UNDER	± 0.25	K. ASAKAWA	2006/08/28									
		30 OVER	± 0.3	Y01 ITO	2006/08/28	molex								
		ANGULAR ±3 °		MATERIAL NO.							DOCUMENT NO.			SHEET NO.
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE							SD-502382-002			2 OF 3
				SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

[illegible]

