

PRODUCT NUMBER
5 5 1 0 2 - X X X - X X - X X X X

PLATING
S=15μ"[0.38μm]GOLD
ON CONTACT AREA
100μ"[2.54μm]TIN
ON TAIL (NOTE 14)
G=30μ"[0.76μm]GOLD
ON CONTACT AREA
100μ"[2.54μm]TIN
ON TAIL (NOTE 14)
T=100μ"[2.54μm]TIN
ON CONTACT AREA
AND ON TAIL
(SEE NOTE 9 & 13)
F=2μ"[0.05μm]GOLD
ON CONTACT AREA
AND ON TAIL

PIN	STYLE	POST	TAIL
11		0.230/5.84	0.090/2.29
17		0.230/5.84	0.120/3.05
12		0.230/5.84	0.190/4.83
34		0.318/8.08	0.100/2.54
35		0.318/8.08	0.120/3.05
36		0.318/8.08	0.200/5.08



RETENTION
R= RETENTIVE LEG
NOTE 6
POLARIZATION
NOTE 7
POSITIONS PER ROW
01 TO 36

LEAD FREE PRODUCT NUMBER
5 5 1 0 2 - X X X X X X X X X X LF


PLATING
S=15μ"[0.38μm]GOLD
ON CONTACT AREA
100μ"[2.54μm]TIN
ON TAIL (NOTE 14)
G=30μ"[0.76μm]GOLD
ON CONTACT AREA
100μ"[2.54μm]TIN
ON TAIL (NOTE 14)
T=100μ"[2.54μm]TIN
ON CONTACT AREA
AND ON TAIL
(NOTE 9 & 13)
F=2μ"[0.05μm]GOLD
ON CONTACT AREA
AND ON TAIL
9=1μ [0.03μm]GOLD
ON CONTACT AREA
AND ON TAIL (FULL PLATING)

PIN	STYLE	POST	TAIL
11		0.230/5.84	0.090/2.29
17		0.230/5.84	0.120/3.05
12		0.230/5.84	0.190/4.83
34		0.318/8.08	0.100/2.54
35		0.318/8.08	0.120/3.05
36		0.318/8.08	0.200/5.08
40		0.559/14.21	0.090/2.30


RETENTION
R= RETENTIVE LEG
NOTE 6
POLARIZATION
NOTE 7
POSITIONS PER ROW
01 TO 36
PACKAGE:
SEE NOTES 5



mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family BERGSTIK			
ltr	ecn no	dr	date	tolerances unless otherwise specified		scale 1:1	title .100 SHROUNDED HDR D/R R/A THRU HOLE			
G	M06-0268	MHT	7/17/06	angles	linear					
H	M06-0435	MHT	10/31/06		.XX±.01/.X±0.3					
J	M08-0237	MHT	8/25/08		.XXX±.005/.XX±0.13					
K	M08-0279	MHT	9/30/08	dr	D.INGRAM	05/20/99	Amphenol FCI	dwg no		sheet 1 of 2
L	ELX-N-30083	MZ	05/04/18	enr	H.SUNDY	07/21/99		55102		A3
				chr	H.SUNDY	07/21/99		type		Product Customer
				appd	H.SUNDY	07/21/99		Drawing		
sheet index	revision sheet	L	L	1	2					



TAPE AND REEL FOR 2X3



NOTES:

- ① HOUSING MAT'L: HIGH TEMPERATURE THERMOPLASTIC.
FLAME RETARDANT PER UL 94V-0
COLOR: BLACK
OR
MINERAL FILLED LCP
FLAME RETARDANT PER UL 94V-0
COLOR: BLACK
- ② PIN MATERIAL: PHOSPHOR-BRONZE
- ③ TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS PER ROW.
EXAMPLE: 10 POS., N x .100[2.54]=1.00[25.40].
- ④ 2LBS/0.9KG MIN. PIN RETENTION IN EITHER DIRECTION
5. PACKAGE:
NONE =IN POLY BAGS
T =TRAY WITHOUT PICK UP CAP
A =TAPE AND REEL WITHOUT PICK UP CAP
- ⑥ RETENTIVE LEG APPLICABLE TO TAIL LENGTH .120/3.05 ONLY.
5LB/2.3KG MAX INSERTION FORCE AND .25LB./1KG MIN RETENTION FORCE
PER RETENTIVE PIN USING .062/1.57 THICK CIRCUIT BOARD AND RECOMMENDED
HOLE PATTERN. RETENTIVE LOCATION AT THE DISCRETION OF THE MANUFACTURER.
OMIT FROM PRODUCT NUMBER IF THIS FEATURE IS NOT APPLICABLE.
- ⑦ FOR POLARIZATION SPECIFY POSITION NUMBER(i.e.. A03=ROW A POS 3)
TO OMIT PIN.
OMIT FROM PRODUCT NUMBER IF THIS FEATURE IS NOT APPLICABLE.
8. UNDERPLATING: 50μ"/1.27μm Ni.
9. PIN TIPS ON Sn PLATED PRODUCT MAY HAVE BARE METAL ON
TWO SIDES, BOTH ENDS.
- ⑩ PART NUMBERS WITH "LF" SUFFIX AT THE END ARE LEAD FREE.
- ⑪ THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
12. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 20 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW
OVEN. SEE APPLICATION NOTES/PROCEDURES IF THEY ARE AVAILABLE OR
FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5mm
MINIMUM THICK CIRCUIT BOARD.
- ⑬ "THIS PRODUCT HAS 100% PURE TIN PLATING IN THE INTERFACE AND
HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT
ENVIRONMENTS."
- ⑭ PLATING OPTIONS:
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.

[illegible]