



Capacitors for Power Factor Correction

Series/Type: **MKK-525-I-10-01**

The following products presented in this data sheet are being withdrawn.

Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B25667A5117A175		2004-07-30		

For further information please contact your nearest EPCOS sales office, which will also support you in selecting a suitable substitute. The addresses of our worldwide sales network are presented at www.epcos.com/sales.

Characteristics

C_N	1x 116 $\mu\text{F} \pm 5 \%$	
U_N	AC 525 V	
f_N	50 Hz	60 Hz
Q_N	10 kvar	12 kvar
I_N	1x 19 A	23 A

$\tan \delta_0$ 0,2 W/kvar (dielectric)

Maximum ratings

$U_{\max}$	AC 580 V, 8 h daily AC 680 V, 1 min
$I_{r(40)}$	1x 40 A ($\Theta_A = 40^\circ\text{C}$, U_N)
I_s	5800 A
$(du/dt)_{\max}$	20 V/ μs
$(du/dt)_s$	50 V/ μs

Test data

U_{TT}	AC 1150 V, 10 s
U_{TC}	AC 3000 V, 10 s


$\tan \delta$ (50 Hz) $\leq 0,5$ W/kvar (total)

Climatic category -40/D

$\Theta_{\min}$	-40 °C
$\Theta_{\max}$	+55 °C
Humidity	Max. relative Humidity $\leq 95 \%$
Θ_{stg}	-55 bis +70 °C

Life expectancy

t_{LD}	100 000 h
----------	-----------



Design data

Dimensions $\varnothing \times l$	121,6 x 164 mm (4,79 x 6,46 in)
Approx. weight	1,3 kg (2,9 lb)
Impregnation	Gas
Fixing	Threaded bolt M12
Mounting hole	14 mm (0,55 in)
Max. torque	10 Nm
Terminals	Isolated terminal, IP20
Max. torque	1,2 Nm
Terminal cross section	16 mm ² (5 AWG)
Creepage distance	12,7 mm (0,50 in)
Clearance	9,6 mm (0,38 in)
Overpressure disconnecter	
Any mounting position possible	

Remarks

Natural cooling