



Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO.	ROWS	POWER				SIGNAL				POWER					E2	
		E1	P1	P2	P3	1	2	3	4	P4	P5	P6	P7	P8		P9
51730-150-- NOTE 3	D C B A		PA	PA	PA	UUUU	TTTT	SSSS	RRRR	PA	PA	PA	PA	PA	PA	
		UU	UU	UU	UU	UU	UU	UU	UU	UU	UU	UU	UU	UU	UU	UU



CODE	DIM "M" MATING LENGTH	CONTACT TYPE
U	[6.86]	SIGNAL
T	[6.86]	SIGNAL
S	[6.86]	SIGNAL
R	[6.86]	SIGNAL
PA	[N/A]	POWER
HA	[N/A]	HOLD-DOWN
E	[5.59]	SIGNAL

mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER	 www.fciconnect.com	
ltr	ecn no.	dr	date			linear	0.X ±0.3	COPY		
A	DG08-0209	JW	07/30/08				0.XX ±0.13	projection		
						angles	0.XXX ±0.051			
							0° ±2°		title 3P + 16S + 6P RIGHT ANGLE SOLDER HEADER	
						dr	JULIA WANG 07/30/08			
						enr	JEROME CHEN 07/30/08		product family PwrBlade	
						chr	GARY HSIEH 07/30/08	size	dwg no	code
						appd	JOSEPH HSIA 07/30/08	A	51730-150	213
sheet index	revision sheet	A	A	A	A			scale		sheet
		1	2	3	4			1:1		1 of 4

Pro/E




cage code
22526

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51730-150-
NOTE: 3



mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date					COPY		www.fciconnect.com	
A				linear		0.X ±0.3		projection		title 3P + 16S + 6P	
						0.XX ±0.13				RIGHT ANGLE SOLDER HEADER	
				angles		0.XXX ±0.051				product family PwrBlade	
				dr	JULIA WANG	07/30/08				code	213
				enrg	JEROME CHEN	07/30/08				size	dwg no
				chr	GARY HSIEH	07/30/08				51730-150	
				appd	JOSEPH HSIA	07/30/08				sheet	2 of 4
sheet index	revision sheet							scale 1:1			

cage code 22526

Pro/E

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

[illegible]

cage code	22526
-----------	-------

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51730-150- NOTE: 3

NOTES:

1. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH
ASME Y14.5M, 1994 UNLESS OTHERWISE SPECIFIED.

CONNECTOR NOTES:

2. HOUSING MATERIAL: UL 94 V-0 GLASS FILLED
HIGH-TEMP THERMOPLASTIC
POWER CONTACT MATERIAL: COPPER ALLOY
SIGNAL PIN MATERIAL: COPPER ALLOY
3. 51730-150; 51730-150LF PLATING SPEC. SEE PRINT:10064183
4. MANUFACTURER'S NAME, P/N, AND DATE CODE TO APPEAR ON
THIS SURFACE.
5. PRODUCT SPECIFICATION GS-12-149.
APPLICATION SPECIFICATION BUS-20-067.
6. PACKAGED IN TRAYS.

PCB NOTES:

7. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.
8. MOUNTING HOLES, WHERE APPLICABLE, ARE UNPLATED.
9. $\varnothing 1.151 \pm 0.025$ DRILLED HOLES PLATED WITH
0.008 MIN SnPb OR Sn OVER 0.03
TO 0.08 Cu PLATING TO ACHIEVE
 $\varnothing 1.02 \pm .07$ HOLE.
10. "DIM XXX" TO BE DETERMINED BY THE CUSTOMER.
11. CONNECTOR KEEP-OUT ZONE.

mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com	
ltr	ecn no.	dr	date	linear	0.X ± 0.3		COPY		projection	title			
A					0.XX ± 0.13		projection			3P + 16S + 6P			
					0.XXX ± 0.051		projection			RIGHT ANGLE SOLDER HEADER			
				angles	0° ± 2°		projection		product family			PwrBlade	code
				dr	JULIA WANG	07/30/08	MM		size		dwg no	213	sheet
				enrg	JEROME CHEN	07/30/08	scale		A		51730-150	4 of 4	
				chr	GARY HSIEH	07/30/08	1:1						
				appd	JOSEPH HSIA	07/30/08							
sheet index		revision sheet											

cage code 22526