

## Contact insert - RC-06P1NS20000 - 1593555

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Contact insert, number of positions: 6, type of contact: Pin, Screw connection

RoHS



### Key Commercial Data

|                                      |                                                                                                         |
|--------------------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit                         | 1 pc                                                                                                    |
| GTIN                                 | <br>4 046356 196857 |
| GTIN                                 | 4046356196857                                                                                           |
| Weight per Piece (excluding packing) | 9.810 g                                                                                                 |
| Custom tariff number                 | 85389099                                                                                                |
| Country of origin                    | Germany                                                                                                 |

### Technical data

#### General

|                                                    |                      |
|----------------------------------------------------|----------------------|
| Insertion/withdrawal cycles mechanical             | 50                   |
| Direction of rotation of contact chamber numbering | Standard             |
| Coding                                             | N                    |
| Contact connection method                          | Screw connection     |
| Type of contacts                                   | Pin                  |
| Number of positions                                | 6                    |
| Contact diameter of power contacts                 | 2 mm                 |
| Litz wire cross section of power contacts min.     | 0.08 mm <sup>2</sup> |
| Litz wire cross section of power contacts max.     | 1 mm <sup>2</sup>    |
| Rated current for power contacts                   | 20 A                 |

#### Material

## Contact insert - RC-06P1NS20000 - 1593555

### Technical data

#### Material

|                    |                             |
|--------------------|-----------------------------|
| Insulator material | PBT                         |
| Contact material   | CuZn                        |
| Contact surface    | Nickel-plated, gold coating |

#### Specifications according to DIN EN 61984:2001

|                                               |        |
|-----------------------------------------------|--------|
| Nominal / operating voltage of power contacts | 300 V  |
| Rated surge voltage of power contacts         | 2.5 kV |
| Overvoltage category of power contacts        | II     |
| Degree of pollution of power contacts         | 3      |
| Overvoltage category of signal contacts       | II     |
| Degree of pollution of signal contacts        | 3      |


#### Environmental Product Compliance

|            |                                                                                                     |
|------------|-----------------------------------------------------------------------------------------------------|
| REACH SVHC | Lead 7439-92-1                                                                                      |
| China RoHS | Environmentally Friendly Use Period = 50 years                                                      |
|            | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

### Drawings


## Contact insert - RC-06P1NS20000 - 1593555

Schematic diagram



## Contact insert - RC-06P1NS20000 - 1593555

Schematic diagram



### Classifications

#### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27440205 |
| eCl@ss 4.0    | 27260700 |
| eCl@ss 4.1    | 27260700 |
| eCl@ss 5.0    | 27260700 |
| eCl@ss 5.1    | 27261200 |
| eCl@ss 6.0    | 27261200 |
| eCl@ss 7.0    | 27440205 |
| eCl@ss 8.0    | 27440205 |
| eCl@ss 9.0    | 27440205 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC001121 |
| ETIM 4.0 | EC001121 |

## Contact insert - RC-06P1NS20000 - 1593555

### Classifications

#### ETIM

|          |          |
|----------|----------|
| ETIM 5.0 | EC000438 |
| ETIM 6.0 | EC000438 |
| ETIM 7.0 | EC000438 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 43172015 |
| UNSPSC 7.0901 | 43201404 |
| UNSPSC 11     | 43172015 |
| UNSPSC 12.01  | 43201404 |
| UNSPSC 13.2   | 39121522 |
| UNSPSC 18.0   | 39121522 |
| UNSPSC 19.0   | 39121522 |
| UNSPSC 20.0   | 39121522 |
| UNSPSC 21.0   | 39121522 |

### Approvals

#### Approvals

---

#### Approvals

#### EAC

---

#### Ex Approvals

---

#### Approval details

|     |                                                                                     |         |
|-----|-------------------------------------------------------------------------------------|---------|
| EAC |  | B.01687 |
|-----|-------------------------------------------------------------------------------------|---------|