


► Tournevis PROTWIST® pour vis Torx® et Resistorex®

ANX Pour vis Torx®

- Conformes aux spécifications Torx® .
- Présentation : lame chromée mate, empreinte traitée noire.


	Torx® n°	Ø1 x L1 mm	I★ mm	Ø2 x L2 mm	L mm	ΔΔ g
ANX6X50	T 6	2,5 x 50	1,65	19 x 94	144	20
ANX7X50	T 7	2,5 x 50	1,97	19 x 94	144	20
ANX8X50	T 8	2,5 x 50	2,30	25 x 103	153	35
ANX9X75	T 9	3,0 x 75	2,48	25 x 103	178	45
ANX10X75	T 10	3,0 x 75	2,74	30 x 109	184	50
ANX15X75	T 15	3,5 x 75	3,26	30 x 109	184	61
ANX20X100	T 20	4,0 x 100	3,84	36 x 120	220	67
ANX20X150	T 20	4,0 x 150	3,84	36 x 120	270	73
ANX25X100	T 25	5,0 x 100	4,40	36 x 120	220	113
ANX27X100	T 27	5,5 x 100	4,96	36 x 120	220	113
ANX30X125	T 30	6,0 x 125	5,49	36 x 120	245	126
ANX40X150	T 40	7,0 x 150	6,60	40 x 125	275	173



ANXP Pour vis Torx Plus®

- Conformes aux spécifications Torx Plus®.
- Présentation : lame chromée mate, empreinte traitée noire.

	Torx® n°	I★ mm	Ø1 x L1 mm	Ø2 x L2 mm	L mm	ΔΔ g
ANXP5X50	IP 5	1,42	2,5 x 50	19 x 95	144	20
ANXP6X50	IP 6	1,65	2,5 x 50	19 x 95	144	20
ANXP7X50	IP 7	1,97	2,5 x 50	19 x 95	144	20
ANXP8X50	IP 8	2,30	2,5 x 50	25 x 103	153	35
ANXP9X75	IP 9	2,48	3,0 x 75	25 x 103	178	45
ANXP10X75	IP 10	2,74	3,0 x 75	30 x 109	184	50
ANXP15X75	IP 15	3,26	3,5 x 75	30 x 110	184	61
ANXP20X100	IP 20	3,84	4,0 x 100	36 x 120	220	67
ANXP25X100	IP 25	4,40	5,0 x 100	36 x 120	220	113
ANXP27X100	IP 27	4,96	5,5 x 100	36 x 120	220	113
ANXP30X125	IP 30	5,49	6,0 x 125	36 x 120	245	126
ANXP40X150	IP 40	6,60	7,0 x 150	40 x 125	275	173



ANXR Pour vis Resistorex®

- Conformes aux spécifications Resistorex®.
- Présentation : lame chromée mate, empreinte traitée noire.

	Resistorex® n°	I★ mm	Ø1 x L1 mm	Ø2 x L2 mm	L mm	ΔΔ g
ANXR10X75	TT 10	2,74	3,0 x 75	25 x 109	184	50
ANXR15X75	TT 15	3,26	3,5 x 75	30 x 110	185	61
ANXR20X100	TT 20	3,84	4,0 x 100	36 x 120	220	67
ANXR25X100	TT 25	4,40	5,0 x 100	36 x 120	220	113
ANXR27X100	TT 27	4,96	5,5 x 100	36 x 120	220	113
ANXR30X125	TT 30	5,49	6,0 x 125	36 x 120	245	126
ANXR40X150	TT 40	6,60	7,0 x 150	40 x 125	275	173

