

Silicon Carbide Power Schottky Diode



V_{RRM}	=	3300 V
V_F	=	1.7 V
I_F	=	0.3 A
Q_C	=	52 nC

Features

- 3300 V Schottky rectifier
- 175 °C maximum operating temperature
- Electrically isolated base-plate
- Positive temperature coefficient of V_F
- Fast switching speeds
- Superior figure of merit Q_C/I_F

Package

- RoHS Compliant



SMB / DO – 214AA

Applications

- Down Hole Oil Drilling, Geothermal Instrumentation
- High Voltage Multipliers
- Military Power Supplies

Advantages

- Improved circuit efficiency (Lower overall cost)
- Significantly reduced switching losses compare to Si PiN diodes
- Ease of paralleling devices without thermal runaway
- Smaller heat sink requirements
- Low reverse recovery current
- Low device capacitance

Maximum Ratings at $T_J = 175\text{ °C}$, unless otherwise specified

Parameter	Symbol	Conditions	Values	Unit
Repetitive peak reverse voltage	V_{RRM}		3300	V
Continuous forward current	I_F	$T_C \leq 125\text{ °C}$	0.3	A
RMS forward current	$I_{F(RMS)}$	$T_C \leq 125\text{ °C}$	0.35	A
Surge non-repetitive forward current, Half Sine Wave	$I_{F,SM}$	$T_C = 25\text{ °C}$, $t_p = 10\text{ ms}$ $T_C = 125\text{ °C}$, $t_p = 10\text{ ms}$	2 1	A
Non-repetitive peak forward current	$I_{F,max}$	$T_C = 25\text{ °C}$, $t_p = 10\text{ }\mu\text{s}$	10	A
I^2t value	$\int I^2 dt$	$T_C = 25\text{ °C}$, $t_p = 10\text{ ms}$	0.1	A ² S
Power dissipation	P_{tot}	$T_C = 25\text{ °C}$	25	W
Operating and storage temperature	T_J , T_{stg}		-55 to 175	°C

Electrical Characteristics at $T_J = 175\text{ °C}$, unless otherwise specified

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Diode forward voltage	V_F	$I_F = 0.3\text{ A}$, $T_J = 25\text{ °C}$		1.7	2.2	V
		$I_F = 0.3\text{ A}$, $T_J = 175\text{ °C}$		4.0	5.0	
Reverse current	I_R	$V_R = 3300\text{ V}$, $T_J = 25\text{ °C}$		1	10	μA
		$V_R = 3300\text{ V}$, $T_J = 175\text{ °C}$		10	100	
Total capacitive charge	Q_C	$I_F \leq I_{F,MAX}$ $dI_F/dt = 35\text{ A}/\mu\text{s}$ $T_J = 175\text{ °C}$		52		nC
Switching time	t_s	$V_R = 1500\text{ V}$		< 60		ns
Total capacitance	C	$V_R = 1\text{ V}$, $f = 1\text{ MHz}$, $T_J = 25\text{ °C}$		42		pF
		$V_R = 400\text{ V}$, $f = 1\text{ MHz}$, $T_J = 25\text{ °C}$		8		
		$V_R = 1000\text{ V}$, $f = 1\text{ MHz}$, $T_J = 25\text{ °C}$		7		

Thermal Characteristics

Thermal resistance, junction – Cu lead frame	R_{thJC}	1.42	°C/W
--	------------	------	------




Figure 1: Typical Forward Characteristics




Figure 2: Typical Reverse Characteristics





Figure 3: Power Derating Curve



**Figure 4: Current Derating Curves ($D = t_p/T$, $t_p = 400 \mu s$)
(Considering worst case Zth conditions)**




Figure 5: Typical Junction Capacitance vs Reverse Voltage Characteristics







Figure 6: Typical Switching Energy vs Reverse Voltage Characteristics


Figure 7: Current vs Pulse Duration Curves at $T_c = 150\text{ }^{\circ}\text{C}$

Figure 8: Transient Thermal Impedance
Package Dimensions:
SMB / DO-214AA
PACKAGE OUTLINE


Dimensions	Inches		Millimeters	
	Min	Max	Min	Max
A	0.077	0.086	1.950	2.200
B	0.160	0.180	4.060	4.570
C	0.130	0.155	3.300	3.940
D	0.084	0.096	2.130	2.440
E	0.030	0.060	0.760	1.520
F	-	0.008	-	0.203
G	0.205	0.220	5.210	5.590
H	0.006	0.012	0.152	0.305
I	0.089	-	2.260	-
J	0.085	-	2.160	-
K	-	0.107	-	2.740
L	0.085	-	2.160	-

NOTE

1. CONTROLLED DIMENSION IS INCH. DIMENSION IN BRACKET IS MILLIMETER.
2. DIMENSIONS DO NOT INCLUDE END FLASH, MOLD FLASH, MATERIAL PROTRUSIONS
3. CONTROLLED LEAD COPLANARITY $<D> 0.004$ INCH MAXIMUM

Revision History			
Date	Revision	Comments	Supersedes
2013/11/12	1	Updated Electrical Characteristics	
2013/09/09	0	Initial Release	

Published by
GeneSiC Semiconductor, Inc.
43670 Trade Center Place Suite 155
Dulles, VA 20166

GeneSiC Semiconductor, Inc. reserves right to make changes to the product specifications and data in this document without notice.

GeneSiC disclaims all and any warranty and liability arising out of use or application of any product. No license, express or implied to any intellectual property rights is granted by this document.

Unless otherwise expressly indicated, GeneSiC products are not designed, tested or authorized for use in life-saving, medical, aircraft navigation, communication, air traffic control and weapons systems, nor in applications where their failure may result in death, personal injury and/or property damage.

SPICE Model Parameters

Copy the following code into a SPICE software program for simulation of the GAP3SLT33-214 device.

```
*      MODEL OF GeneSiC Semiconductor Inc.
*
*      $Revision:   1.0           $
*      $Date:      09-SEP-2013   $
*
*      GeneSiC Semiconductor Inc.
*      43670 Trade Center Place Ste. 155
*      Dulles, VA 20166
*      http://www.genesicsemi.com/index.php/sic-products/schottky
*
*      COPYRIGHT (C) 2013 GeneSiC Semiconductor Inc.
*      ALL RIGHTS RESERVED
*
* These models are provided "AS IS, WHERE IS, AND WITH NO WARRANTY
* OF ANY KIND EITHER EXPRESSED OR IMPLIED, INCLUDING BUT NOT LIMITED
* TO ANY IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A
* PARTICULAR PURPOSE."
* Models accurate up to 2 times rated drain current.
*
* Start of GAP3SLT33-214 SPICE Model
*
.SUBCKT GAP3SLT33 ANODE KATHODE
R1 ANODE INT R=((TEMP-24)*0.0535); Temperature Dependant Resistor
D1 INT KATHODE GAP3SLT33_25C; Call the 25C Diode Model
D2 ANODE KATHODE GAP3SLT33_PIN; Call the PiN Diode Model
.MODEL GAP3SLT33_25C D
+ IS      1.39E-14      RS      2.88
+ N       1.0120127     IKF     36.05007504
+ EG      1.2           XTI     -3
+ CJO     6.01E-11      VJ      0.924257443
+ M       0.3084545     FC      0.5
+ TT      1.00E-10      BV      3300
+ IBV     1.00E-03      VPK     3300
+ IAVE    3.00E-01      TYPE    SiC_Schottky
+ MFG     GeneSiC_Semiconductor
.MODEL GAP3SLT33_PIN D
+ IS      178.99E-18    RS      15
+ N       5             EG      3.23
+ XTI     50           FC      0.5
+ TT      0            BV      3300
+ IBV     1.00E-03      VPK     3300
+ IAVE    3.00E-01      TYPE    SiC_PiN
.ENDS
* End of GAP3SLT33-214 SPICE Model
```