




Rx Series Diagonal cutters Oval head, RX 8130-RX 8162

These cutters are made from high performance ball bearing steel, black oxidised. Numerically controlled machine grinding guarantees edge angle accuracy and contact which increases the tools reliability and consistency.

Precision induction hardened edges 63-65 HRC. Handles in two component synthetic material and come with return spring. The cutting capacity that is given is for copper wire!

These Oval Head cutters are ideal for wire harness work and standard printed circuit board assembly.



	 731415+		A mm	B mm	C mm	D mm	F mm				
RX 8130	0103003	1	133.5	8.5	8.0	5	0.8	0.2-1.0	Micro		68
RX 8131	0103010	1	133.5	8.5	8.0	5	0.8	0.1-1.0	Flush		68
RX 8132	0103027	1	133.5	8.5	8.0	5	0.8	0.1-0.8	Ultra		68
RX 8140	0103034	1	135.5	10.5	10.0	6	0.8	0.2-1.25	Micro		70
RX 8141	0103041	1	135.5	10.5	10.0	6	0.8	0.1-1.25	Flush		70
RX 8142	0103058	1	135.5	10.5	10.0	6	0.8	0.1-1.0	Ultra		70
RX 8150	0103133	1	138.0	13.0	12.5	6	1.2	0.3-1.6	Micro		73
RX 8151	0103140	1	138.0	13.0	12.5	6	1.2	0.2-1.6	Flush		73
RX 8152	0103157	1	138.0	13.0	12.5	6	1.2	0.2-1.25	Ultra		73
RX 8160	0111534	10	147.0	16.0	16.0	8	1.6	0.4-2.0	Micro		97
RX 8161	0111541	10	147.0	16.0	16.0	8	1.6	0.3-2.0	Flush		97
RX 8162	0111558	10	147.0	16.0	16.0	8	1.6	0.3-1.6	Ultra		97