

SMT & THROUGH-HOLE BOARD STACKERS

(2.00 mm) .0787" PITCH • TW SERIES

CLT or MMS	SQT
8	4
G b p s	G b p s

TW

Board Mates:

CLT, SQT, SQW, ESQT,
TLE, SMM, MMS

Cable Mates:

TCSD

SPECIFICATIONS

Insulator Material:

Black Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Sn or Au over
50 μ " (1.27 μ m) Ni

Current Rating:

TW-SM = 4.9 A per pin
(2 pins powered)

TW-TH = 5.2 A per pin
(2 pins powered)

Operating Temp Range:

-55 °C to +105 °C with Tin;
-55 °C to +125 °C with Gold

PROCESSING



Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0.15 mm) .006" max*

*(.004" stencil solution
may be available; contact
ipg@samtec.com)

TW	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	STACKER HEIGHT	SM	OTHER OPTION																					
	02 thru 36	Specify LEAD STYLE from chart	-F = Gold flash on post, Matte Tin on tail	-S = Single Row -D = Double Row	-“XXX” = Stacker Height in inches (0.13 mm) .005" increments Example: -250 = (6.35 mm) .250"		-“XXX” = Polarized Position -A = Alignment Pin (Metal or plastic at Samtec discretion) (4.83 mm) .190" min. board space (-D only) -P = Pick & Place Pad (1.91 mm) .075" min. post height (04-36 only)																					
			<table><thead><tr><th>LEAD STYLE</th><th>OAL</th></tr></thead><tbody><tr><td>-02</td><td>(7.85) .309</td></tr><tr><td>-03</td><td>(11.86) .467</td></tr><tr><td>-04</td><td>(12.37) .487</td></tr><tr><td>-06</td><td>(15.37) .605</td></tr><tr><td>-07</td><td>(17.35) .683</td></tr><tr><td>-09</td><td>(9.86) .388</td></tr></tbody></table>		LEAD STYLE	OAL	-02	(7.85) .309	-03	(11.86) .467	-04	(12.37) .487	-06	(15.37) .605	-07	(17.35) .683	-09	(9.86) .388	<table><thead><tr><th>ROW OPTION</th><th>A</th></tr></thead><tbody><tr><td>-S</td><td>(5.08) .200</td></tr><tr><td>-D</td><td>(6.35) .250</td></tr></tbody></table>		ROW OPTION	A	-S	(5.08) .200	-D	(6.35) .250		
LEAD STYLE	OAL																											
-02	(7.85) .309																											
-03	(11.86) .467																											
-04	(12.37) .487																											
-06	(15.37) .605																											
-07	(17.35) .683																											
-09	(9.86) .388																											
ROW OPTION	A																											
-S	(5.08) .200																											
-D	(6.35) .250																											
					-A OPTION	-P OPTION																						

TW	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	STACKER HEIGHT	TAIL SPEC																																			
	02 thru 50	Specify LEAD STYLE from chart	-F = Gold flash on post, Matte Tin on tail	-S = Single Row -D = Double Row -T = Triple Row -Q = Four Row -5 = Five Row -6 = Six Row	-“XXX” = Stacker Height in inches (0.13 mm) .005" increments Example: -250 = (6.35 mm) .250"	-“XXX” = Tail Length in inches (0.13 mm) .005" increments Example: -150 = (3.81 mm) .150" -“XXX” = Polarized Position (Specify position to be removed)																																			
-S, -D*, -Q -T, -5, -6			<table><tr><th>LEAD STYLE</th><th>OAL</th></tr><tr><td>-01</td><td>(8.20) .323</td></tr><tr><td>-02</td><td>(9.60) .377</td></tr><tr><td>-03</td><td>(13.60) .535</td></tr><tr><td>-04</td><td>(14.10) .555</td></tr><tr><td>-05</td><td>(15.10) .594</td></tr><tr><td>-06</td><td>(17.10) .673</td></tr><tr><td>-07</td><td>(19.10) .751</td></tr><tr><td>-08*</td><td>(21.10) .830</td></tr><tr><td>-09</td><td>(11.60) .456</td></tr><tr><td>-10</td><td>(15.60) .614</td></tr><tr><td>-11</td><td>(10.08) .397</td></tr><tr><td>-12*</td><td>(28.19) 1.110</td></tr></table>			LEAD STYLE	OAL	-01	(8.20) .323	-02	(9.60) .377	-03	(13.60) .535	-04	(14.10) .555	-05	(15.10) .594	-06	(17.10) .673	-07	(19.10) .751	-08*	(21.10) .830	-09	(11.60) .456	-10	(15.60) .614	-11	(10.08) .397	-12*	(28.19) 1.110	<table><tr><th>ROW OPTION</th><th>STACKER HEIGHT</th></tr><tr><td>-S, -D*, -Q</td><td>(3.05) .120 MIN</td></tr><tr><td>-T, -5, -6</td><td>(4.06) .160 MIN</td></tr></table>		ROW OPTION	STACKER HEIGHT	-S, -D*, -Q	(3.05) .120 MIN	-T, -5, -6	(4.06) .160 MIN	*-D with stacker height greater than (4.06 mm) .160" will not have standoffs.	
LEAD STYLE	OAL																																								
-01	(8.20) .323																																								
-02	(9.60) .377																																								
-03	(13.60) .535																																								
-04	(14.10) .555																																								
-05	(15.10) .594																																								
-06	(17.10) .673																																								
-07	(19.10) .751																																								
-08*	(21.10) .830																																								
-09	(11.60) .456																																								
-10	(15.60) .614																																								
-11	(10.08) .397																																								
-12*	(28.19) 1.110																																								
ROW OPTION	STACKER HEIGHT																																								
-S, -D*, -Q	(3.05) .120 MIN																																								
-T, -5, -6	(4.06) .160 MIN																																								
			*Style -08 & -12 = S & D only																																						

Notes:

For added mechanical stability, Samtec recommends mechanical board spacers be used in applications with gold or selective gold plated connectors. Contact ipg@samtec.com for more information.

This Series is non-standard, non-returnable.