



DO NOT SCALE

DIMENSIONS IN mm

THIRD ANGLE

PROJECTION





NOTES:

- 1 PHOSPHORBRONZE # 4 HD / THICKNESS 0,8mm
- 2 2,54µm Sn OVER
1,25µm MIN. NICKEL.
- 3 PLATING: UNDERLAYER; 1,25µm min. NICKEL
- 4 PLATING: 1.25 µm min. NICKEL OVER ALL
- ZONE X ; 3µm Ag MIN.
ZONE Y ; 2,54µm-5,00µm Sn
ZONE X ; 1 - 3µm SN

J2

P.C.B. HOLE DIM. ACTION PIN

DRILLED HOLE	:1,6	±0,025	mm
FIN. HOLE	:1,39	+0,15 -0,0	mm
AFTER REFLOW	:1,37	+0,15 -0,0	mm
Cu-thks	:0,025	to 0,075	mm
Sn-thks or SnPb-thks	:0,004	to 0,010	mm



OBSOLETE

4	216842-5	J
3	216842-4	J
2	216842-2	J
FINISH	MATERIAL	PARTNUMBER
Rev		

CUSTOMER
DRAWING



TE Connectivity

J4	ECR-16-012935	BW	RS	20SEP2016
REV.	ECN No.	DRW.	APVD	DATE
LTR.				

REVISION RECORD

DR.	DATE
J.v.LIEMPT.	02.01.90
CHK.	DATE
A. BIJNEN	30-11-01
APP.	DATE
A. BIJNEN	30-11-01

WIRE RANGE

INSUL. RANGE

SIZE
A3

NAME

INSUL. RANGE

SHEET
1 OF 1

.250 SRS TAB WITH ACTION-PIN
FOR POSITIVE LOCK RECEPTACLE
(FOR 1,6-3,2 PC.B. THICKNESS)

DWG. No.

C-216842

REV. DATE
D M Y

30 11 01

REV. LTR.
J4

8

7

6

5

4

3

2

1