


FLAT WASHERS



Tolerances	
A =	+.020 -.005
B =	±.010
C =	±.003 up to .032 thick ±.006 .033 to .062 thick ±.009 .063 to .093 thick ±.010 for .094 and over

Tighter tolerances for the A, B, & C dimensions can be provided. See order example.

Color	Code	Recommended Thickness "C"	
Natural	1	.010	.125
Black	2	.015	.156
Red	3	.020	.187
Blue	4	.030	.250
Purple	5	.040	.312
Brown	6	.045	.375
Orange	7	.060	.437
Green	8	.062	.500
Yellow	9	.093	

ORDER EXAMPLE:

155 - .015 - S - 1

Basic Part Number C Thickness: See chart or fill in any length Material: See chart Finish: See page 278

EXAMPLE FOR NYLON AND DELRIN PARTS: 155-015-N-2 ← BLACK
Choose color from chart, otherwise Natural is provided.
If a different tolerance and/or dimension change is required, add to part number.
EXAMPLE: 155-.015-S-1 (A = .375 ± .005)

Available Material (see page 276)

A	Aluminum	Ph	Phenolic (Paper)
B	Brass	Phl	Phenolic (Linen)
C	Copper	L	Polycarbonate(Lexan)
S	Steel	PA	A.B.S.
SS	Stainless Steel	PP	P.V.C.
N	Nylon	T	Teflon
D	Delrin	F	Fibre
GM	Glass Melamine G 5	GE	Glass Epoxy G10
GS	Glass Silicone G 7	UL*	ULTEM 1000

* ULTEM 1000 - UL Rating 94V-0

Screw Size	B ID	A OD	Basic Part No.	C Thickness	Material	Finish	Screw Size	B ID	A OD	Basic Part No.	C Thickness	Material	Finish
10	.195	.437	155				1/4	.222	1.500	207			
	.196	.375	166					.251	.329	208			
	.196	.437	167					.252	.420	209			
	.196	.750	168					.252	.450	9745			
	.198	.683	169					.252	.500	211			
	.199	.312	171					.252	.592	212			
	.199	.500	172					.252	.752	213			
	.199	.750	173					.253	.470	214			
	.199	1.500	174					.253	.562	215			
	.200	.325	176					.253	.878	216			
	.200	.359	177					.254	.400	217			
	.200	.500	179					.254	.622	218			
	.201	.460	181					.254	1.063	219			
	.202	.632	182					.255	.340	220			
	.203	.309	183					.255	.375	221			
	.203	.375	184					.255	.481	222			
	.203	.437	187					.255	.505	223			
	.203	.469	188					.255	1.062	224			
12	.209	.438	160					.256	.695	225			
	.219	.390	189					.257	.410	226			
	.219	.443	191					.257	.620	227			
	.220	.365	192					.257	.694	228			
	.220	.635	193					.257	1.125	229			
	.221	.468	196					.258	.318	230			
	.222	.300	198					.258	.747	231			
	.222	.372	210					.258	1.443	232			
	.222	.500	202					.259	.875	233			
	.222	.730	203					.260	.300	234			
	.222	1.000	204					.260	.400	235			
	.222	1.130	206					.260	.473	236			