



Product: [1613A](#)

CATV Video, RG6, 18 AWG BCCS, Tri Shield, CM PVC Jacket



Product Description

CATV, Series 6, 18 AWG solid .040" bare copper-covered steel conductor, gas-injected foam polyethylene insulation, Duobond® III, aluminum braid shield (77% coverage), CM PVC jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
18	Solid	BCCS - Bare Copper Covered Steel	0.04 in	1

Conductor Count:

1

Insulation

Material	Nominal Diameter
PE - Polyethylene (Foam)	0.18 in

Insulation Table Notes:

Gas Injected

Outer Shield

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
Braid	2	Aluminum		77%
Tape	3	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%

Outer Jacket

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.275 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR	Outer Conductor DCR
28 Ohm/1000ft	5.6 Ohm/1000ft	5.6 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
16.2 pF/ft

Inductance

Nominal Inductance
0.097 µH/ft

Impedance

Nominal Characteristic Impedance	Nominal Characteristic Tolerance
75 Ohm	± 3 Ohm

Return Loss

Frequency [MHz]	Min. Structural Return Loss (SRL)
5 - 1002 MHz	20 dB
1002 - 2250 MHz	15 dB
2250 - 3000 MHz	10 dB

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.2 ns/ft	83%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)
5 MHz	0.58 dB/100ft
55 MHz	1.60 dB/100ft
211 MHz	3.05 dB/100ft
270 MHz	3.37 dB/100ft
300 MHz	3.55 dB/100ft
350 MHz	3.85 dB/100ft
400 MHz	4.15 dB/100ft
450 MHz	4.40 dB/100ft
550 MHz	4.90 dB/100ft
750 MHz	5.65 dB/100ft
870 MHz	6.11 dB/100ft
1000 MHz	6.55 dB/100ft
1450 MHz	8 dB/100ft
1800 MHz	8.80 dB/100ft
2250 MHz	10.0 dB/100ft
3000 MHz	11.9 dB/100ft

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

UL Temperature Rating:	80°C
Operating Temperature Range:	-40°C To +80°C

Mechanical Characteristics

Bulk Cable Weight:	28 lbs/1000ft
Maximum Recommended Pulling Tension:	138 lbs
Minimum Minor Axis Bend Radius:	3 in

Standards

NEC/(UL) Compliance:	CATV, CM
CEC/C(UL) Compliance:	CM
CPR Euroclass:	Eca
RG Type:	6
Series Type:	6

Applicable Environmental and Other Programs

Environmental Space:	Indoor (Not Riser or Plenum), Indoor/Outdoor
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes - Black only

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 UL Loading
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
1613A 0101000	Black	Reel	1,000 ft	612825119098
1613A 010A1000	Black	Reel-in-Box	1,000 ft	612825119074
1613A 010U1000	Black	UnReel	1,000 ft	612825119081
1613A 0091000	White	Reel	1,000 ft	612825119067
1613A 009A1000	White	Reel-in-Box	1,000 ft	612825119043
1613A 009U1000	White	UnReel	1,000 ft	612825119050
1613A Q5HU1000	White, Neutral	UnReel	1,000 ft	612825119036

History

Update and Revision:	Revision Number: 0.463 Revision Date: 02-03-2025
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.