


VRM10 Series Single Output

Input Voltage: 12 Vdc
of Outputs: Single



Special Features

- Designed for use in low profile applications where VRM10.0 or 10.1 specifications are required
- Output current up to 105 A continuous
- Open-collector power good (PWRGD) output
- 6-bit microprocessor voltage identification input (VID)
 - 0.8375 Vdc to 1.6000 Vdc in 12.5mV steps
 - Allows dynamic VID code changes
- Differential remote sense for improved load regulation
- Vertical plug-in to standard motherboard connector
- Selectable output load line impedances, via LL0 and LL1
- Output over-voltage signal (OVP)
- Monotonic output turn-on and turn-off with no overshoot or undershoot
- RoHS compliant
- 2 Year Warranty

Safety

VDE Certificate
No. 2487000-3336-0016

The VRM10 non-isolated DC-DC converters are designed to meet the exceptionally fast transient response requirements of today's microprocessors and fast switching logic in a compact size at a very affordable price. Advanced circuit techniques, component selection and placement optimization, state-of-the-art thermal packaging, and surface-mount technologies provide a high power density, highly reliable, and very precise voltage regulation system for advanced microprocessors.



Specifications

Rev.07.20.07
vrml0 series
2 of 10

Unless otherwise stated, all specifications are typical at nominal input, maximum continuous rated load at 25 °C and voltages are referenced to Vin-.

OUTPUT SPECIFICATIONS			INPUT SPECIFICATIONS CONTD.		
Voltage adjustability	(See VID codes, Table 3)	0.8375-1.6000 Vdc	OUTEN, VID and LL signal valid states: ON or Logic '1' 0.8 Vdc min., 5.5 Vdc max. OFF or Logic '0' -0.3 Vdc min., 0.4 Vdc max.		
Output current (Iout)		0 A min.	GENERAL CHARACTERISTICS		
VRM10-85-12-UY	Continuous	85 A max.			
	Peak non-sustained	100 A max.	Efficiency	See table 2 on page 2	VID = 1.325 V
VRM10-80-12-PY	Continuous	80 A max.	Switching frequency	80 A/85 A	2.2 MHz
	Peak non-sustained	91 A max.	Fixed (See Note 4)	105 A	1.1 MHz
VRM10-105-12-EJ	Continuous	105 A max.	Approvals and standards	(See Note 5)	IEC/EN60950 VDE
	Peak non-sustained	120 A max.	Material flammability		UL94V-0
Load line (LL) adjustability	(See LL codes, Table 1)	0.91-1.25 mW	Weight	80 A/85 A	38 g (1.34 oz)
			105 A	70 g (2.47 oz)	
Output voltage (Vout)	Vo max	VID - Rout * Iout V	MTBF	80 A/85 A	2,000,000 hours
(Vo sen+ minus Vo sen-)	Vo min	VID - Rout * Iout - 0.040V (-U/-E)	Telecordia SR-332	105 A	1,648,000 hours
(See Notes 3, B)	Vo min	VID - Rout * Iout - 0.038V (-P)	Mating connector	80 A/85 A	See Figure 7
	Where	VID = programmed voltage (V)	105 A	See Figure 8	
	Rout	Fixed or programmable	Connector fingers		Gold plated, 30 μ-inches
	Iout	output impedance (W)	ENVIRONMENTAL SPECIFICATIONS		
		Output current (A)	Temperature shock	Operating	10 °C/hour
Ripple and noise	20 MHz bandwidth	8 mV pk-pk	non-operating	20 °C/hour	
(See Notes 1, 2)			Humidity	Operating	85% RH
Short circuit protection		Continuous current limit, brickwall automatic recovery	(Non-condensing)	storage	95% RH
Remote sensing compensating voltage		Up to 300 mV max.	Altitude	Operating	10,000 feet max.
			storage	50,000 feet max.	
INPUT SPECIFICATIONS			Shock	Operational and	30 G 11ms
Input voltage range	12 Vin nominal	11.0-12.6 Vdc	non-operational	Half sine wave	
Input current			Vibration	Operational and	0.02 G ² /Hz max.
VRM10-85-12-UY	11Vin, VID=1.325 V, Iout=100 A	15.3 A	(See Note 6)	non-operational	
VRM10-80-12-PY	11Vin, VID=1.400 V, Iout=91 A	14.2 A	Thermal performance	Operating ambient	0 °C to +60 °C
VRM10-105-12-EJ	11VIN, VID=1.325V, Iout=120 A	18.5 A	(See Note 7)	temperature	
No load		250 mA typ., 300 mA max.	Storage temperature	(Non-condensing)	-40 °C to +100 °C
OUTEN OFF		50 mA max.			
UVLO turn ON voltage	0 °C <tamb <60 °C	9.5 V ± 2.6%			
UVLO turn OFF voltage	0 °C <tamb <60 °C	8.7 V ± 4.5%			
Hysteresis		0.8 V typ			
Start-up time	11.0 V < Vin <12.6 V	10 ms max.			
(using OUTEN)	(PWRGD transitioning high)				

Specifications

Rev.07.20.07
vrml10 series
3 of 10

INPUT VOLTAGE	OUTPUT VOLTAGE	OVP ⁽⁸⁾	OUTPUT CURRENT (MIN)	OUTPUT CURRENT (MAX.) CONTINUOUS	OUTPUT CURRENT (MAX.) NON-SUSTAINED	EFFICIENCY (TYP.)	REGULATION LOAD	MODEL NUMBER
12 Vdc	0.8375-1.6000 Vdc	1.8 V	0 A	80 A	91 A	85%	1.24 mV/A	VRM10-80-12-PY ⁽¹¹⁾
12 Vdc	0.8375-1.6000 Vdc	1.8 V	0 A	85 A	100 A	85%	See Table 1	VRM10-85-12-UY ⁽¹¹⁾
12 Vdc	0.8375-1.6000 Vdc	1.8 V	0 A	105 A	120 A	84%	See table 1	VRM10-105-12-EY ⁽¹¹⁾

MODEL	LL0	LL1	LOAD LINE SLOPE, Rout	UNITS
VRM10-85-12-UY	0	0	1.25	mW
VRM10-85-12-UY	0	1	1.25	mW
VRM10-85-12-UY	1	0	1.25	mW
VRM10-85-12-UY	1	1	Reserved	mW
VRM10-80-12-PY	N/A	N/A	1.24	mW
VRM10-105-12-EY	0	0	1.25	mW
VRM10-105-12-EY	0	1	1.25	mW
VRM10-105-12-EY	1	0	1.25	mW
VRM10-105-12-EY	1	1	Reserved	mW

Table 1: LL0, LL1 Load Line Codes

EFFICIENCY TABLE	
OUTPUT VOLTAGE	EFFICIENCY (typ.)
VID = 1.325 V @ 85 A	85%
VID = 1.325 V @ 80 A	85%
VID = 1.325 V @ 105 A	84%

Table 2: Efficiency Values

Notes

- Recommended output capacitance, 12 x 560 μ F aluminium polymer and 44 x 10 μ F MLCC for slew rates up to 430 A/ μ s, 14 x 560 μ F aluminum polymer and 45 x 10 μ F MLCC for slew rates up to 930 A/ μ s.
- 8 mV pk-pk ripple. Vin = 12 V, Vout = 1.35 V, Iout = 85 A.
- With the recommended capacitors (See Note 1) across the output, the output voltage stays within the load regulation window for all loads and transient events, up to 100 A for the VRM10-85-12-UY (91 A for the VRM10-80-12-PY) over a 20MHz bandwidth, 0 °C < T_{amb} < 60 °C.
- VRM10 uses a four phase buck topology. Each phase switches at 550 KHz for the VRM10-85-12-UY and VRM10-80-12-PY. This gives an equivalent switching frequency of 2.2 MHz. For the VRM10-105-12-EJ, each phase switches at 275 KHz. This gives an equivalent switching frequency of 1.1 MHz
- Recommended input fusing: one 20 A (or two 10 A in parallel) very fast acting fuse(s). The VRM10 is a high current device. Use appropriate care in handling and installation of this device, which is intended only for use within enclosed equipment.
- 0.01 G²/Hz from 5 Hz to 20 Hz, maintaining 0.02 G²/Hz from 20 Hz to 500 Hz, all axes.
- Maximum current requires adequate forced air over the converter. Please consult Figures 2 and 3 for thermal de-rating.
- When the VRM detects an output over-voltage event, the OVP pin transitions to logic high. This signal can be used to shut down the supply to the VRM, or drive a crowbar device.
- Pins 12 and 51 are not connected on VRM10-80-12-PY. On VRM10-85-12-UY, do not leave these pins floating.
- When included in the users system ESD event shall cause no out-of-regulation conditions.
- The 'Y' suffix indicates that these parts are TSE RoHS 5/6 (non Pb-free) compliant.

Specifications

Rev.07.20.07
vrml0 series
4 of 10

VOLTAGE IDENTIFICATION (VID) CODES							VOLTAGE IDENTIFICATION (VID) CODES (CONTD.)						
VID4	VID3	VID2	VID1	VID0	VID5	VID (V)	VID4	VID3	VID2	VID1	VID0	VID5	VID (V)
0	1	0	1	0	0	0.8375	1	1	0	1	0	0	1.2125
0	1	0	0	1	1	0.8500	1	1	0	0	1	1	1.2250
0	1	0	0	1	0	0.8625	1	1	0	0	1	0	1.2375
0	1	0	0	0	1	0.8750	1	1	0	0	0	1	1.2500
0	1	0	0	0	0	0.8875	1	1	0	0	0	0	1.2625
0	0	1	1	1	1	0.9000	1	0	1	1	1	1	1.2750
0	0	1	1	1	0	0.9125	1	0	1	1	1	0	1.2875
0	0	1	1	0	1	0.9250	1	0	1	1	0	1	1.3000
0	0	1	1	0	0	0.9375	1	0	1	1	0	0	1.3125
0	0	1	0	1	1	0.9500	1	0	1	0	1	1	1.3250
0	0	1	0	1	0	0.9625	1	0	1	0	1	0	1.3375
0	0	1	0	0	1	0.9750	1	0	1	0	0	1	1.3500
0	0	1	0	0	0	0.9875	1	0	1	0	0	0	1.3625
0	0	0	1	1	1	1.0000	1	0	0	1	1	1	1.3750
0	0	0	1	1	0	1.0125	1	0	0	1	1	0	1.3875
0	0	0	1	0	1	1.0250	1	0	0	1	0	1	1.4000
0	0	0	1	0	0	1.0375	1	0	0	1	0	0	1.4125
0	0	0	0	1	1	1.0500	1	0	0	0	1	1	1.4250
0	0	0	0	1	0	1.0625	1	0	0	0	1	0	1.4375
0	0	0	0	0	1	1.0750	1	0	0	0	0	1	1.4500
0	0	0	0	0	0	1.0875	1	0	0	0	0	0	1.4625
1	1	1	1	1	1	OFF	0	1	1	1	1	1	1.4750
1	1	1	1	1	0	OFF	0	1	1	1	1	0	1.4875
1	1	1	1	0	1	1.1000	0	1	1	1	0	1	1.5000
1	1	1	1	0	0	1.1125	0	1	1	1	0	0	1.5125
1	1	1	0	1	1	1.1250	0	1	1	0	1	1	1.5250
1	1	1	0	1	0	1.1375	0	1	1	0	1	0	1.5375
1	1	1	0	0	1	1.1500	0	1	1	0	0	1	1.5500
1	1	1	0	0	0	1.1625	0	1	1	0	0	0	1.5625
1	1	0	1	1	1	1.1750	0	1	0	1	1	1	1.5750
1	1	0	1	1	0	1.1875	0	1	0	1	1	0	1.5875
1	1	0	1	0	1	1.2000	0	1	0	1	0	1	1.6000

Table 3: Voltage Identification Codes

Specifications

Rev.07.20.07
vrn10 series
5 of 10

SIGNAL ELECTRICAL INTERFACE						
CHARACTERISTIC - SIGNAL NAME	SYMBOL	MIN	TYP	MAX	UNITS	NOTES AND CONDITIONS
OUTEN - on	$V_{OUTEN(on)}$	0.8		5.5	V	No pull up resistor provided by the VRM
OUTEN - off	$V_{OUTEN(off)}$	-0.3		0.4	V	No pull up resistor provided by the VRM
OUTEN - leakage current		-1		1	μA	
PWRGD - low	$V_{PWRGD(low)}$			0.4	V	Sink current 4 mA
PWRGD - sink current	$I_{PWRGD(sink)}$			4	mA	Open-collector output to not more than 5.5 V
PWRGD - low threshold		72	74	76	%	Percentage of VID code setting
PWRGD - turn-on response to OUTEN going high	T_{rise}	0	4	10	ms	For waveforms, refer to Application Note 171
VID - high	$V_{ih(VID)}$	0.8		5.5	V	
VID - low	$V_{il(VID)}$	-0.3		0.4	V	
VID - pull up current	$I_{(VID)}$	35	50	65	μA	
OVP signal trip point	$R_{(VID)}$	1.7		VID + 0.2	V	
OVP drive voltage			1.9 (5.5)		V	$I_{ovp} = -100 \text{ mA}$ ($I_{ovp} = -1 \text{ mA}$)
LL - high	$V_{ih(LL)}$	0.8		5.5	V	VRM10-85-12-UY only
LL - low	$V_{il(LL)}$	-0.3		0.4	V	VRM10-85-12-UY only
LL - input impedance	$Z_{i(LL)}$	2.18	2.21		kW	VRM10-85-12-UY only
VR_Hot# - low	$V_{VR_HOT\#(low)}$	0		0.4	V	Sink current 30 mA. VR_HOT# is pulled as a thermal event is present in the VRM
VR_Hot# - sink current	$I_{VR_HOT\#(sink)}$	0		30mA		Open-collector output to not more than V_{in} . Sinks current as long as thermal event is present in the VRM

ELECTROMAGNETIC COMPATIBILITY						
CHARACTERISTIC - SIGNAL NAME	SYMBOL	MIN	TYP	MAX	UNITS	NOTES AND CONDITIONS
ESD - operating (See Note 10)		15	kV			IEC61000-4-2. In end user equipment
ESD - non-operating				25	kV	IEC61000-4-2. In end user equipment
Radiated emissions		B			Class	FCC and EN55022. In end user equipment
Input characteristics: Input current - operating	I_{IN}		10.7		A	$V_{in} = V_{in}(typ.)$, $I_{out(cont.)} = 85A$, VID = 1.325 V
Input capacitance - external bypass	C_{INext}	680	1000		μF	

Specifications

Rev.07.20.07
vr10 series
6 of 10




Figure 1: Thermal Derating Curve for VRM10-85-12-UY
(See Note A)




Figure 2: Thermal Derating Curve for VRM10-80-12-PY
(See Note A)




Figure 3: Thermal Derating Curve for VRM10-105-12-EY
(See Note A)





Figure 4: Load Regulation (See Notes 3 and B)

Notes


- A For the LFM and VID conditions graphed, there is no derating between 0 °C and 25 °C.
- B For load regulation equations: VID is in Volts, programmed by the VID bits (refer to Table 3); Rout is in W's, programmed by the LL bits (refer to Table 1); and the output current, Iout is in amps. VWindow is 0.040 for VRM10-85-12-UY and 0.038 for VRM10-80-12-PY.
- C Efficiency Vs load plotted is representative of a typical VRM10-85-12-UY with VID = 1.4 V, LL0 = 0, LL1 = 1.
- D Shown for a VRM10-80-12-P with VID = 1.4 V.

Specifications


Rev.07.20.07
vrn10 series
7 of 10



**Figure 5: Typical Efficiency Vs Load (See Note C)
For VRM10-85-12-UY and VRM10-80-12-PY**




**Figure 5a: Typical Efficiency Vs Load (See Note C)
For VRM10-105-12-EJ**



**Figure 6: Short Circuit and Over Current Protection (See Note D)
For VRM10-85-12-UY and VRM10-80-12-PY**

Specifications

Rev.07.20.07
vrm10 series
8 of 10




PIN CONNECTIONS			
PIN NO.	FUNCTION	PIN NO.	FUNCTION
1	Vin+	62	Vin-
2	Vin+	61	Vin-
3	Vin+	60	Vin-
4	Vin+	59	Vin-
5	N/U	58	VRM_pres#
6	VID4	57	Key
7	VID3	56	VID2
8	VID1	55	VID0
9	OV P	54	VID5
10	PWRGD	53	Outen
11	Vo sen-	52	Vo sen+
12	LL0 ⁽⁹⁾	51	LL1 ⁽⁹⁾
13	Vo-	50	Vo+
14	Vo+	49	Vo+
15	Vo-	48	Vo-
16	Vo+	47	Vo+
17	Vo-	46	Vo-
18	Vo+	45	Vo+
19	Vo-	44	Vo-
20	Vo+	43	Vo+
21	Vo-	42	Vo-
22	Vo+	41	Vo+
23	Vo-	40	Vo-
24	Vo+	39	Vo+
25	Vo-	38	Vo-
26	Vo+	37	Vo+
27	Vo-	36	Vo-
28	Vo+	35	Vo+
29	Vo-	34	Vo-
30	Vo+	33	Vo+
31	Vo-	32	Vo-

Figure 7: 80/85 A Mechanical Drawing and Pinout Table

Specifications

Rev.07.20.07
vrml0 series
9 of 10



PIN CONNECTIONS			
PIN NO.	FUNCTION	PIN NO.	FUNCTION
1	Vin-	54	Vin+
2	Vin-	53	Vin+
3	Vin-	52	Vin+
4	VID4	51	VID3
5	VID2	50	VID1
6	VID0	49	VID5
7	Vo sen+	48	Vo_sen-
8	V _{CC} PWRGD	47	VR_HOT#
9	Outen	46	LL0 ⁽⁹⁾
10	OVP	45	LL1 ⁽⁹⁾
11	NA	44	NA
12	VRM_pres#	43	NA
13	Vo+	42	Vo+
14	Vo+	41	Vo+
15	Vo+	40	Vo+
16	Vo-	39	Vo-
17	Vo-	38	Vo-
18	Vo-	37	Vo-
19	Vo+	36	Vo+
20	Vo+	35	Vo+
21	Vo+	34	Vo+
22	Vo-	33	Vo-
23	Vo-	32	Vo-
24	Vo-	31	Vo-
25	Vo+	30	Vo+
26	Vo+	29	Vo+
27	Vo+	28	Vo+

Figure 8: 105 A Mechanical Drawing and Pinout Table

Americas

5810 Van Allen Way
Carlsbad, CA 92008
USA
Telephone: +1 760 930 4600
Facsimile: +1 760 930 0698

Europe (UK)

Waterfront Business Park
Merry Hill, Dudley
West Midlands, DY5 1LX
United Kingdom
Telephone: +44 (0) 1384 842 211
Facsimile: +44 (0) 1384 843 355

Asia (HK)

16th - 17th Floors, Lu Plaza
2 Wing Yip Street, Kwun Tong
Kowloon, Hong Kong
Telephone: +852 2176 3333
Facsimile: +852 2176 3888

For global contact, visit:

www.powerconversion.com

technicalsupport@powerconversion.com

While every precaution has been taken to ensure accuracy and completeness in this literature, Emerson Network Power assumes no responsibility, and disclaims all liability for damages resulting from use of this information or for any errors or omissions.

Emerson Network Power.

The global leader in enabling
business-critical continuity.

- AC Power
- Connectivity
- DC Power
- **Embedded Power**
- Inbound Power
- Integrated Cabinet Solutions
- Outside Plant
- Precision Cooling
- Site Monitoring and Services

EmersonNetworkPower.com

Emerson Network Power and the Emerson Network Power logo are trademarks and service marks of Emerson Electric Co.
©2007 Emerson Electric Co.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Emerson Network Power:

[VRM10-105-12-EY](#) [VRM10-80-12-PY](#) [VRM10-80-12-P](#) [VRM10-85-12-U](#) [VRM10-85-12-UY](#)