




NOTES:

- 1 - HOUSING MATERIAL: GLASS FILLED LCP, COLOR: BLACK.
- 2 - TERMINAL MATERIAL: PHOSPHOR BRONZE
- 3 - SEE SHEET 2 FOR CIRCUIT SIZE, PART NUMBERS AND OVER-ALL DIMENSIONS.
- 4 - FOR ILLUSTRATION, 6 CIRCUIT ASSEMBLY SHOWN.
- 5 - REFER TO PRODUCT SPECIFICATION PS-79107.
- 6 - PACKAGING PER PK-70873-0180.
- 7 - SEE SHEET 3 FOR VOIDED ASSEMBLIES.
- 8 - CKTS. NUMBERED FROM LEFT TO RIGHT WHEN PART IS VIEWED FROM TOP WITH RECESS ON RIGHT AS SHOWN.

PLATING OPTION :

- (4) 0.76µm MIN. GOLD PLATE IN SELECTED AREA AND 1.91µm MIN. TIN IN SELECTED AREA OVER 1.27µm MIN. NICKEL OVER-ALL
- (5) 0.38µm MIN. GOLD PLATE IN SELECTED AREA AND 1.91µm MIN. TIN IN SELECTED AREA OVER 1.27µm MIN. NICKEL OVER-ALL
- (6) 0.13µm MIN. GOLD PLATE IN SELECTED AREA AND 1.91µm MIN. TIN IN SELECTED AREA OVER 1.27µm MIN. NICKEL OVER-ALL



REVISE PDR#S1436 EC NO: S2007-0532 DRWN:KFLIM CHKD:M-LONG APPR:SKTOH 2006/12/06 2006/12/07 2006/12/07	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		▽=0	4 PLACES	mm ± ---	INCH ± ---	DRAWN BY AAB	DATE 1998/05/15	TITLE 2MM DUAL ROW, FFC VERTICAL RECEPTACLE				
		▽=0	3 PLACES	± 0.10	± ---	CHECKED BY MJM	DATE 1998/05/15					
		2 PLACES	± 0.15	± ---	APPROVED BY WAZ	DATE 1998/05/15						
		1 PLACE	± ---	± ---	MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
E2 REV			ANGULAR ±1/2°			SEE TABLE		SDA-79108-****		1 OF 4		
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

10987654321

F

E

D

C

B

A

ib_frame_A3_P_AM_T
Rev. E 2006/04/15

987654321

MOLDED VOID OPTION

CKT. SIZE	ASSEMBLY		VOID LOCATION(S) SEE SHEET 1 FOR CONVENTION		PLATING OPTION	DIM. "A"	DIM. "B"
	EDP NO.	ENG. NO.	ROW	CKT. NO.(S)			
44	791085003	79108-5003	ROW A	I3	4	(42.00)	(44.19)
44	791085004	79108-5004	ROW B	I0	4	(42.00)	(44.19)



NOTES:

1. TERMINALS WILL BE PRESENT IN VOIDED LOCATIONS HOWEVER, PIN WINDOWS WILL BE CLOSED.

2. VOIDS CAN ONLY BE PRESENT IN ONE ROW OF THE CONNECTOR.


REVISE PDR#S1436 EC NO: S2007-0532 DRWN:KFLM 2006/12/06 CHKD:M.LONG 2006/12/07 APPR:SKTOH 2006/12/07 E2	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mmINCH 4 PLACES ± --- ± --- 3 PLACES ± 0.10 ± --- 2 PLACES ± 0.15 ± --- 1 PLACE ± --- ± --- ANGULAR ±1/2°	DIMENSION STYLE MM ONLY DRAWN BY DATE AAB 1998/05/15 CHECKED BY DATE MJM 1998/05/15 APPROVED BY DATE WAZ 1998/05/15 MATERIAL NO.	SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	TITLE 2MM DUAL ROW, FFC VERTICAL RECEPTACLE	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SEE TABLE	MOLEX INCORPORATED		DOCUMENT NO. SDA-79108-****		SHEET NO. 3 OF 4	
		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

ASSEMBLY P/N PACKED IN T&R	CKT SIZE	PLATING OPTION	DIM A	DIM B	(F)	(Bo)	(W)
79108-6001	16	5	14.00	16.19	11.50	16.60	24.00




NOTES:


1. LEADER AND TRAILER TAPE



2. PEELING OFF FORCE OF THE TOP TAPE: 20-80gf.
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIGURE)



- PACKAGING STANDARD IS AS PER EIA-481.
- THE TAPE IS TREATED FOR ANTI-STATIC.
- MATERIAL: CLEAR POLYSTYRENE.
- TAPE & REEL QUANTITY = 800 PCS/REEL



REVISE PDR#S1436 EC NO: S2007-0532 DRWN:KFLIM CHKD:M.LONG APPR:SKTOH 2006/12/06 2006/12/07 2006/12/07	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																												
			<table><tr><td></td><td>mm</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>3 PLACES</td><td>± 0.10</td><td>± ---</td></tr><tr><td>2 PLACES</td><td>± 0.15</td><td>± ---</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± ---</td></tr></table>			mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± 0.10	± ---	2 PLACES	± 0.15	± ---	1 PLACE	± ---	± ---	<table><tr><td>DRAWN BY</td><td>DATE</td></tr><tr><td>AAB</td><td>1998/05/15</td></tr><tr><td>CHECKED BY</td><td>DATE</td></tr><tr><td>MJM</td><td>1998/05/15</td></tr><tr><td>APPROVED BY</td><td>DATE</td></tr><tr><td>WAZ</td><td>1998/05/15</td></tr></table>		DRAWN BY	DATE	AAB	1998/05/15	CHECKED BY	DATE	MJM	1998/05/15	APPROVED BY	DATE	WAZ	1998/05/15	TITLE 2MM DUAL ROW, FFC VERTICAL RECEPTACLE			
				mm	INCH																																
			4 PLACES	± ---	± ---																																
			3 PLACES	± 0.10	± ---																																
			2 PLACES	± 0.15	± ---																																
			1 PLACE	± ---	± ---																																
			DRAWN BY	DATE																																	
			AAB	1998/05/15																																	
			CHECKED BY	DATE																																	
MJM	1998/05/15																																				
APPROVED BY	DATE																																				
WAZ	1998/05/15																																				
ANGULAR ±1/2°		MOLEX MOLEX INCORPORATED																																			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		DOCUMENT NO.		SHEET NO.																															
		SEE TABLE		SDA-79108-****		4 OF 4																															
		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																			

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

SEE TABLE

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION