


1918472

REV

THIS DRAWING IS A CONTROLLED DOCUMENT

Restricted to: General Release

USED ON



Connector(s): LC-Duplex
Mode: MM
Housing Color: Beige
Geom. Spec: N/A

Number of Fibers: 2
Mode: MM
Jacket Diameter: 2.0 mm
Jacket Color: Aqua
FiberType: XG - 50/125

Connector(s): Pigtail - (1.6 to 2.0mm)
Mode: MM
Housing Color: Pigtail
Geom. Spec: N/A

LC strain relief - 1.6 to 2.0 mm cable
Color: Beige/Beige

Pigtail - 1.6 to 2.0 zipcord
Color: Pigtail

Notes:


- 1 Includes dust caps (not shown on print).
- 2 Product and Processing must meet requirements of Tyco Electronics Standard 230-702

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS, INC. AND ITS SUBSIDIARIES. IT MAY BE DISCLOSED TO OTHERS ONLY BY WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

	A	Rev Per EC#	RELEASE	4/3/2006	-		
P	LTR	REVISION	RECORD	DATE	DIN	APVD	



Customer Print

DIMENSIONS:
meters

TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0 PLC	± .
1 PLC	± .
2 PLC	± .
3 PLC	± .
4 PLC	± .

DIN		Cable Assy Configurator		MATERIAL	HEAT TREAT	
CHK		Cable Assy Configurator				
APVD		Refer to Engineering Change				
NAME						
FO C/A - 2 fiber, 2mm, XG - 50/125, OFNR (Riser) jacket, LC-Duplex to Pigtail - (1.6 to 2.0mm)						
SCALE		SIZE	DRAWING NO.		SHEET	REV
NTS		A2	C- 1918472		1 of 3	A

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.
PAGE NO

LOC
CE
DIST
16

CAC Customer Layout Rev: D

Part #	L (meters)	LC-Duplex, Beige		Pigtail - (1.6 to 2.0mm), Pigtail	
		IL (dB)	RL (dB)	IL (dB)	RL (dB)
0-1918472-1	0.950 - 1.050	0.50	N/A	0.00	N/A
0-1918472-2	1.950 - 2.050	0.50	N/A	0.00	N/A
0-1918472-3	2.950 - 3.050	0.50	N/A	0.00	N/A
0-1918472-4	3.920 - 4.080	0.51	N/A	0.01	N/A
0-1918472-5	4.920 - 5.080	0.51	N/A	0.01	N/A
0-1918472-6	5.920 - 6.080	0.51	N/A	0.01	N/A
0-1918472-7	6.920 - 7.080	0.51	N/A	0.01	N/A
0-1918472-8	7.920 - 8.080	0.51	N/A	0.01	N/A
0-1918472-9	8.850 - 9.150	0.51	N/A	0.01	N/A
1-1918472-0	9.850 - 10.150	0.52	N/A	0.02	N/A
1-1918472-1	10.850 - 11.150	0.52	N/A	0.02	N/A
1-1918472-2	11.850 - 12.150	0.52	N/A	0.02	N/A
1-1918472-3	12.850 - 13.150	0.52	N/A	0.02	N/A
1-1918472-4	13.850 - 14.150	0.52	N/A	0.02	N/A
1-1918472-5	14.850 - 15.150	0.52	N/A	0.02	N/A
1-1918472-6	15.840 - 16.160	0.52	N/A	0.02	N/A
1-1918472-7	16.830 - 17.170	0.53	N/A	0.03	N/A
1-1918472-8	17.820 - 18.180	0.53	N/A	0.03	N/A
1-1918472-9	18.810 - 19.190	0.53	N/A	0.03	N/A
2-1918472-0	19.800 - 20.200	0.53	N/A	0.03	N/A
2-1918472-1	20.790 - 21.210	0.53	N/A	0.03	N/A
2-1918472-2	21.780 - 22.220	0.53	N/A	0.03	N/A
2-1918472-3	22.770 - 23.230	0.53	N/A	0.03	N/A
2-1918472-4	23.760 - 24.240	0.54	N/A	0.04	N/A
2-1918472-5	24.750 - 25.250	0.54	N/A	0.04	N/A
2-1918472-6	25.740 - 26.260	0.54	N/A	0.04	N/A
2-1918472-7	26.730 - 27.270	0.54	N/A	0.04	N/A
2-1918472-8	27.720 - 28.280	0.54	N/A	0.04	N/A
2-1918472-9	28.710 - 29.290	0.54	N/A	0.04	N/A
3-1918472-0	29.700 - 30.300	0.55	N/A	0.05	N/A
3-1918472-1	30.690 - 31.310	0.55	N/A	0.05	N/A
3-1918472-2	31.680 - 32.320	0.55	N/A	0.05	N/A
3-1918472-3	32.670 - 33.330	0.55	N/A	0.05	N/A
3-1918472-4	33.660 - 34.340	0.55	N/A	0.05	N/A
3-1918472-5	34.650 - 35.350	0.55	N/A	0.05	N/A
3-1918472-6	35.640 - 36.360	0.55	N/A	0.05	N/A
3-1918472-7	36.630 - 37.370	0.56	N/A	0.06	N/A
3-1918472-8	37.620 - 38.380	0.56	N/A	0.06	N/A
3-1918472-9	38.610 - 39.390	0.56	N/A	0.06	N/A
4-1918472-0	39.600 - 40.400	0.56	N/A	0.06	N/A
5-1918472-0	49.500 - 50.500	0.58	N/A	0.08	N/A

	A	Rev Per EC#	RELEASE	4/3/2006	-		
P	LTR	REVISION RECORD		DATE	DIN	APVD	

DIMENSIONS:
meters



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

9 P.L.C.	± .
1 P.L.C.	± .
2 P.L.C.	± .
3 P.L.C.	± .
4 P.L.C.	± .

Customer Print

DIN Cable Assy Configurator		MATERIAL -	HEAT TREAT -	
OK Cable Assy Configurator		AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608		
APVD Refer to Engineering Change				
NAME FO C/A - 2 fiber, 2mm, XG - 50/125, OFNR (Riser) jacket, LC-Duplex to Pigtail - (1.6 to 2.0mm)				
SCALE NTS	SIZE A2	DRAWING NO C- 1918472	SHEET 2 of 3	REV A

8

7

6

5

4

3

2

1

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.
REV NO

LOC
CE
DIST
16

CAC Customer Layout Rev: D

8

7

6

5

4

3

2

1

Label 1

Per specification 107-1645-1



Trace # - Bar Code

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

	A	Rev Per EC#	RELEASE	4/3/2006	-		
P	LTR	REVISION RECORD		DATE	DIN	APVD	

DIMENSIONS: meters

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± .
1 PLC ± .
2 PLC ± .
3 PLC ± .
4 PLC ± .

Customer Print

DIN	Cable Assy Configurator	MATERIAL	-	HEAT TREAT	
OK	Cable Assy Configurator	AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD	Refer to Engineering Change				
NAME	FO C/A - 2 fiber, 2mm, XG - 50/125, OFNR (Riser) jacket, LC-Duplex to Pigtail - (1.6 to 2.0mm)				
SCALE	NTS	SIZE	A2	DRAWING NO	C- 1918472
SHEET	3 of 3			REV	A

D

C

B

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity Divested:](#)

[3-1499151-5](#)