


Cat5e 350 MHz Bulk Solid-Core Plenum-Rated PVC Cable, Black, 1000 ft.

MODEL NUMBER: **N024-01K-BK**



Highlights

- Ideal for all horizontal wiring applications
- Rated for 350 MHz/1 Gbps communications
- High-quality 24 AWG 4-pair solid copper wire
- Plenum-rated PVC jacket
- Meets IEEE 802.3ab and ANSI/EIA/TIA 568 standards

Package Includes

- N024-01K-BK Cat5e 350 MHz Bulk Solid-Core Plenum-Rated PVC Cable, Black, 1000 ft.

Description

The N024-01K-BK Cat5e 350 MHz Bulk Solid-Core Plenum-Rated PVC Cable is premium cabling designed for Cat5/5e premise applications in air ducts and drop ceilings, such as connecting an Ethernet wall jack to a router, patch panel or switch. Designed for fast transmission and excellent signal quality, this black cable ensures peak performance through your LAN (local area network).

Manufactured from 24 AWG copper wire, the four-pair solid UTP N024-01K-BK delivers speeds up to 350 MHz/1 Gbps. Protected by a plenum-rated PVC jacket, this cable is ideal for all horizontal wiring applications, including 10/100/1000 Base-T Ethernet, 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type 3 applications.

The N024-01K-BK meets most current industry standards, including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 5e, draft 11).

Features

Perfect Solution for Cat5/5e Premise Applications in Air Ducts and Drop Ceilings

- Designed for fast transmission and excellent signal quality throughout your LAN
- Delivers speeds up to 350 MHz/1 Gbps
- Ideal for all horizontal wiring applications, including 10/100/1000 Base-T Ethernet, 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type 3 applications

Premium Construction for Superior Performance

- Made from 24 AWG copper wire
- 4-pair solid UTP
- Plenum-rated PVC jacket
- Meets most current industry standards, including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568,

ISO/IEC 11801 and ETL (category 5e, draft 11)

Specifications

| MODEL TEXT | |
|-------------------------------------|--|
| What Does This Product Do? | Premium cabling designed for Cat5/5e premise (in-wall) applications in air ducts and drop ceilings, such as connecting an Ethernet wall jack to a router, patch panel or switch. |
| INPUT | |
| Cable Length (ft.) | 1000 |
| Cable Length (m) | 304.8 |
| PHYSICAL | |
| Shipping Dimensions (hwd / in.) | 10.63 x 14.17 x 13.78 |
| Shipping Dimensions (hwd / cm) | 27.00 x 35.99 x 35.00 |
| Shipping Weight (lbs.) | 20 |
| Shipping Weight (kg) | 9.07 |
| Color | Black |
| CONNECTIONS | |
| Side A - Connector 1 | BARE WIRE |
| Side B - Connector 1 | BARE WIRE |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>