

# FWA-1204

## Tabletop Fanless Intel based Platform with 4 GbE LAN Ports

NEW



### Features

- Tabletop fanless application platform
- Intel EP80579 Integrated Processor solution
- Single channel DDR2 SODIMM support up to 2 GB
- 4 x 10/100/1000 Mbps GbE LAN ports
- Console port for local setting



CE FCC

## Introduction

The FWA-1204 incorporates Intel's System-on-Chip which combines Intel's QuickAssist Technology and integrates an Intel Pentium M class core, memory controller and I/O controller. The high-performance CPU core supplies the horse power needed to perform deep packet inspection and other complex operations and is particularly optimized for entry level to mid-range network security appliances.

Security applications can run existing x86 software applications because of backward code compatibility with earlier Intel processors. Most network security platforms already run on Intel x86 processors and can run existing software applications on Intel EP80579 integrated processor because it is backward compatible with earlier Intel processors. Typical appliance workloads which require IP-SEC encryption, acceleration and compression of content can offload processing on to the QuickAssist Integrated Accelerator which increases the effective data throughput and performance and reduces the overall power consumption of a given application.


The FWA-1204 features a low-power design, and supports up to 2 GB DDR2 on one single-channel SODIMM. It provides a total of four GbE LANs, three of which are from the on-chip MACs and the fourth from a PCIe-based Intel 82574 Ethernet controller. The on-chip MACs are routed to 3 Marvell PHY devices. The system supports one 2.5" SATA HDD and CompactFlash for OS and/or Internet security applications. The system is fully FCC, CE and RoHS compliant.

## Specifications

Processor System	CPU & Chipset	Intel EP80579 Integrated Processor supports 600 MHz processor	
	Max. Speed	600 MHz/Embedded	
	Front Side Bus	400/533 MHz	
	BIOS	Award™ 4 Mbit Flash	
Memory	Technology	Single channel DDR2 800/667/533/400 MHz SODIMM	
	Capacity	Up to 2 GB with 1 slot	
Ethernet	Interface	4 x 10/100/1000 Mbps	
	Controller	Three GbE from Intel EP80579 Integrated Processor + Marvell 88E1111 PHY One GbE from Intel 82574, with one segment LAN bypass	
Storage	SATA	1 x 2.5" HDD bay Max. data transfer rate at 150 MB/sec	
	Controller	JMicron (SATA to IDE bridge)	
	Compact Flash Socket	1 x CF socket on IDE 0 (Primary)	
Peripheral	USB	2 x USB 2.0	
	Serial	1 x RS-232 with RJ-45 connector	
Power	Watts	65 W	
	Input	90 ~ 246 V AC, auto range	
Environment		Operating	Non-Operating
	Temperature	0 ~ 40° C (32 ~ 104° F)	-20 ~ 75° C (-4 ~ 167° F)
	Humidity	5 ~ 85 % @ 40° C (104° F)	5 ~ 95 %
Physical	Dimensions (W x H x D)	250 x 42 x 185.8 mm (9.8" x 1.6" x 7.3")	
	Weight	1.2 kg (2.6 lb)	

## Dimensions

Unit: mm (inch)



## Ordering Information

Part number	Processor	LAN
FWA-1204E	600 M/Embedded	4

## Accessories

P/N	Description
1700001947	2P 180 cm, USA
1700001948	2P 180 cm, Europe
1700001949	2P 180 cm, JP

## Packing List

P/N	Description
1700002270	Console cable RJ-45 to D-Sub 9PIN 1.8 M

