





PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF VECTOR ELECTRONICS & TECHNOLOGY, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF VECTOR ELECTRONICS & TECHNOLOGY, INC IS PROHIBITED.



REVISIONS				
ZONE	REV	DESCRIPTION	DATE	APPROVED
ALL	A	INITIAL RELEASE	08/31/12	









TOP EJECTOR HANDLE DETAIL
MIRROR VIEW OF BOTTOM HANDLE




TOP SUPPORT BRACKET DETAIL
MIRROR VIEW OF BOTTOM BRACKET




BOTTOM EJECTOR HANDLE DETAIL



BOTTOM SUPPORT BRACKET DETAIL




CENTER L-BRACKET DETAIL



CM10 PARTS LIST

ITEM NO	DESCRIPTION	QTY	U/M
1	EJECTOR HANDLE, BOTTOM	1	EACH
2	EJECTOR HANDLE, TOP	1	EACH
3	SUPPORT BRACKET, BOTTOM	1	EACH
4	SUPPORT BRACKET, TOP	1	EACH
5	ID PANEL	2	EACH
6	CENTER L-BRACKET	2	EACH
7	RETAINER SLEEVE	2	EACH
8	CAPTIVE SCREW, M2.5-0.45X11mm	2	EACH
9	SCREW, FLAT HEAD, M2.5-0.45X8mm	4	EACH
10	SCREW, PAN HEAD, M2.5-0.45X14mm	2	EACH
11	SCREW, PAN HEAD, M2.5-0.45X10mm	2	EACH
12	HEX NUT, M2.5X0.45-6H	8	EACH



ID PANEL DETAIL

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES TOLERANCES: DEC .X.X ±0.1 DEC .X.XX ±0.03 DEC .X.XXX ±0.010 FRACTIONS ±0.050 ANGLES ±1°		NAME DRAWN TRUSHAR DATE 08/31/12		 11116 VANOWEN ST. NORTH HOLLYWOOD, CA 91605 ELECTRONICS & TECHNOLOGY, INC. www.vectorlect.com
THIRD ANGLE PROJECTION		Q.A.		
MATERIAL		COMMENTS:		
FINISH				
		SIZE DWG. NO.		REV
		D CM10		A
		SCALE: 4:1 CAGE CODE : 82893		SHEET 1 OF 1