

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2013

© COPYRIGHT 2013

BY - TE Connectivity


ALL RIGHTS RESERVED.

LOC





DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER E.O. PI6218	30JUL1999		CLW
	C	REVISED PER E.O. PI9162	15MAR2006		RDR
	DI	REVISED PER ECO-16-005960	18APR2016	KM	DM
	E	REVISED PER ECR-16-017570	12DEC2016	KM	DM



3D VIEW



DIODE POLARITY REFERENCE

6. MOLDED-IN DIODE ELECTRICAL CHARACTERISTICS
PEAK REVERSE VOLTAGE = 400.0 V MAX.
PEAK FORWARD VOLTAGE = 1.0 V MAX.
AVERAGE FORWARD CURRENT = 3.0 A MAX.


5. MATERIAL: PA GF BLACK

4. TEMPERATURE RANGE : -55°C TO +125°C.

3. RECEPTACLE MATES WITH DT06-2S-****.

2. ALL DIMENSIONS W/O TOLERANCE ARE +/- .025 [+/- 0.63]

1. ALL DIMENSIONS ARE INCHES (METRIC).

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. McKEE 17DEC2013	 TE Connectivity					
DIMENSIONS: INCHES[mm]		CHK K. McKEE 25AUG2015	NAME TERMINATING RECEPTACLE, 2-PIN DT SERIES					
		APVD D. MEYER 25AUG2015						
		PRODUCT SPEC -	SIZE A3			CAGE CODE 4AFU8	DRAWING NO C-DT04-2P-RT02	RESTRICTED TO -
MATERIAL -		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-	APPLICATION SPEC -	WEIGHT 10.37 g		Customer Drawing		
FINISH -		SCALE 2:1		SHEET 1		OF 1		REV E